

Zyklus Mini



EAN:	4013288145765	Size:	170x85x35 mm
Part number:	05346293001	Weight:	361 g
Article number:	Bit-Check 30 Zyklus Mini 2	Country of origin:	CZ
		Customs tariff number:	82079030

- Bit-Checks convince due to their functionality in a minimum of space
- Wera Mini ratchet for particularly fast screwdriving even in confined spaces
- Ideal for working in confined spaces
- Tough viscous bits for universal use
- In handy and robust Bit-Check

The Wera Mini ratchet: a symbiosis of strength and stylishness. Incredibly robust due to its drop-forged, full-steel design. Can withstand torque forces up to 65 Nm. The petite sizing is particularly suited for work in confined spaces. The thumbwheel allows fast screwdriving. Comes in a set in the proven Wera Bit-Check with socket adaptor and belt clip. Simple tool removal and reinsertion is ensured, very robust and durable.

Web link

https://products.wera.de/en/zyklus_ratchets_and_accessories_zyklus_mini_bit-check_30_zyklus_mini_2.html

Wera - Bit-Check 30 Zyklus Mini 2
05346293001 - 4013288145765

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bit-Check 30 Zyklop Mini 2, 31pieces

Zyklop Mini



Set contents:




8001 A
05073999001 1 x 1/4" x 87 mm



889/4/1 K
05052502001 1 x 1/4" x 50 mm



870/1
05136000001¹⁾ 1 x 1/4" x 25 mm
1) With friction ball; for manual nut spinner sockets



851/1 TZ PH
05056505001 2 x PH 1 x 25 mm
05056510001 3 x PH 2 x 25 mm
05056525001 1 x PH 3 x 25 mm



867/1 TZ TORX®
05066305001 1 x TX 10 x 25 mm
05066308001 1 x TX 15 x 25 mm
05066310001 1 x TX 20 x 25 mm
05066312001 1 x TX 25 x 25 mm
05066315001 1 x TX 30 x 25 mm
05066320001 1 x TX 40 x 25 mm



867/1 Z TORX® BO
05066500001 1 x TX 10 x 25 mm
05066505001 1 x TX 15 x 25 mm
05066510001 1 x TX 20 x 25 mm
05066515001 1 x TX 25 x 25 mm
05066525001 1 x TX 30 x 25 mm



840/1 Z Hex-Plus
05135072001 1 x 3/32" x 25 mm
05135073001 1 x 1/8" x 25 mm
05135074001 1 x 5/32" x 25 mm
05135075001 1 x 3/16" x 25 mm
05135076001 1 x 1/4" x 25 mm



800/1 TZ
05056225001 1 x 1 x 5.5 x 25 mm



868/1 Z
05066405001 1 x # 1 x 25 mm
05066410001 3 x # 2 x 25 mm
05066415001 1 x # 3 x 25 mm

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_zyklop_mini_bit-check_30_zyklop_mini_2.html

Wera - Bit-Check 30 Zyklop Mini 2
05346293001 - 4013288145765

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklop Mini

The Zyklop Mini Ratchets




Zyklop Mini



For all difficult-to-access applications.

Small return angle



The fine tooth mechanism, with its 60 teeth, allows a small return angle of only 6° – ideal for precision work.

Rapid screwdriving



Thumbwheel enables rapid screwdriving, even when there isn't sufficient room for ratcheting use.

Simple direction change



Simple switching between left/right operations.

Slim design



Its slim design makes it ideal for all particularly confined working situations.

Is such a small tool sufficiently resilient?



The Zyklop Mini 1 can withstand at least 65 Nm. That is far more power than can normally be transferred to such a small tool.

What parts can be connected to the Zyklop Mini 1?



Bits and sockets. Bits can be connected directly. However, a holder can be connected first and then the bit can be attached to this. This then serves as an extension with a free-turning sleeve. An adaptor e.g. Wera 870/1 is needed for sockets – 1/4" hexagonal on a square drive (included in the Bit-Check and with the individual Zyklop Mini 1 in the set).

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_zyklop_mini_bit-check_30_zyklop_mini_2.html

Wera - Bit-Check 30 Zyklop Mini 2
05346293001 - 4013288145765

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de