




AkroDrawers®

Keep supplies, parts, tools and other materials secure and dust-free

- Nine sizes and five colors make it easy to label and color code inventory
- Use alone or with Pick Racks, Cabinets, Mobile Carts, or Enclosed Shelving

AkroDrawers®



AkroDrawers Model No.	Outside Dimensions (In.)			Inside Dimensions (In.)			Capacity/Qty.		Dividers*	Pkg. Qty
	L	W	H	L	W	H	Weight Capacity	Ctn. Qty.		
31142	11-5/8	3-3/4	4-5/8	10-1/4	3-1/16	4-7/16	15 lbs.	6	41440 (8)	6
31148	17-5/8	3-3/4	4-5/8	16-1/4	3-1/16	4-7/16	20 lbs.	6	41440 (13)	6
31162	11-5/8	5-9/16	4-5/8	10-1/4	4-7/8	4-7/16	20 lbs.	6	41460 (8)	6
31168	17-5/8	5-9/16	4-5/8	16-1/4	4-7/8	4-7/16	25 lbs.	6	41460 (13)	6
31164	23-7/8	5-9/16	4-5/8	22-1/2	4-7/8	4-7/16	25 lbs.	6	41460 (18)	6
31182	11-5/8	8-3/8	4-5/8	10-1/4	7-5/8	4-7/16	20 lbs.	4	41480 (8)	6
31188	17-5/8	8-3/8	4-5/8	16-1/4	7-5/8	4-7/16	25 lbs.	4	41480 (13)	6
31112	11-5/8	11-1/8	4-5/8	10-1/4	10-7/16	4-7/16	25 lbs.	4	41410 (8)	8
31118	17-5/8	11-1/8	4-5/8	16-1/4	10-7/16	4-7/16	25 lbs.	4	41410 (13)	8

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. *(*) = Max. # of divider slots per bin.



Sturdy backstop tab allows drawer to tip out for complete access.



Dividers available to keep contents neatly separated in drawers.




Wide front handle for easy gripping when AkroDrawers contain heavy contents.



Shelving Systems, Carts & Cabinets

For **AkroDrawers**®



MA4824P1



MA3618B1

Small Louvered Cart 37" L x 18" W x 36" H			Capacity/Qty.	
Model No.	Description	Cart Color	Wt. Capacity (lbs.)	Qty. of Drawers
MA3618C MA3618B MA3618P	Small Louvered Cart with no AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	-
MA3618C1 MA3618B1 MA3618P1	Small Louvered Cart with 31118 AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	6
MA3618CAST MA3618BAST MA3618PAST	Small Louvered Cart with 31168 & 31188 AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	12 / 4


Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray or Black Cart. Blue or Crystal Clear available with Putty Cart. Only one color per unit.

UP TO
800
LBS.

Large Louvered Cart 49" L x 24" W x 37½" H			Capacity/Qty.	
Model No.	Description	Cart Color	Wt. Capacity (lbs.)	Qty. of Drawers
MA4824C MA4824B MA4824P	Large Louvered Cart with no AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	-
MA4824C1 MA4824B1 MA4824P1	Large Louvered Cart with 31142 & 31162 AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	22 / 16
MA4824C2 MA4824B2 MA4824P2	Large Louvered Cart with 31142 & 31182 AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	22 / 10
MA4824C3 MA4824B3 MA4824P3	Large Louvered Cart with 31112 AkroDrawers	Textured Charcoal Gray Textured Black Textured Putty	800	16

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray or Black Cart. Blue or Crystal Clear available with Putty Cart. Only one color per unit.

UP TO
800
LBS.



AD3511C82,
AD3517C68,
AD3517BSC

Stackable Cabinet 35" W x 11" D x 22" H			Bin Dimensions (In.)			Shelf Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	D	L	H	
AD3511C AD3511P	Stackable Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	34	4-11/16	-
AD3511CAST2 AD3511PAST2	Stackable Cabinet with 31112 & 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	11-1/8*	4-5/8	11	34	4-11/16	8 / 8
AD3511C62 AD3511P62	Stackable Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	5-9/16	4-5/8	11	34	4-11/16	24
AD3511C82 AD3511P82	Stackable Cabinet with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	8-3/8	4-5/8	11	34	4-11/16	16

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit. *Width of 31112 bin.

UP TO
120
LBS.

Stackable Cabinet 35" W x 17" D x 22" H			Bin Dimensions (In.)			Shelf Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	D	L	H	
AD3517C AD3517P	Stackable Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	17	34	4-11/16	-
AD3517CAST2 AD3517PAST2	Stackable Cabinet with 31118 & 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17-5/8	11-1/8*	4-5/8	17	34	4-11/16	8 / 8
AD3517C68 AD3517P68	Stackable Cabinet with 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17-5/8	5-9/16	4-5/8	17	34	4-11/16	24
AD3517C88 AD3517P88	Stackable Cabinet with 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	17-5/8	8-3/8	4-5/8	17	34	4-11/16	16
AD3517CAST AD3517PAST	Stackable Cabinet with 31168 & 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			17	34	4-11/16	12 / 8

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit. *Width of 31118 bin.

UP TO
120
LBS.

Optional Base Stands for Stackable Cabinets			Dimensions (In.)		
Model No.	Description	Base Stand Color	W	D	H
AD3511BSC AD3511BSP	Base Stand for 11" Stackable Cabinet	Textured Charcoal Gray Textured Putty	35-1/4	11-1/4	8
AD3517BSC AD3517BSP	Base Stand for 17" Stackable Cabinet	Textured Charcoal Gray Textured Putty	35-1/4	17-1/4	8



AD3517BSC

Shelving Systems, Carts & Cabinets

For **AkroDrawers**®



Quick-View Mini-Cabinet 19¼" W x 13¼" D x 38" H			Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	
ACQV4C ACQV4P	Secure Mini-Cabinet, Quick-View Door, no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	-
ACQV4C42 ACQV4P42	Secure Mini-Cabinet, Quick-View Door with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	3-3/4	4-5/8	16
ACQV4C62 ACQV4P62	Secure Mini-Cabinet, Quick-View Door with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	5-9/16	4-5/8	12
ACQV4C82 ACQV4P82	Secure Mini-Cabinet, Quick-View Door with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	8-3/8	4-5/8	8
ACQV4CAST ACQV4PAST	Secure Mini-Cabinet, Quick-View Door with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			4 / 6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit.

UP TO
350
LBS.



ACQV4P62

Steel Door Mini-Cabinet 19¼" W x 13¼" D x 38" H			Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	
ACS4C ACS4P	Secure Mini-Cabinet, Steel Door, no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	-
ACS4C42 ACS4P42	Secure Mini-Cabinet, Steel Door with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	3-3/4	4-5/8	16
ACS4C62 ACS4P62	Secure Mini-Cabinet, Steel Door with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	5-9/16	4-5/8	12
ACS4C82 ACS4P82	Secure Mini-Cabinet, Steel Door with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	8-3/8	4-5/8	8
ACS4CAST ACS4PAST	Secure Mini-Cabinet, Steel Door with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			4 / 6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit.

UP TO
350
LBS.




ACS4CAST

Super Modular Cabinets 18" W x 11" D x 16½" H			Bin Dimensions (In.)			Shelf Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	D	L	H	
AD1811C AD1811P	Small Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	17	4-19/32	-
AD1811C62 AD1811P62	Small Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	5-9/16	4-5/8	11	17	4-19/32	9
AD1811C82 AD1811P82	Small Cabinet with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	8-3/8	4-5/8	11	17	4-19/32	6
AD1811CAST AD1811PAST	Small Cabinet with 31162 and 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	17	4-19/32	6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit.

UP TO
60
LBS.




AD1811P62

Super Modular Cabinets 18" W x 17" D x 16½" H			Bin Dimensions (In.)			Shelf Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	D	L	H	
AD1817C AD1817P	17" Deep Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	17	17	4-19/32	-
AD1817C68 AD1817P68	17" Deep Cabinet with 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17-5/8	5-9/16	4-5/8	17	17	4-19/32	9
AD1817C88 AD1817P88	17" Deep Cabinet with 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	17-5/8	8-3/8	4-5/8	17	17	4-19/32	6
AD1817CAST AD1817PAST	17" Deep Cabinet with 31168 and 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			17	17	4-19/32	6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit.

UP TO
60
LBS.




AD1817C68

Super Modular Cabinets 23" W x 11" D x 16½" H			Bin Dimensions (In.)			Shelf Dimensions (In.)			Qty. of Drawers
Model No.	Description	Cabinet Color	L	W	H	D	L	H	
AD2311C AD2311P	Medium Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	22	4-19/32	-
AD2311C62 AD2311P62	Medium Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11-5/8	5-9/16	4-5/8	11	22	4-19/32	12

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. One drawer color per unit.

UP TO
75
LBS.



AD2311C62

Shelving Systems, Carts & Cabinets


For **AkroDrawers**®



12" Enclosed Steel Shelving Systems		Bin Dimensions (In.)			Shelf Dimensions (In.)			Quantity	
Model Number	Description	L	W	H	D	L	H	Drawers	Shelves
ASC1279112	Shelving with 31112 AkroDrawers	11-5/8	11-1/8	4-5/8	12	36	79	36	13
ASC1279142	Shelving with 31142 AkroDrawers	11-5/8	3-3/4	4-5/8	12	36	79	108	13
ASC1279162	Shelving with 31162 AkroDrawers	11-5/8	5-9/16	4-5/8	12	36	79	72	13
ASC1279182	Shelving with 31182 AkroDrawers	11-5/8	8-3/8	4-5/8	12	36	79	48	13
ASC1279AST	Shelving with 31142, 31162, 31182 AkroDrawers	See Above			12	36	79	30 / 36 / 12 ‡	13

Drawer color code: R=Red, B=Blue, Y=Yellow, GR=Gray, CR=Clear. Specify drawer color when ordering. Only one color per unit. ‡Bonus drawers included.

UP TO
6000
LBS.



ASC1879118

18" Enclosed Steel Shelving Systems		Bin Dimensions (In.)			Shelf Dimensions (In.)			Quantity	
Model Number	Description	L	W	H	D	L	H	Drawers	Shelves
ASC1879118	Shelving with 31118 AkroDrawers	17-5/8	11-1/8	4-5/8	18	36	79	36	13
ASC1879148	Shelving with 31148 AkroDrawers	17-5/8	3-3/4	4-5/8	18	36	79	108	13
ASC1879168	Shelving with 31168 AkroDrawers	17-5/8	5-9/16	4-5/8	18	36	79	72	13
ASC1879188	Shelving with 31188 AkroDrawers	17-5/8	8-3/8	4-5/8	18	36	79	48	13
ASC1879AST	Shelving with 31168, 31188 AkroDrawers	See Above			18	36	79	36 / 24	13


Drawer color code: R=Red, B=Blue, Y=Yellow, GR=Gray, CR=Clear. Specify drawer color when ordering. Only one color per unit.

UP TO
6500
LBS.

12" Deep Pick Racks			Bin Dimensions (In.)			
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRS112	Single-Sided Rack with AkroDrawers	31112	11-5/8	11-1/8	4-5/8	24
APRS142	Single-Sided Rack with AkroDrawers	31142	11-5/8	3-3/4	4-5/8	72
APRS162	Single-Sided Rack with AkroDrawers	31162	11-5/8	5-9/16	4-5/8	48
APRS182	Single-Sided Rack with AkroDrawers	31182	11-5/8	8-3/8	4-5/8	32
APRSAST	Single-Sided Rack with AkroDrawer Mix	31142, 31162, 31182	See Above			18 / 24 / 8
APRD112	Double-Sided Rack with AkroDrawers	31112	11-5/8	11-1/8	4-5/8	48
APRD142	Double-Sided Rack with AkroDrawers	31142	11-5/8	3-3/4	4-5/8	144
APRD162	Double-Sided Rack with AkroDrawers	31162	11-5/8	5-9/16	4-5/8	96
APRD182	Double-Sided Rack with AkroDrawers	31182	11-5/8	8-3/8	4-5/8	64
APRDAST	Double-Sided Rack with AkroDrawer Mix	31142, 31162, 31182	See Above			36 / 48 / 16


Drawer color code: R=Red, B=Blue, Y=Yellow, GR=Gray, CR=Clear. Specify drawer color when ordering. Only one color per unit.

UP TO
400
LBS.



APRD142

UP TO
800
LBS.



APRS18188

18" Deep Pick Racks			Bin Dimensions (In.)			
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRS18148	Single-Sided Rack with AkroDrawers	31148	17-5/8	3-3/4	4-5/8	72
APRS18168	Single-Sided Rack with AkroDrawers	31168	17-5/8	5-9/16	4-5/8	48
APRS18188	Single-Sided Rack with AkroDrawers	31188	17-5/8	8-3/8	4-5/8	32
APRS18118	Single-Sided Rack with AkroDrawers	31118	17-5/8	11-1/8	4-5/8	24
APRD18148	Double-Sided Rack with AkroDrawers	31148	17-5/8	3-3/4	4-5/8	144
APRD18168	Double-Sided Rack with AkroDrawers	31168	17-5/8	5-9/16	4-5/8	96
APRD18188	Double-Sided Rack with AkroDrawers	31188	17-5/8	8-3/8	4-5/8	64
APRD18118	Double-Sided Rack with AkroDrawers	31118	17-5/8	11-1/8	4-5/8	48

Drawer color code: R=Red, B=Blue, Y=Yellow, GR=Gray, CR=Clear. Specify drawer color when ordering. Only one color per unit.

UP TO
900
LBS.

UP TO
1800
LBS.



akro-mils.com

1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
In Canada: Ak-West, Inc. • Tel: 877.979.8940 • Fax: 403.225.1696 • sales@ak-westinc.com • ak-westinc.com