

PORTABLE WET & DRY VACUUMS

Portable vacuums are designed to provide excellent cleaning maintenance where portability and versatility is required. For moderate frequency use in general purpose applications.

- Compact and lightweight
- High performance, single-stage (wet/dry pick up) motors
- On-board tool storage
- Durable plastic tank with top carry handle



784HV0

2.5, 4 & 5 Gallon Plastic Tank Vacuums

Includes:

- No. 784HV0 features 4 ft. x 1.25 in. diameter hose, reusable cloth filter, foam filter sleeve, disposable filter bag and deluxe 2-piece 1.25 in. diameter tool set.
- No. 784HV4 features 8 ft. x 1.50 in. diameter Lock-On® hose, small standard cartridge filter, high efficiency disposable filter bag, small foam filter sleeve, deluxe 8-piece 1.50 in. diameter tool set, integral wide stance caster system and convertible blower port with diffuser accessory.
- No. 784HV1 features 8 ft. x 1.50 in. diameter Lock-On® hose, small standard cartridge filter, high efficiency disposable filter bag, small foam filter sleeve and deluxe 3-piece 1.50 in. diameter tool set.



784HV4



784HV1

ITEM NO.	TANK SIZE (Gal.)*	TANK TYPE	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS‡	POWER CORD LENGTH (Ft.)
2.5, 4 & 5 Gallon Plastic Tanks								
784HV0	2.5	Plastic	2.5	8	60	53	120	12
784HV4	4	Plastic	5.5	11.6	105	68	265	20
784HV1	5	Plastic	6	11.8	90	50	180	20
Filters and Bags								
784HX5	Reusable cloth filter for 784HV0							
784HW7	Small cartridge filter for 784HV4 & 784HV1							
784HZ3	Small foam filter sleeve for 784HV4 & 784HV1							
784HZ1	High efficiency disposable filter bag for 784HV4							
784HY6	High efficiency disposable filter bag for 784HV1							
784HZ4	Foam filter sleeve for 784HV0							

CONTRACTOR WET/DRY VACUUMS

Contractor grade high airflow wet/dry vacuums are designed for moderate frequency use in general purpose applications.

- Lock-On® hoses
- Ultra Web® cartridge filter, high efficiency disposable filter bag and foam filter sleeve
- Powerful single-stage motors
- Convertible blower port with diffuser
- Integral wide stance caster system
- Swiveling casters provides ease of movement in any direction
- Durable plastic and stainless steel tanks
- On-board tool storage

6, 10, 12 & 18 Gallon Plastic Tank Vacuums

Includes:

- No. 784HV2 features large rear tool storage and 6-piece 1.25 in. diameter tool set.
- Nos. 784HV3, 784HV5 & 784HV6 feature deluxe 7-piece 1.50 in. diameter tool set.
- Nos. 784HV3, 784HV5 & 784HV6 feature large rear tool basket.
- Nos. 784HV3, 784HV5 & 784HV6 feature a tank drain.



784HV2



784HV3



784HV5



784HV6

ITEM NO.	TANK SIZE (Gal.)*	TANK TYPE	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS‡	POWER CORD LENGTH (Ft.)
6, 10, 12 & 18 Gallon Plastic Tanks								
784HV2	6	Plastic	3.5	8.1	85	55	150	12
784HV3	10	Plastic	4.5	9.7	95	55	175	20
784HV5	12	Plastic	5.5	11.6	105	70	325	20
784HV6	18	Plastic	6.5	12	110	72	335	20
Filters and Bags								
784HX2	Ultra Web® cartridge filter for 784HV2, 784HV3, 784HV5 & 784HV6							
784HY6	High efficiency disposable filter bag for 784HV2							
784HY7	High efficiency disposable filter bag for 784HV3 & 784HV5							
784HY8	High efficiency disposable filter bag for 784HV6							
784HZ4	Foam filter sleeve for 784HV2, 784HV3, 784HV5 & 784HV6							

12 & 16 Gallon Stainless Steel Tank Vacuums



784HV7



784HV8

Includes:

- 12 ft. x 1.50 in. diameter Lock-On® hose, Ultra Web® cartridge filter, high efficiency disposable filter bag, foam filter sleeve and tank drain.
- Nos. 784HV7 features large rear wheel dolly, metal transport handle and deluxe 7-piece 1.50 in. diameter tool set.
- No. 784HV8 features large rear wheel dolly, metal transport handle and deluxe metal 6-piece 1.50 in. diameter tool set.

ITEM NO.	TANK SIZE (Gal.)*	TANK TYPE	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS*‡	POWER CORD LENGTH (Ft.)
12 & 16 Gallon Stainless Steel Tanks								
784HV7	12	SS	6.5	12	105	72	325	20
784HV8	16	SS	6.5	12	110	72	335	20
Filters and Bags								
784HX2	Ultra Web® cartridge filter for 784HV7 & 784HV8							
784HY7	High efficiency disposable filter bag for 784HV7							
784HY8	High efficiency disposable filter bag for 784HV8							
784HZ4	Foam filter sleeve for 784HV7 & 784HV8							

COMMERCIAL/INDUSTRIAL WET/DRY VACUUMS

Commercial/Industrial wet/dry vacuums are designed for high frequency use in heavy duty and Jan-San applications.

- Quiet operation motor housing
- Greater suction for liquids and heavier particles
- On-board tool storage
- Tank drains (on 10 gallon and larger tanks)

8, 10 and 16 Gallon Plastic Tank Vacuums

Includes:

- Nos. 784HW0 & 784HW1 feature 8 ft. x 1.50 in. diameter Lock-On® hose, standard cartridge filter, high efficiency disposable filter bag, foam filter sleeve and deluxe 8-piece 1.50 in. diameter tool set.
- No. 784HV9 features powerful 2-stage bypass motor, 12 ft. x 1.50 in. diameter Lock-On® hose, Ultra Web® cartridge filter & high efficiency disposable filter bag, foam filter sleeve, large rear wheel dolly, metal transport handle and deluxe 7-piece 1.50 in. diameter tool set.



784HW0



784HW1



784HV9

ITEM NO.	TANK SIZE (Gal.)*	TANK TYPE	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS‡	POWER CORD LENGTH (Ft.)
8, 10 & 16 Gallon Plastic Tanks								
784HW0	8	Plastic	6	9.5	100	60	225	20
784HW1	10	Plastic	6	9.5	100	60	225	20
784HV9	16	Plastic	3	11.5	80	85	225	35
Filters and Bags								
784HW8	Cartridge filter for 784HW0 & 784HW1							
784HX2	Ultra Web® Cartridge filter for 784HV9							
784HY6	High efficiency disposable filter bag for 784HW0							
784HY7	High efficiency disposable filter bag for 784HW1							
784HY8	High efficiency disposable filter bag for 784HV9							
784HZ4	Foam filter sleeve for 784HV9, 784HW0 & 784HW1							



784HW2

Industrial 55 Gallon Wet/Dry Drum

Includes:

- 12 ft. x 1.50 in. diameter crush resistant hose and convertible blower port.
- Ultra Web® cartridge filter.
- 4-Wheel heavy-duty dolly.
- Powerful 2-stage bypass motor.
- Deluxe 2-piece 1.50 in. diameter tool set.

ITEM NO.	TANK SIZE (Gal.)*	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS‡	POWER CORD LENGTH (Ft.)
Industrial 55 Gallon Wet/Dry Drum							
784HW2	55	3.0	11	80	95	230	35
Filters and Bags							
784HX2	Ultra Web® cartridge filter for 784HW2						



784HW3

Industrial Wet/Dry Vacuum Drum Head

Includes:

- Durable metal housing for heavy-duty use.
- Mount on 55 gallon full removable head (FRH) drum with three lid latches.
- Ultra Web® cartridge filter.
- 12 ft. x 1.50 in. diameter crush resistant hose and convertible blower port.
- Deluxe 2-piece 1.50 in. diameter tool set.
- Powerful 2-stage bypass motor.

ITEM NO.	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS‡	POWER CORD LENGTH (Ft.)
Industrial Wet/Dry Vacuum Head						
784HW3	3.0	11	80	95	230	35
Filters and Bags						
784HX2	Ultra Web® cartridge filter for 784HW3					

SPECIALTY VACUUMS

Specialty Pump Vac with built in water pump moves large quantities of water by picking it up and then pumping it to another location.



784HW4

18 Gallon Pump Vac

Includes:

- Powerful single-stage motor.
- 8 ft. x 2.50 in. diameter hose.
- Deluxe 9-piece 2.50 in. diameter tool set.
- Cartridge filter, disposable filter bag and foam filter sleeve.
- Convertible blower port with diffuser.
- On-board tool storage.

ITEM NO.	TANK SIZE (Gal.)*	TANK TYPE	PEAK HP†	AMPS @120V	CFM AIR FLOW‡	STATIC PRESSURE (In.)‡	AIR WATTS‡	POWER CORD LENGTH (Ft.)
18 Gallon Pump Vacuum								
784HW4	18	Plastic	6.0	11.8	130	50	235	20
Filters and Bags								
784HW8	Cartridge filter for 784HW4							
784HZ4	Foam sleeve for 784HW4							
784HY5	Disposable filter bag for 784HW4							



DRY & WET/DRY VACUUM FILTERS AND ACCESSORIES

Cartridge Filters



784HW8

Standard Cartridge Filter

Large size filter, standard filtration type, for shop vacuums. Fits vacuum Item Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HW2, 784HW3, 784HV2. Replaces filter Item No. 2W435.



784HW7

Standard Cartridge Filter

Small size filter, standard filtration type, for shop vacuums. Fits vacuum Item Nos. 784HV4, 784HV1. Replaces filter Item No. 4TB95.



784HX2

Ultra Web[®] Cartridge Filter

Large size filter, high efficiency filtration type, for shop vacuums. Fits vacuum Item Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HW2, 784HW3, 784HV2. Replaces filter Item No. 45UZ58.



784HX1

Ultra Web[®] Cartridge Filter

Small size filter, high efficiency filtration type, for shop vacuums Nos. 784HV4, 784HV1. Replaces filter Item No. 55EY33.



784HX0

HEPA Cartridge Filter

Large size filter, HEPA filtration type, for shop vacuums. Up to 99.97% efficient on particle sizes as small as 0.3 microns. Fits vacuum Item Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HW2, 784HW3, 784HV2. Replaces filter Item No. 4TB93.



784HW9

HEPA Cartridge Filter

Small size filter, HEPA filtration type, for shop vacuums. Up to 99.97% efficient on particle sizes as small as 0.3 microns. Fits vacuum Item Nos. 784HV4, 784HV1. Replaces filter Item No. 6AKY8.



784HX4

High Efficiency Cartridge Filter

Large size filter, high efficiency filtration type, for shop vacuums. Fits vacuum Item Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HW2, 784HW3, 784HV2.



784HX3

Fits Ridgid[®] Vacuum Brand

Large size filter, standard filtration type, for shop vacuums.

Reusable and Foam Filters



784HX5

Reusable Filter

Disc filter, cloth, standard filtration type, for shop vacuum. Fits vacuum Item Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HV2. Replaces filter Item No. 6H008.



784HX6

Super Performance Cloth Filter

Made from durable Dacron material. Perfect for pick up of larger debris and dry materials. Fits vacuum Item Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HV2.



784HZ4

Foam Filter

Foam filter sleeve, for wet pick up. Fits vacuums Nos. 784HW0, 784HW1, 784HV0, 784HV9, 784HW4, 784HV3, 784HV5, 784HV6, 784HV7, 784HV8, 784HV2. Replaces filter Item No. 5X879.



784HZ3

Small Foam Filter

Foam filter sleeve, for wet pick up. Fits vacuum Item Nos. 784HV4 & 784HV1.

Disposable Filter Bags



Standard Filtration

- Easy to use and install.
- Use for everyday pick up needs of general dirt and debris.
- Dry filtration only.

ITEM NO.	BAGS/ PKG.	PRODUCT DESCRIPTION
Standard Bag Filtration Type		
784HZ2	3	Replaces filter bag Item No. 48UH45
784HY3	3	Fits vacuum Item Nos. 784HV1, 784HW0 & 784HV2 Replaces filter bag Item No. 55EY35
784HY4	3	Fits vacuum Item Nos. 784HW1, 784HV3, 784HV5 & 784HV7 Replaces filter bag Item No. 55EY36
784HY5	3	Fits vacuum Item Nos. 784HV9, 784HW4, 784HV6 & 784HV8 Replaces filter bag Item No. 48UH45
784HY9	3	Replaces filter bag Item No. 13JO22
784HZ0	3	Replaces filter bag Item No. 13JO23



High Efficiency Filtration

- Improve air quality in fine dust applications.
- Durable 2-ply construction with micro inner liner.
- Dry filtration only.

ITEM NO.	BAGS/ PKG.	PRODUCT DESCRIPTION
High Efficiency Bag Filtration Type		
784HZ1	2	Fits vacuum Item No. 784HV4
784HY6	2	Fits vacuum Item Nos. 784HV1, 784HW0 & 784HV2 Replaces filter bag Item No. 3UP65
784HY7	2	Fits vacuum Item Nos. 784HW1, 784HV3, 784HV5 & 784HV7 Replaces filter bag Item No. 3UP66
784HY8	2	Fits vacuum Item Nos. 784HV9, 784HW4, 784HV6 & 784HV8 Replaces filter bag Item No. 1UG85



784HX7 / 784HX8



784HX9 / 784HY0



784HY1 / 784HY2

Tear Resistant Standard Bag

- Made of durable material with plastic mounting collars to resist tears.
- Built-in collar handle to facilitate full bag removal.
- Cap to plug bag intake to reduce dust escape while changing.
- Three types: Standard, Wet/Dry & HEPA.



ITEM NO.	BAGS/ PKG.	PRODUCT DESCRIPTION
----------	------------	---------------------

Tear Resistant Collection Filter Bag Type		
784HX7	2	Tear Resistant Standard Collection Bag fits vacuum Nos. 784HV1, 784HW0, 784HW1, 784HV3 & 784HV2 Replaces filter bag Item No. 45UZ59
784HX8	2	Tear Resistant Standard Collection Bag fits vacuum Nos. 784HV9, 784HW4, 784HV5, 784HV6, 784HV7 & 784HV8 Replaces filter bag Item No. 45UZ60
784HX9	2	Tear Resistant Wet/Dry Collection Bag fits vacuum Nos. 784HV1, 784HW0, 784HW1, 784HV3 & 784HV2 Replaces filter bag Item No. 45UZ61
784HY0	2	Tear Resistant Wet/Dry Collection Bag fits vacuum Nos. 784HV9, 784HW4, 784HV5, 784HV6, 784HV7 & 784HV8 Replaces filter bag Item No. 45UZ62
784HY1	2	Tear Resistant HEPA Collection Bag fits vacuum Nos. 784HV1, 784HW0, 784HW1, 784HV3 & 784HV2 Replaces filter bag Item No. 45UZ63
784HY2	2	Tear Resistant HEPA Collection Bag fits vacuum Nos. 784HV9, 784HW4, 784HV5, 784HV6, 784HV7 & 784HV8 Replaces filter bag Item No. 45UZ64

Accessory Tools

For wet/dry vacuums with hose systems



784J02

Round Brush w/ Adapter

Fits 1.50 in. diameter hose, plastic, 3.0 in. diameter brush head.



784J05

Hose Handle Grip

Fits 2.50 in. diameter hose, for a comfortable hand grip while vacuuming.



784J03

Crevice Tool w/ Adapter

Fits 1.50 in. diameter hose, plastic, gets hard-to-reach places.



784J01

2-Piece Extension Wands

Fits 1.50 in. diameter hose, plastic, provides longer reach when cleaning.



784J07

Vacuum Hose Adapter

Use to adapt virtually any tool to work with all Shop-Vac[®] Brand wet/dry vacs.



784J06

Micro Cleaning Kit

The perfect way to clean your audio/video equipment and vehicles. The kit includes mini versions of our straight wand, curved wand, crevice tool, round brush, oval brush, and reduction nozzle.

Vacuum Hoses



784HZ6



784HZ8



784HZ5



784HZ7



784HZ9

Standard Hose with Hose Ends

- 8 ft. long, plastic, black.

ITEM NO.	PRODUCT DESCRIPTION
Standard Hose with Hose Ends	
784HZ6	1.25 in. diameter hose, fits standard and locking inlets
784HZ8	1.50 in. diameter hose, fits standard and locking inlets
784HZ5	2.50 in. diameter hose, fits standard and locking inlets

Standard Hose with Hose Ends

- 12 ft. long, plastic, black.

ITEM NO.	PRODUCT DESCRIPTION
Standard Hose with Hose Ends	
784HZ7	1.50 in. diameter hose, fits standard and locking inlets

Premium Crush-Resistant Vacuum Hose

- 12 ft. long, plastic, black & red.

ITEM NO.	PRODUCT DESCRIPTION
Premium Crush-Resistant Vacuum Hose	
784HZ9	1.50 in. diameter hose, fits standard and locking inlets



All specifications contained within are subject to change.

† “Peak Horsepower” (PHP) is a term used in the wet-dry vacuum industry for consumer comparison purposes. It does not denote the operational horsepower of a wet-dry vacuum, but rather the horsepower output of a motor, including the motor’s inertial contribution, achieved in laboratory testing. In actual use, wet dry vacuum motors do not operate at the peak horsepower shown.

* Tank capacity refers to actual tank volume, and does not reflect capacity available during operation.

‡ Tested to ASTM standard with same hose length & diameter supplied with vacuum.