

One-Piece, Food Grade Shovels

Hygiene | Sanitation | Safety



Whether it's scooping food material from conveyors to tubs or picking up large loads, Remco Products has the shovels to do the job. As part of a comprehensive line of hygienic material handling tools, Remco and Vikan shovels are designed to minimize the risk of cross-contamination in food processing. Remco shovels' one-piece construction helps eliminate areas for bacteria to hide and multiply. Available in a vast array of colors, Remco and Vikan shovels support color-coding programs and hygienic sanitary and safety procedures throughout food processing facilities.

Remco™ Shovels for Material Handling.



Remco one-piece shovels are made from FDA-compliant injection-molded polypropylene providing safe material handling in wet or dry food processing. These hygienic shovels are often used with conveyors or tubs. The shovels are easy to use, easy to clean, autoclavable, and non-sparking. The dual grip shovel features a textured surface on the shaft for improved grip.



REMCO

One-Piece Shovel w/10" Blade - 6981x



Colors Available:	1 2 3 4 5 6 7 8 9		
Length:	Width:	Height:	
37.5"	10.2"	5.9"	
Weight:	2.60 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene		



Pink Green Blue Red White Yellow Orange Purple Black



REMCO

One-Piece Shovel w/14" Blade - 6982x



Colors Available:	1 2 3 4 5 6 7 8 9		
Length:	Width:	Height:	
42.5"	13.75"	6.6"	
Weight:	3.56 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene		



Pink Green Blue Red White Yellow Orange Purple Black



REMCO

One-Piece Dual Grip Shovel w/14" Blade - 6984x



Colors Available:	2 3 4 5 6		
Length:	Width:	Height:	
47.5"	13.6"	6.25"	
Weight:	4.84 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene		



Green Blue Red White Yellow

Denotes product is made of FDA compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

Vikan™ Shovels for Material Handling.



Vikan shovels are made from FDA-compliant polypropylene providing safe material handling in wet or dry food processing. The shovels are easy to use, easy to clean, and are autoclavable. The small and large blade Ergonomic Shovel utilize an aluminum rod within the handle to provide enhanced durability.



Ergonomic Shovel - Large Blade - 5601x



Colors Available:	2 3 4 5 6	
Length:	Width:	Height:
51.2"	13.5"	9.8"
Weight:	4.05 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene / Aluminum	



Green Blue Red White Yellow



Ergonomic Shovel - Small Blade - 5611x



Colors Available:	2 3 4 5 6	
Length:	Width:	Height:
50.0"	10.7"	8.1"
Weight:	3.39 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene / Aluminum	



Green Blue Red White Yellow



Ergonomic Shovel - D-Grip Handle w/ Small Blade - 56125



Colors Available:	White	
Length:	Width:	Height:
63.8"	10.75"	7.5"
Weight:	4.03 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	



White

Denotes product is made of FDA compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

Vikan™ Sieve Shovel, Hygienic Fork, and Rake

The Vikan Sieve Shovel employs holes that enable liquids to drain quickly from food products. The Vikan Hygienic Fork and Hygienic Rake are mostly used to empty out fresh produce from large containers, e.g. during grape harvest for wine making. The rake is designed to attach to any Vikan or Remco handle, including telescopic handles.



Ergonomic Shovel - Large Sieve - 56045



Colors Available:	White	
Length:	Width:	Height:
44.9"	13.7"	8.3"
Weight:	3.44 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	



White



Hygienic Fork - 56905



Colors Available:	White	
Length:	Width:	Height:
63.8"	10.75"	7.5"
Weight:	4.03 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	



White



Hygienic Rake - 56915



Colors Available:	White	
Length:	Width:	Height:
7.9"	8.0"	8.9"
Weight:	0.91 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	




White

For more information regarding Vikan or Remco shovels, fork, rakes or handles, call **317.876.9856**, email cs@remcoproducts.com or visit remcoproducts.com.

 Denotes product is made of FDA compliant materials.

 Denotes product is autoclavable to 250°F.

 Denotes product is dishwasher safe to 176°F.

Remco Products Corporation

4735 West 106th Street | P.O. Box 698
Zionsville, Indiana 46077

PHONE: 317.876.9856 | FAX: 800.585.8619

www.remcoproducts.com

REMCO

