



SPC Sorbents



MRO Plus™ Pads & Rolls

- Strong and durable 3 ply dimpled gray absorbent for all industrial liquids (water, petroleum, and chemical based fluids)
- Perforated to help you use only what you need - reduces waste



Re-Form™ Pads

- Universal sorbent made from recycled newsprint and cellulose
- Quick clean up for basic drips and spills
- Netted construction adds durability

Part No.	Description	Qty
MRO100	15" x 19" Heavy Weight Pad	100
MRO300	15" x 19" Medium Weight Pad	100
MRO15DP	15" x 150' Heavy Weight Roll, perfed every 9"	1
MRO30DP	30" x 150' Heavy Weight Roll, perfed every 15"	1

Part No.	Description	Qty
RF100	15" x 19" Heavy Weight	100
RF300	15" x 19" Medium Weight	100
RF500	15" x 19" Light Weight	100



ENV Oil Only Pads & Rolls

- Oil only sorbent equally effective on land or water
- Repels water & floats indefinitely - even when saturated
- 1 ply, white, economy pads



Re-Form™ Plus Pads & Rolls

- Universal sorbent made from recycled newsprint and cellulose
- For drips, spills and wiping applications
- Spunbound/Perforated coverstock on 1 side withstands foot traffic

Part No.	Description	Qty
ENV100	15" x 19" Medium Weight	100
ENV500	15" x 19" Light Weight	100
ENV150	30" x 150' Heavy Weight Roll	1

Part No.	Description	Qty
RFP100	15" x 19" Heavy Weight	100
RFP300	15" x 19" Medium Weight	100
RFP500	15" x 19" Light Weight	100
RFP28DP	28.5" x 150' Heavy Weight Double Perfd.	1
RFP14P	14.25" x 150' Heavy Weight	1
RFP314P	28.5" x 150' Medium Weight Double Perfd.	1
RFP328DP	14.25" x 150' Medium Weight	1



BattleMat™ Rolls

- Tough construction and camouflage patterned are ideal as walk-on mats
- 3 ply, gray, camouflage roll
- Perfed up the center
- For use with oil and water-based fluids



High Traffic™ Rolls

- Durability and high absorbency and ideal for busy problem areas.
- 3 ply, gray, heavy-weight, high traffic
- Perfed every 15" and up the center

Part No.	Description	Qty
BM15	15" x 150', perfed every 9"	1
BM30	30" x 150', perfed every 15"	1

Part No.	Description	Qty
HT30	30" x 150' Heavy Weight Roll, perfed every 15"	1



Slikwik® SOC

- Dependable, flexible tubes that contain and absorb liquids
- Molds around corners and conforms to uneven surfaces

Part No.	Size	Qty
SW46	3" x 42"	40



Multiwik™ SOC

- Multi-purpose SOC filled with universal polypropylene for non aggressive liquids

Part No.	Size	Qty
MS50	3"x4'	40



Allwik™ SOC

- All-purpose maint. SOC
- Moderate chemical resistance
- Can be wrung or incinerated

Part No.	Size	Qty
AW430	3"x4'	30
AW412	3"x4'	12
AW806	3" x 8'	6



Oil Only SOC

- For oil & petroleum based spills
- Will not absorb water or water-based solutions
- Wringable and incinerable

Part No.	Size	Qty
OIL430	3" x 4'	30
OIL412	3" x 4'	12
OIL806	3" x 8'	6
OIL124	3" x 12'	4

20 Gallon Lab Pack

- UN approved, water and chemical resistant polyethylene lab pack
- Absorbs up to 15 gallons
- Contents:
 - 12 pads (15" x 19") - Goggles
 - 3 SOC's (3" x 12") - Nitrile gloves
 - 3 disposable bags - Emergency response handbook



Part No.	Description	Qty
SKO-20	Oil Only 20 Gallon Spill Kit	1
SKA-20	Allwik™ 20 Gallon Spill Kit	1

Attack Pac™ Spill Kit

- Packed in puncture and UV resistant foil bag
- Absorbs up to 7 gallons per kit
- Contents:
 - 1 disposable bag
 - 15 pads (15" x 19") - Goggles
 - 2 SOC's (3" x 4") - Nitrile gloves



Part No.	Description	Qty
SKA-ATK	Universal Attack Pac Spill Kit	4

95 Gallon Lab Pack

- Tough, secure and highly visible
- Container has screw top lid
- Meets UN and DOT specifications
- Absorbs up to 75 gallons
- Contents:
 - 110 pads (15" x 19") - 10 disposable bags
 - 12 SOC's (3" x 4") - Goggles
 - 8 SOCS (3" x 12") - Nitrile gloves
 - 8 pillows (18" x 18") - Emergency response handbook



Part No.	Description	Qty
SKO-95	Oil Only 95 Gallon Spill Kit	1

Economy Spill Kit

- Highly visible yellow PVC bag
- Absorbs up to 5 gallons
- Contents:
 - 10 pads (15" x 19") - 1 disposable bag
 - 2 SOC's (3" x 4") - Nitrile gloves



Part No.	Description	Qty
SKA-PP	Allwik™ Economy Spill Kit	1
SKO-PP	Oil Only Economy Spill Kit	1
SKH-PP	Hazwik™ Economy Spill Kit	1