

Omega Supreme Plus HEPA Vacuum

by **Atrix**™



VACOMEGASCT

PRODUCT HIGHLIGHTS

WARRANTY

3 Year Limited

ESD SAFE SERVICE VACUUM

HEPA Filtration and Self Storage/Contained Accessories

POWERFUL

1,000 Hour Rated Ametek Advantek II Motor

QUIET

69 Decibels

SAFE

HEPA Filtration along with ESD Safety draining damaging static voltages to ground

APPLICATIONS

Hazardous debris such as lead dust, silica dust, mold, etc. as well as for servicing and cleaning static sensitive equipment, i.e. computers, copiers, printers, data centers, ATM's, gaming, banking, robotics, telecomm



Ultrafine Vacuums Built to Last. Quality Assured.

www.atrrix.com | sales@atrrix.com | 1-800-222-6154 | Burnsville, MN, USA

Omega Supreme Plus HEPA Vac

by **Atrix™**

SPECIFICATIONS

VACOMEGASCT

DIMENSIONS

Length: 20" (508 mm)
Width: 6.25" (159 mm)
Height: 9.25" (235 mm)

WEIGHT 11.15 lbs. (5.05 kg)

HOSE DIAMETER

Inside - 1.00" (25.4 mm)
Outside - 1.25" (31.75 mm)

POWER

120, 628W

CFM

99 CFM

INCLUDED CONTENTS

- A - Omega Supreme Plus HEPA Vac by Atrix
- B - 31651-120V Detachable Power Cord
- C - 31652 - Crevice Tool Brush
- D - 31654 - ESD Safe Crevice Tool
- E - 31657 - ESD Safe Flexible Gooseneck Tool
- F - 31661 - ESD Safe 6' Stretch Hose
- G - OF612HE - HEPA Filter Cartridge
- H - 410017 - Filter Plug
- I - AVPA016 - Adjustable Shoulder Strap

FILTRATION

HEPA

99.97% Efficient at .3 Micron
1 Gallon Dry
56 Pleat, 3 Layer
One Cellulose Layer
Two Glass Layers

CERTIFICATION



GENERAL INFORMATION

PACKAGING

Dimensions: L W H
Inches: 20.25 7.75 10.75
mm: 514 197 273
Weight: 12.4 lbs.
5.62 kg

HS Code

8508.11.0000

UPC

8 38067 00063 9

OPTIONAL ACCESSORIES

Omega ULPA Filter Cartridge
OF712UL



Omega HEPA Filter Cartridge
with Static Dissipative Body -
OF912HE



HEPA CERTIFIED Omega Series
Filter Cartridge - OF612HE-IC

