

For Repair Parts, call 1-800-323-0620

24 hours a day – 365 days a year

Please provide following information:

- Model number
- Serial number (if any)
- Part description and number as shown in parts list

E
N
G
L
I
S
H




Figure 1 – Repair Parts Illustration for GEN-14000-1GHE 082710

Models 6FYA4

Repair Parts

Ref. No.	Description	Part No.	Qty.	Ref. No.	Description	Part No.	Qty.
1	Decal- Carbon Monoxide (See 34-9039)	N/A	1	32	Bolt	27-9550	1
2	Engine Assembly -Honda GX630	850-0395	1	33	Push/Pull Toggle Clamp	33-0400	1
3	Isolation Plate	5-0279A01	1	34	Locknut	30-0155	4
4	Washer	28-0022	8	35	Battery Cable Cover	33-0429	1
5	Bolt	27-0121	4	36	Battery Cable Cover	33-0004	1
6	Locknut	30-0157	26	37	Battery	32-0058	1
7	Washer	28-0003	36	38	Bolt	27-0066	2
8	Isolator	33-0028	6	39	Bolt	27-0017	2
9	Grommet	33-0001	3	40	Fuel Hose *(Three Feet Required)	15-0261	1
10	Terminal Protector	33-0508	1	41	Battery Strap	33-0430	1
11	Locknut	30-0159	4	42	Carb Canister	62-0212	1
12	Heat Shield	20-1116A01	1	43	Bolt	27-8807	1
13	Bolt	27-0015	6	44	Carb Canister Strap	20-1187A01	2
14	Lockwasher	29-0006	2	45	External Lockwasher	28-1009	4
15	Washer	28-0002	12	46	Nut	30-6001	3
16	Lockwasher	29-0112	1	47	Decal- Ground Pictoral (See 34-9039)	N/A	1
17	Washer	28-0005	2	48	Decal- Warning Explosion (See 34-9039)	N/A	1
18	Locknut	30-0161	1	49	Electric Box Assembly	N/A Sep	1
19	Gas Tank Assembly	856-0019	1	50	Side Panel	20-1117A01	2
20	Bolt	27-9527	10	51	Decal - Marketing	34-2545	2
21	Clamp Worm	42-0004	3	52	Bolt	27-3062	8
22	Fuel Hose *(Five Feet Required)	15-0008	1	53	Frame	5-0269A01	1
23	Isolation Plate	5-0280A01	1	54	Bolt	27-8878	4
24	Bolt	27-0168	1	55	Decal - Grainger 800# Large	34-1444	1
25	Lockwasher	29-0110	1	56	Alternator	32-0886	1
26	Axle	5-0278A01	2	57	Conduit Elbow	32-0907	1
27	Bolt	27-0067	8	58	Bolt	27-0117	4
28	Locknut	30-0117	4		Decal Set (Inc. 1, 30, 48, 49)	34-9039	1
29	Wheel	14-0006	4				
30	Decal- California Emissions	N/A	1				
31	Decal- Silver Sticker	N/A	1				

* (Must order in one foot lengths)

For Repair Parts, call 1-800-323-0620

24 hours a day – 365 days a year

Please provide following information:

- Model number
- Serial number (if any)
- Part description and number as shown in parts list




Figure 2 – Repair Parts Illustration for 850-395 082710
For additional engine repair parts (i.e. air and oil filters), consult engine owners manual.

Models 6FYA4

Repair Parts List for Engine

Ref. No.	Description	Part No.	Qty.	Ref. No.	Description	Part No.	Qty.
1	Spark Arrestor	45-0110	1	5	Drain Hose	70-0504	1
2	Fuel Hose *(Five Feet Required)	15-0261	1	6	Engine -Honda GX630	1-0188	1
3	Coupling-Barb	55-0700	1	7	Muffler	45-0162	1
4	Hose Fuel *(One Foot Required)	15-0020	1	* (Must order in one foot lengths)			


E
N
G
L
I
S
H

For Repair Parts, call 1-800-323-0620

24 hours a day – 365 days a year

Please provide following information:

- Model number
- Serial number (if any)
- Part description and number as shown in parts list



E
N
G
L
I
S
H

Figure 3 – Repair Parts Illustration for 856-0019 071410

Models 6FYA4

Repair Parts List for Gas Tank Assembly

Ref. No.	Description	Part No.	Qty.	Ref. No.	Description	Part No.	Qty.
1	Decal- Caution: Gasoline Only (See 34-9039)	N/A	1	5	Fuel Pick Up	33-0271	1
2	Fuel Cap	12-0229	1	6	Elbow	23-0054	1
3	Fuel Cap Catch	12-0228	1	7	Fuel Gauge	12-0184	1
4	Barb	23-0051	1	8	Plug	24-0009	1
				9	Fuel Tank	12-0207A01	1

For Repair Parts, call 1-800-323-0620

24 hours a day – 365 days a year

Please provide following information:

- Model number
- Serial number (if any)
- Part description and number as shown in parts list

E
N
G
L
I
S
H




Figure 4 – Repair Parts Illustration for GEN-12000-1GHE E-Box Assy

Models 6FYA4

Repair Parts List for Electric Box Assembly

Ref. No.	Description	Part No.	Qty.	Ref. No.	Description	Part No.	Qty.
1	Power Block 3-Pole	32-0905	1	20	Bolt	27-0740	2
2	Power Block Adder	32-0912	4	21	Idle Down Board	32-0896	1
3	Bolt	27-8942	4	22	Toggle Breaker SP-30A	32-0836	1
4	Electric Box	20-1114A01	1	23	Toggle Breaker SP 20A	32-0834	3
5	Toggle Breaker DP-30A	32-0837	1	24	Locknut	32-0587	1
6	Circuit Breaker Toggle DP-50A	32-0902	1	25	Strain Relief	32-0586	1
7	Locknut	30-0152	16	26	Bolt	27-0022	1
8	Electric Panel	20-1115A01	1	27	Washer	28-0002	2
9	Hour Meter	32-0668	1	28	Capacitor Clamp Bracket	20-0797A01	2
10	Lockwasher	29-1013	26	29	Capacitor	32-0846	2
11	Bolt	27-8881	12	30	Conduit Flex		
12	Rocker Switch	32-0626	1		*(Two Feet Required)	32-0908	1
13	Lockwasher	29-1009	7	31	Conduit Flex	32-0996	1
14	Receptacle L14-50	32-0904	1	32	Decal- Carbon Monoxide (See 34-9039)	N/A Sep.	1
15	Receptacle L14-30	32-0831	1	33	Decal- Operations (See 34-9039)	N/A Sep.	1
16	Receptacle L5-30	32-0832	1	34	Decal- Warning (See 34-9039)	N/A Sep.	1
17	Receptacle GFCI 20A	32-0830	2		Decal Set (Inc 19, 32, 33-34)	34-9039	1
18	Bolt	27-9574	14				
19	Decal-Control Panel (See 34-9039)	N/A Sep.	1				

For Repair Parts, call 1-800-323-0620

24 hours a day – 365 days a year

Please provide following information:

- Model number
- Serial number (if any)
- Part description and number as shown in parts list




Figure 5 – Repair Parts Illustration Wire Diagram Dayton 12KW 102510