

Features

- Comes with a welded 3/8" cap nut, allowing easy attachment to threaded rod
- Equipped with an EPDM rubber sleeve that serves to minimize noise
- Complies with the requirements of DIN 4109; average noise reduction of 20 dBA
- Conforms with Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 12)
- Fits a full range of steel pipe and copper tubing sizes from 1/4" (12 mm) through 4" (114 mm)
- Has a fire rating DIN EN 13501-1:E
- Has an operating temperature range of -58°F (-50°C) up to +230°F (110°C)



The CADDY® SUPERFIX 454 is an easy-to-close pipe clamp that works on steel and copper pipes from 1/4" (12 mm) to 4" (114 mm). A unique hinged design eliminates the need to disassemble the clamp prior to installation and allows the installer to close the pipe clamp with one hand without turning a screw. Once the pipe is installed, simply tighten the screw to secure the pipe in place.

The cleverly designed pipe clamp requires only one screw and hinge. The all steel design of the patented closing mechanism means the strength is not significantly reduced by exposure to heat.

All of the pipe clamps have a 5-8 microns electro-galvanized coating to protect against corrosion.



Part Number	Nominal Pipe Size IP	CT	Rod Size	Max. Rec. Load (lbs)
454001	1/4"	3/8"	3/8"	180
454002	3/8"	1/2"	3/8"	180
454003	-	5/8"	3/8"	180
454004	1/2"	3/4"	3/8"	180
454005	3/4"	1"	3/8"	180
454006	1"	1-1/4"	3/8"	180
454007	1-1/4"	1-1/2"	3/8"	180
454008	1-1/2"	-	3/8"	180
454009	-	2"	3/8"	180
454010	2"	-	3/8"	180
454011	-	2-1/2"	3/8"	300
454012	2-1/2"	-	3/8"	300
454013	-	3"	3/8"	300
454014	3"	-	3/8"	300
454015	-	3-1/2"	3/8"	300
454016	3-1/2"	4"	3/8"	300
454017	4"	-	3/8"	300

WARNING
 ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright ©2008 ERICO International Corporation. All rights reserved.
 CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

Phone: 800-333-0852
 Fax: 800-677-5403
www.erico.com

