



# AVIATION WHEEL CHOCKS

For use with Aviation Vehicles and Equipment

## FEATURES

- Impact-absorbing urethane
- Weather and abrasion resistant
- High load-bearing capacity
- Resistant to aircraft fuels, oils, and lubricants
- Eliminates Foreign Object Damage
- Optional anti-skid rubber pads for polished hanger floors


MONSTER® AVIATION WHEEL CHOCKS include the AC Series, made of highly durable, lightweight polyurethane. AC Chocks last longer than wood chocks, never need painting and eliminate Foreign Object Damage threats for aircraft. The AC Series is ideal for private, commercial, cargo and military aircraft.

### CUSTOMIZE YOUR CHOCKS


6800, 4600, and 3500 Series Aviation Wheel Chocks can be customized to reflect your company's unique identity with a special color or adding your logo on the chock.

- Lightweight and easy to use
- Will not rot, crack or splinter like wood
- Rope-lock system
- Optional rope carrying handle
- Molded-in high-visibility yellow color

## AC6800 SERIES - for large and oversized aircraft



**ROPE LOCK SYSTEM** The original military style chock-to-chock rope lock system allows a wheel chock to be temporarily and securely attached to the opposing wheel chock on the opposite side of the aircraft tire. This chock-locking system ensures that wheel chocks remain firmly positioned against each side of the aircraft tire during engine test procedures.



### 20 INCH MODELS

MODEL	DESCRIPTION	A: LENGTH	B: WIDTH	C: HEIGHT	LANYARD	WEIGHT	COLOR
5NHT0	Aviation Chock with 36" Locking Rope (no Rubber Pad)	20 in. (50.8 cm)	8 in. (20.3 cm)	6 in. (15.2 cm)	36 in. (91.4 cm)	13.9 lb. (6.3 kg)	Hi-Vis Yellow
A5NHT1	Aviation Chock with Rubber Pad and 36" Locking Rope	20 in. (50.8 cm)	8 in. (20.3 cm)	6 in. (15.2 cm)	36 in. (91.4 cm)	18.9 lb. (8.6 kg)	Hi-Vis Yellow

### 56 INCH MODELS

MODEL	DESCRIPTION	A: LENGTH	B: WIDTH	C: HEIGHT	LANYARD	WEIGHT	COLOR
5NHT2	Aviation Chock with Rubber Pad and 48" Locking Rope	56 in. (142.2 cm)	8 in. (20.3 cm)	6 in. (15.2 cm)	48 in. (122 cm)	43.25 lb. (19.7 kg)	Hi-Vis Yellow




5NHT2 in-use




5NHT2 in-use

## AC4600 SERIES - for mid-sized to large aircraft

LR MODEL



FOR MID-SIZE TO LARGE AIRCRAFT




MODEL	DESCRIPTION	A: LENGTH	B: WIDTH	C: HEIGHT	LANYARD	WEIGHT	COLOR
5NHR8	Aviation Chock with 36" Locking Rope (no Rubber Pad)	14 in. (35.6 cm)	6 in. (15.2 cm)	4 in. (10.2 cm)	36 in. (91.4 cm)	6.2 lb. (2.8 kg)	Hi-Vis Yellow
5NHR9	Aviation Chock with Rubber Pad and 36" Locking Rope	14 in. (35.6 cm)	6 in. (15.2 cm)	4.25 in. (10.8 cm)	36 in. (91.4 cm)	8.3 lb. (3.8 kg)	Hi-Vis Yellow

## AC3500 SERIES - for small to mid-sized aircraft

FOR SMALL TO MID-SIZED AIRCRAFT



An updated version of the original wood wheel chock design. Standard with 1/2 in. x 24 in. replaceable Polyester rope lanyard. Sold as singles or roped together in pairs.



MODEL	DESCRIPTION	A: LENGTH	B: WIDTH	C: HEIGHT	LANYARD	WEIGHT (PAIR)	COLOR
5NHR0	Pair of Aviation Chocks	12 in. (30.5 cm)	5 in. (12.7 cm)	3 in. (7.6 cm)	24 in. (61.0 cm)	6.5 lb. (2.9 kg)	Hi-Vis Yellow
5NHR1	Pair of Aviation Chock with Rubber Bases	12 in. (30.5 cm)	5 in. (12.7 cm)	3.25 in. (8.3 cm)	24 in. (61.0 cm)	8.4 lb. (3.8 kg)	Hi-Vis Yellow
5NHR2	Pair of Aviation Chocks	15 in. (38.1 cm)	5 in. (12.7 cm)	3 in. (7.6 cm)	24 in. (61.0 cm)	7.8 lb. (3.4 kg)	Hi-Vis Yellow
5NHR3	Pair of Aviation Chock with Rubber Bases	15 in. (38.1 cm)	5 in. (12.7 cm)	3.25 in. (8.3 cm)	24 in. (61.0 cm)	10.4 lb. (4.4 kg)	Hi-Vis Yellow
5NHR4	Pair of Aviation Chocks	18 in. (45.7 cm)	5 in. (12.7 cm)	3 in. (7.6 cm)	24 in. (61.0 cm)	9.2 lb. (4.2 kg)	Hi-Vis Yellow
5NHR5	Pair of Aviation Chock with Rubber Bases	18 in. (45.7 cm)	5 in. (12.7 cm)	3.25 in. (8.3 cm)	24 in. (61.0 cm)	12.0 lb. (5.6 kg)	Hi-Vis Yellow
5NHR6	Pair of Aviation Chocks	21 in. (53.3 cm)	5 in. (12.7 cm)	3 in. (7.6 cm)	24 in. (61.0 cm)	11.0 lb (5.0 kg)	Hi-Vis Yellow
5NHR7	Pair of Aviation Chock with Rubber Bases	21 in. (53.3 cm)	5 in. (12.7 cm)	3.25 in. (8.3 cm)	24 in. (61.0 cm)	15.0 lb. (6.8 kg)	Hi-Vis Yellow

\* Part numbers come in pairs. Dimensions are of individual chocks.



5NHR8 in-use



5NHR0 in-use



# AVIATION WHEEL CHOCKS


For use with Aviation Vehicles and Equipment

## FEATURES

- Impact-absorbing urethane
- Weather and abrasion resistant
- High load-bearing capacity
- Resistant to aircraft fuels, oils, and lubricants
- Eliminates Foreign Object Damage
- Optional anti-skid rubber pads for polished hanger floors



MONSTER® AVIATION WHEEL CHOCKS include the AC Series, made of highly durable, lightweight polyurethane. AC Chocks last longer than wooden chocks, never need painting and eliminate Foreign Object Damage threats for aircraft. The AC Series is ideal for business, commercial, cargo and military aircraft.

- Lightweight and easy to use
- Will not rot, crack or splinter like wood
- Rope-lock system
- Optional rope carrying handle
- Molded-in high-visibility yellow color



## AC200 SERIES - for small aircraft

Fits the curvature of the tire to absorb wheel-squat during loading and fueling operations. Features molded-in soft base for increased traction. 3/8 in. x 24 in. replaceable Polyester rope lanyard connects two chocks together. Custom rope lengths available. Sold in pairs.



MODEL	A: LENGTH	B: WIDTH	C: HEIGHT	LANYARD	WEIGHT (PAIR)	COLOR
5NHP9	5.5 in. (14.0 cm)	4.5 in. (11.4 cm)	2.75 in. (7.0 cm)	24 in. (61.0 cm)	1.5 lb. (.68 kg)	Hi-Vis Yellow



Monster 5NHTO aviation chocks used on a McDonnell Douglas F-15 Eagle