

## Cut resistance with exceptional dexterity

### **JACKSON SAFETY\* G60 Level 2 Polyurethane Coated Cut Gloves**

Add cut resistance to your workers' gloves without compromising dexterity with our **NEW JACKSON SAFETY\* G60 Level 2 Polyurethane Coated Cut Gloves**. They're a great choice for working environments that pose a risk of minor cuts and abrasions.

- ANSI/EN 388 Level 2 cut resistance
- Stretch KEVLAR® liner provides cut resistance and a comfortable fit
- Excellent dexterity for improved productivity
- Polyurethane provides a barrier against oil penetration





## Helping reduce hand injuries

### Typical Uses

- Metal fabrication
- Glass handling
- Automotive and aerospace assembly
- Stamping and assembly



Great dexterity and oil grip

ANSI/EN 388 Level 2 cut resistance

Comfortable fit

Barrier against oil penetration

Suitable for intermittent heat contact up to 212°F†



EN388  
2221

### JACKSON SAFETY\* G60 Level 2 Polyurethane Coated Cut Gloves

| Code No. | Color         | Size     | Case Count               |
|----------|---------------|----------|--------------------------|
| 38635    | Grey & Yellow | 7 (S)    | 12 pair/bag • 1 bag/case |
| 38636    | Grey & Yellow | 8 (M)    | 12 pair/bag • 1 bag/case |
| 38637    | Grey & Yellow | 9 (L)    | 12 pair/bag • 1 bag/case |
| 38638    | Grey & Yellow | 10 (XL)  | 12 pair/bag • 1 bag/case |
| 38639    | Grey & Yellow | 11 (XXL) | 12 pair/bag • 1 bag/case |

† Glove must not come into contact with a naked flame.

**Caution:** This product contains natural rubber latex, which may cause allergic reactions. This product should not be worn by, or exposed to, individuals allergic to natural rubber latex. Safe use of this product on or by latex-sensitive individuals has not been established.

### Our Guarantee

Your total satisfaction means everything to us. If, for any reason, our products do not meet your expectations, Kimberly-Clark will reimburse you† for your initial purchase, via FREE product, for up to \$1,000.

For more information on KIMBERLY-CLARK PROFESSIONAL\*, visit us online at [www.kcprofessional.com](http://www.kcprofessional.com), contact your Kimberly-Clark Sales Representative, or call us at 1-888-346-GOKC (4652).

† Guarantee extended to consuming end-user accounts only.

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers except for auto darkening filters which shall be warranted for two years from date of end user purchase (verified by valid sales receipt) and powered air purifying respirators which shall be warranted for one year from date of end user purchase (verified by valid sales receipt); (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. **THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

®/\* Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © 2012 KCWW. KEVLAR is a registered trademark of E.I. DuPont de Nemours and Company.

K02419 K0030-12-01 01/12

Effective January 2012