



500 lbs.
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20X990	DXL3810-06	6'
20X991	DXL3810-08	8'



TYPE IAA
375 lbs.
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20X992	DXL3410-04	4'
20X993	DXL3410-06	6'
20X994	DXL3410-08	8'
20X995	DXL3410-10	10'
20X996	DXL3410-12	12'



TYPE IA
300 lbs.
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20X976	DXL3010-04	4'
20X977	DXL3010-05	5'
20X978	DXL3010-06	6'
20X979	DXL3010-07	7'
20X980	DXL3010-08	8'
20X981	DXL3010-10	10'
20X982	DXL3010-12	12'



TYPE IA
300 lbs.
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20X983	DXL2010-02	2'
20X984	DXL2010-03	3'
20X985	DXL2010-04	4'
20X986	DXL2010-05	5'
20X987	DXL2010-06	6'
20X988	DXL2010-08	8'
20X989	DXL2010-10	10'



TYPE I
250 lbs.
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
36Y402	DXL3110-04	4'
36Y403	DXL3110-05	5'
36Y404	DXL3110-06	6'
36Y405	DXL3110-07	7'
36Y406	DXL3110-08	8'





TYPE IAA **375 lbs.**
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20Y005	DXL3420-16PG	16'
20Y006	DXL3420-20PG	20'
20Y007	DXL3420-24PG	24'
20Y008	DXL3420-28PG	28'
20Y009	DXL3420-32PG	32'



TYPE IA **300 lbs.**
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20X997	DXL3020-16PT	16'
20X998	DXL3020-20PT	20'
20X999	DXL3020-24PT	24'
20Y001	DXL3020-28PT	28'
20Y002	DXL3020-32PT	32'
20Y003	DXL3020-36PT	36'
20Y004	DXL3020-40PT	40'



TYPE IA **300 lbs.**
LOAD CAPACITY

ITEM NUMBER	MFR MODEL	LADDER HEIGHT
20Y010	DXL2090-17	17'
20Y011	DXL2090-22	22'

For more information contact your Grainger Representative or visit Grainger.com®.

AVAILABLE THROUGH

GRAINGER®

FOR THE ONES WHO GET IT DONE