


## DURASHELF® SHELVING & STORAGE



When you're ready to step up to the toughest, largest plastic shelving in the industry, it's time to go with DuraShelf® all-plastic industrial-grade shelving systems.

Our unique locking system lets you choose whether to build up, out or both. Our rigid high-density polyethylene panels are like nothing else you've ever seen in plastic shelving. Each panel is a stout 2-5/8" thick with a grid top that allows liquids to flow through, promotes air circulation and prevents dust build up. The entire system is chemically resistant, making it an ideal choice for HAZMAT storage or any other application, corrosive or not.

Grid Top Shelving												
2-Shelf					3-Shelf				4-Shelf			
Sizes	Part #	Desc.	Cap.	Wt.	Part #	Desc.	Cap.	Wt.	Part #	Desc.	Cap.	Wt.
36"x 16"	S3616B	27" High Shelving	340	22	S3616x3	51" High Shelving	500	35	S3616x4	75" High Shelving	675	48
36"x 24"	S3624B	27" High Shelving	500	26	S3624x3	51" High Shelving	750	41	S3624x4	75" High Shelving	1000	56
36"x 36"	S3636B	27" High Shelving	750	44	S3636x3	51" High Shelving	1125	70	S3636x4	75" High Shelving	1500	97
48"x 24"	S4824B	27" High Shelving	690	35	S4824x3	51" High Shelving	1015	57	S4824x4	75" High Shelving	1375	78
66"x 16"	S6616B	27" High Shelving	615	36	S6616x3	51" High Shelving	925	58	S6616x4	75" High Shelving	1235	80
66"x 24"	S6624B	27" High Shelving	925	40	S6624x3	51" High Shelving	1390	64	S6624x4	75" High Shelving	1850	88
66"x 36"	S6636B	27" High Shelving	1375	74	S6636x3	51" High Shelving	2065	118	S6636x4	75" High Shelving	2750	163
96"x 16"	S9616B	27" High Shelving	900	49	S9616x3	51" High Shelving	1350	78	S9616x4	75" High Shelving	1800	107
96"x 24"	S9624B	27" High Shelving	1350	65	S9624x3	51" High Shelving	2025	102	S9624x4	75" High Shelving	2700	139
96"x 36"	S9636B	27" High Shelving	2015	103	S9636x3	51" High Shelving	3025	165	S9636x4	75" High Shelving	4030	226

Solid Top Shelving												
36"x 24"	ST3624B	27" High Shelving	660	31	ST3624x3	51" High Shelving	990	49	ST3624x4	75" High Shelving	1320	67
36"x 36"	ST3636B	27" High Shelving	985	51	ST3636x3	51" High Shelving	1475	81	ST3636x4	75" High Shelving	1965	112
66"x 24"	ST6624B	27" High Shelving	1210	53	ST6624x3	51" High Shelving	1820	84	ST6624x4	75" High Shelving	2420	115
66"x 36"	ST6636B	27" High Shelving	1800	85	ST6636x3	51" High Shelving	2705	135	ST6636x4	75" High Shelving	3600	186
96"x 24"	ST9624B	27" High Shelving	1770	76	ST9624x3	51" High Shelving	2650	119	ST9624x4	75" High Shelving	3540	161
96"x 36"	ST9636B	27" High Shelving	2640	127	ST9636x3	51" High Shelving	3960	201	ST9636x4	75" High Shelving	5280	275

Published weight capacities of all products assume even distribution of materials across all panels

## CONTAINMENT TRAYS

Containment trays keep materials separated and confine spills to prevent damage to items stored on lower shelves or in adjacent compartments of the same shelf. Use one tray between each section of leg posts. Available in OSHA-designated chemical storage color coding. A perfect fit for any of our 24-inch wide shelving or Dunnage-Rack™.



24 - INCH CONTAINMENT TRAYS						
Storage Type	Part #	Color	Max Trays Per Shelf System			
			Size	x2	x3	x4
General Storage	CT300124	Black	36"	2	3	4
			66"	4	6	8
			96"	6	9	12
Flammables	CTR300124	Red				
Health Hazards/Toxics	CTB300124	Blue				
Reactives/Oxidizers	CTY300124	Yellow				
Contact Hazards	CTW300124	White				

