

Stainless Steel and Steel Worktables and Utility stands

Easily assembled worktables and utility stands feature stainless steel tops with stainless steel or heavy-duty 16-ga .galvanized legs and undershelf.

Rolled-edges on front and rear,90°turned down ends allow additional tables to be placed flush to end.600-lb.capacity,based on evenly distributed loads.

Casters are optional.

Item#	Desc	Overall Dimensions		
		Width	Length	Height
		(in)	(in)	(in)
4UEJ9	with backsplash,stainless steel leg and undershelf	30	48	34 1/2-35 1/2
4UEK1	with backsplash,stainless steel leg and undershelf	30	60	34 1/2-35 1/2
4UEK2	with backsplash,stainless steel leg and undershelf	30	72	34 1/2-35 1/2
2KRD6	with backsplash,galvanized leg and undershelf	30	48	34 1/2-35 1/2
2KRD7	with backsplash,galvanized leg and undershelf	30	72	34 1/2-35 1/2



4UEJ6	with flat top,stainless steel leg and undershelf	30	48	34 1/2-35 1/2
4UEJ7	with flat top,stainless steel leg and undershelf	30	60	34 1/2-35 1/2
4UEJ8	with flat top,stainless steel leg and undershelf	30	72	34 1/2-35 1/2
2KRD8	with flat top,galvanized leg and undershelf	30	48	34 1/2-35 1/2
4UEK4	with flat top,galvanized leg and undershelf	30	60	34 1/2-35 1/2
2KRD9	with flat top,galvanized leg and undershelf	30	72	34 1/2-35 1/2
2KRE6	with flat top,galvanized leg and undershelf	24	24	34 1/2-35 1/2
2KRE7	with flat top,galvanized leg and undershelf	24	48	34 1/2-35 1/2



2KRE8	with flat top,galvanized leg and undershelf	24	72	34 1/2-35 1/2
-------	---------------------------------------------	----	----	---------------

Item#	Desc	Overall Dimensions		
		Width	Length	Height
		(in)	(in)	(in)
2KRE3	with flat top,galvanized leg and undershelf	24	24	24-25
2KRE4	with flat top,galvanized leg and undershelf	30	30	24-25
4UEL2	with flat top,galvanized leg and undershelf	30	36	24-25



4UEJ3	with flat top,stainless steel tubular base	30	48	34 1/2-35 1/2
4UEJ4	with flat top,stainless steel tubular base	30	60	34 1/2-35 1/2
4UEJ5	with flat top,stainless steel tubular base	30	72	34 1/2-35 1/2
2KRE1	with flat top,galvanized tubular base	30	48	34 1/2-35 1/2
4UEK3	with flat top,galvanized tubular base	30	60	34 1/2-35 1/2
2KRE2	with flat top,galvanized tubular base	30	72	34 1/2-35 1/2



Enclosed Worktable

Item#	Desc	Overall Dimensions		
		Width	Length	Height
		(in)	(in)	(in)
4UEK8	with sliding doors and flat top	30	48	34 1/2-35 1/2
4UEK9	with sliding doors and flat top	30	60	34 1/2-35 1/2
4UEL1	with sliding doors and flat top	30	72	34 1/2-35 1/2



Worktables have four 33" posts.

Item#	Desc	Overall Dimensions		
		Width	Length	Height
		(in)	(in)	(in)
4UEL3	with flat top, chrome leg with 2 C frame bases	30	48	34 1/2
4UEL4	with flat top, chrome leg with 2 C frame bases	30	60	34 1/2



4UEL7	with flat top, chrome leg with 2 wire shelves	30	48	34 1/2
4UEL8	with flat top, chrome leg with 2 wire shelves	30	60	34 1/2



4UEL5	with flat top, chrome leg with 1 wire shelf and 1 C frame	30	48	34 1/2
4UEL6	with flat top, chrome leg with 1 wire shelf and 1 C frame	30	60	34 1/2



4UEL9	with flat top, chrome leg with 1 wire shelf and 1 H frame	30	48	34 1/2
4UEN1	with flat top, chrome leg with 1 wire shelf and 1 H frame	30	60	34 1/2



Worktables With Cantilevered Overhead System

Item#	Desc	Overall Dimensions		
		Width	Length	Height
		(in)	(in)	(in)
4UEK5	with flat top ,galvanized legs,undershelf and flex-master riser kit	30	48	63
4UEK6	with flat top ,galvanized legs,undershelf and flex-master riser kit	30	60	63
4UEK7	with flat top ,galvanized legs,undershelf and flex-master riser kit	30	72	63



4UEN2	with flat top, chrome leg with 2 C frame bases, with chrome cantilevered overshelf	30	48	63
4UEN3	with flat top, chrome leg with 2 C frame bases ,with chrome cantilevered overshelf	30	60	63



4UEN4	with flat top, chrome leg with 1 wire shelf and 1 H frame ,with chrome cantilevered overshelf	30	48	63
4UEN5	with flat top, chrome leg with 1 wire shelf and 1 H frame ,with chrome cantilevered overshelf	30	60	63



Accessories

Item#	Desc	Overall Dimensions			Remark
		Width	Length	Height	
		(in)	(in)	(in)	
4UEN7	Cantilever Shelf	12	48	1 5/8	Fit 4UEN2/4UEN4
4UEN8	Cantilever Shelf	12	60	1 5/8	Fit 4UEN3/4UEN5
2KRE5	Caster Kit. Pkg of 4. (2 Swivel and 2 with brake)				Fit 2KRD6/2KRD7/2KRD8/2KRD9/2KRE1/2KRE2/2KRE3/2KRE4/2KRE6/2KRE7/2KRE8.4UEJ3/4UEJ4/4UEJ5/4UEJ6/4UEJ7/4UEJ8/4UEJ9/4UEK1/4UEK2/4UEK3/4UEK4/4UEK5/4UEK6/4UEK6/4UEK7/4UEK8/4UEK9/4UEL1/4UEL2

