



GREENLEE®
A Textron Company

**MADE
FOR THE
TRADE**

DIAGONAL CUTTING PLIERS

AVAILABLE SIZES:
5", 6", 7", 8", 8" angled

Exceeds ASME/ANSI
Specifications



DIAGONAL CUTTING PLIERS

FEATURES	BENEFITS
1 Tapered/Flared Handles	Allows for increased leverage when cutting large diameter wire.
2 Ergonomic Flattened Oval Grip Profile	Allows for a larger load surface to increase comfort and reduce user fatigue.
3 Induction-Hardened Cutting Knives	For superior cutting capability, wear resistance and long life.
4 Brushed Finish	For professional look and longer wear.
5 Riveted Joint	For precision feel, smooth action with minimum joint looseness.
6 Integral Thumb Stops	To reduce slipping and allow user maximum tool control.
7 Short Cutting Jaws	Allow for maximum cutting force.
8 Beveled Cutting Edges	Allow close cuts to any surface.
9 Identification Area	To allow user to personally label or identify their tool.

Note: This is not an insulated tool.

Diagonal Cutting Pliers

CAT. NO.	UPC NO.	DESCRIPTION
0251-05M	54736	Diagonal Cutting Pliers 5" Mini Molded Grip
0251-06M	54737	Diagonal Cutting Pliers 6" Molded Grip
0251-07M	54738	High Leverage Diagonal Cutting Pliers 7" Molded Grip
0251-08M	54739	High Leverage Diagonal Cutting Pliers 8" Molded Grip
0251-08M-CP	95926	High Leverage Diagonal Cutting Pliers 8" Molded Grip Counter Pack (Qty 5)
0251-08AM	54740	High Leverage Diagonal Cutting Pliers 8" Angled Molded Grip

SPECIFICATIONS	5"	6"	7"	8"
Overall Length	5-1/2" (14.0 cm)	6-1/8" (15.5 cm)	7" (17.8 cm)	8-3/4" (22.2 cm)
Weight	.28 lbs. (.13 kg)	.35 lbs. (.16 kg)	.57 lbs. (.26 kg)	.85 lbs. (.39 kg)

International Tel: +1.815.397.7070
Fax: +1.815.397.9247

Canada Tel: 800.435.0786
Fax: 800.524.2853

USA Tel: 800.435.0786
Fax: 800.451.2632



4455 BOEING DRIVE, ROCKFORD, IL 61109-2988 USA
GENERAL OFFICES: 815.397.7070

www.greenlee.com

MA-4901 11/06 ©2006 Greenlee Textron Inc.
Greenlee Textron Inc. is a subsidiary of Textron Inc.