



Critical information for determining the products you need!

TERMINAL TYPE	TERMINAL SERIES	PLIERS					ERGONOMIC RATCHET HAND TOOLS						RATCHET HAND TOOLS	
		WT110M	WT111M	WT112M	WT161M	WT2000	ERG2001	ERG2002	ERG2004	ERG2005	ERG2006	ERG1255	WT1377	WT145A
Nylon Terminals	RZZ			•		•	•				•			•
	RA, RAX			•		•	•							•
	RB			•		•	•							•
	RBC, RC			•		•	•							•
Nylon Butt Splices	RA			•		•	•							
	RB			•		•	•							
	RC			•		•	•							
Nylon Parallel Splices	RAA					•								
	RBB					•								
	RCC					•								
All Nylon Disconnects (except .110 size)	RA			•		•	•							
	RB			•		•	•							
	RC			•		•	•							
Heat Shrinkable Terminals, Splices, Disconnects	RAS											•		
	RBS											•		
	RCS											•		
Vinyl Terminals and Splices	RA, RAA			•		•	•							
	RB, RBB			•		•	•							
	RC, RCC, RBC			•		•	•							
				•		•	•							
Bare Terminals and Splices	A,AA	•	•	•	•	•		•						
	B,BB	•	•	•	•	•		•			•			
	C,CC	•	•	•	•	•		•			•			
Wire Joints	RB			•		•	•							
	RC			•		•								
	RP			•		•								
	PT		•		•									
Hi-Temp Terminals and Splices	NW-Rings												•	
	NW-Splices												•	
Insulation Grip	A	•												
	B	•												
.110 Disconnects	A,B	•	•	•										
	RA, RB										•			
Flag Terminals	AB								•					
	C								•					
Tefzel® Terminals and Splices	RAT, RAAT			•		•								
	RBT, RBBT			•		•								
	RCT, RCCT			•		•								
Vinyl Disconnects	RA			•		•	•							
	RB			•		•	•							
	RC			•		•	•							
Bare Disconnects	A	•	•	•	•	•		•						
	B	•	•	•	•	•		•			•			
	C	•	•	•	•	•		•			•			

Tefzel® is a registered trademark of DuPont.

Tool Selection Charts (continued)

Critical information for determining the products you need!

TERMINAL TYPE	TERMINAL SERIES	RATCHET HAND TOOLS (CONT.)			BAT22-6 BAIR22-6 PAIR22-6			12050 MYLAR TAPE AUTO TOOL													
		WT145C	WT2130A	DIE2001	DIE2002	DIE2005	12051	12052	12054	12055	12056	12057	12058	12059	12060	683-54335					
Nylon Terminals	RZZ																				
	RA, RAX	•								•											
	RB	•			•							•									
	RBC, RC	•	•		•								•								
Nylon Butt Splices	RA	•			•																
	RB	•			•																
	RC	•	•		•																
Nylon Parallel Splice	RAA																				
	RBB																				
	RCC																				
All Nylon Disconnects (except .110 size)	RA	•			•					•											
	RB	•			•						•										
	RC	•	•		•								•								
Heat Shrinkable Terminals, Splices, Disconnects	RAS																				
	RBS																				
	RCS																				
Vinyl Terminals and Splices	RA, RAA	•			•						•										
	RB, RBB	•			•							•									
	RC, RCC, RBC	•	•		•								•								
Bare Terminals and Splices	A,AA																				
	B,BB					•												•			
	C,CC						•														•
Wire Joints	RB				•																
	RC																				
	RP		•																		
	PT		•																		
Hi-Temp Terminals and Splices	NW-Rings																				
	NW-Splices																				
Insulation Grip	A																				
	B																				
.110 Disconnects	A,B																				
	RA,RB																				
Flag Terminals	AB																				
	C																				
Tefzel Terminals and Splices	RAT, RAAT	•																			
	RBT, RBBT	•																			
	RCT, RCCT	•																			
Vinyl Disconnects	RA	•			•						•										
	RB	•			•							•									
	RC	•	•		•								•								
Bare Disconnects	A																				
	B					•															
	C						•							•							

Tefzel® is a registered trademark of DuPont.