

JOBBOX[®]

INDUSTRIAL 2-DOOR, 8-DRAWER CABINET



Unmatched Security, Versatility and Durability

High Load Capacity Drawers

- Exclusive drawer design supports up to 60% greater loads
- Three 2 1/2" deep drawers feature 75 lb. load capacity
- Five 5 1/2" deep drawers feature 125 lb. load capacity



New EZ-Loader™ Anti-Tip Skid Bolster

- Skid bolster extends to the front to help prevent tipping
- Casters install with 5/16" self-tapping bolts
- Now fork lift accessible from all sides
- Patent pending



PREMIUM STORAGE SOLUTIONS



Fully Welded Padlock Housing

Six, 5/8" Steel Locking Pin Security

Eight built-in door shelves. Extra deep 4 1/2" Top Door Shelves

Grip-Rite™ Door Channels

Formed-In Lifting Handles

Fork Lift Accessible From All Sides

Welded Corner Gussets Reinforce Body

Fully Staked and Welded 3/8" Hinge with 1" Knuckles and Hardened 1/4" Pin

Drawers Fully Extend for Easy Access

Three-2 1/2" Drawers support 75 lbs. and Five 5 1/2" Deep Drawers Support Up To 125 lbs.

NEW EZ-Loader™ Anti-Tip Skid Bolster

Hand or Foot-Operated Door Latch Release System

Uses 5/16" Self-Tapping Screws for Caster Installation



REINFORCED SHELF FRAME

Shelves are supported by independently reinforced frame mounted inside cabinet



RUGGED 3/8" LATCH HOOKS

Extra heavy duty door latch hooks resist repeated pry bar attempted break-ins. Recessed Grip-Rite™ door channels add reinforcement to doors



EXPANDED DOOR SHELVES

Top shelf inside both doors is expanded to hold oversized objects and tools



REINFORCED FRAME

Heavy-gauge, 7" full corner gussets resist warping and give added strength to our one-piece, formed and rolled steel cabinet



PADLOCK PROTECTED


5/8" round solid steel locking pins along front of cabinet creates virtually impossible to break-in storage



REINFORCED SHELVES

Cabinet shelves are braced on their undersides with a heavy-gauge steel "V-Shaped" brace

Model #	UPC	Drawers (24" D; 21 1/2" W)	A	B	C	D	E	Usable Cu. Ft.	Shipping Cu. Ft.	Shipping Wt. (Lbs.)
Drawer Cabinet										
1-679990	0-43419-93219-7	Three 2 1/2" Deep; Five 5 1/2" Deep	60 3/4	60 1/8	30 1/4	53 1/4	25 3/4	58.7	62.5	610.0



www.deltastorage.com

All information on this sheet is subject to change without notice. For ordering, use Part# LIT141 © 2007 Delta Consolidated Industries, Inc.

Delta Consolidated Industries, Inc.
PO BOX 1846 Jonesboro, AR 72403-1846
800-643-0084 • Fax 877-356-1879