

John Sterling™

CLOSET MAX™ Closet Hardware



Assembled Unit



Closet Poles and Rods



Brackets and End Caps



Over-the-Door Program



Pole Sockets

Professional-grade performance for a great price!

Closet Max™ organizational products maximize the storage space in any size and style of closet, from small coat storage to a large master suite walk-in. The shelf rod brackets offer Slide-Thru™ features so hangers slide through without obstruction. The brackets hold up to 1,000 lbs. per pair, giving a steady and strong support for any kind of storage. Installation is fast and easy with the poles snapping in place - no screws are required. All components are available in a variety of upscale finishes. Finally, adding the closet pole end caps will create a clean and finished look in any closet.

Applications:

- Homes
- Offices
- Businesses
- Displays
- Bathrooms
- Studies
- Living Areas
- Light storage




KNAPPE & VOGT

2700 Oak Industrial Drive NE, Grand Rapids, MI USA 49505 | 800.253.1561 | www.kv.com




Heavy-Duty Cut-to-Fit Closet Poles



0015

- 1-5/16" Diameter
- "Double-thick" 17 gauge walls
- Cut-to-fit



Heavy-Duty Adjustable Closet Rods



RP0020

- Material thickness: 1.2 mm
- Poles adjust 48" to 72"
- 1-1/4" diameter



Item	Description	Finish	Unit Dimensions			Unit Pack Qty.	Unit Wt. (lbs.)	Master Carton Dimensions			Master Pack Qty.	Master Carton Wt. (lbs.)	UPC Code	SCM Code
			L	W	D			L	W	D				
Closet-Max™														
Heavy-Duty Closet Poles														
0015-6BN	6' Heavy-Duty Closet Pole	BN	72	1.3125	1.3125	1	4.5	73	3	4.5	4	18.1	077355018028	10077355018025
0015-8BN	8' Heavy-Duty Closet Pole	BN	96	1.3125	1.3125	1	5.6	97	3	4.5	4	22.5	077355018011	10077355018018
0015-6BRZ	6' Heavy-Duty Closet Pole	BRZ	72	1.3125	1.3125	1	4.5	73	3	4.5	4	18.1	077355000122	10077355000129
0015-8BRZ	8' Heavy-Duty Closet Pole	BRZ	96	1.3125	1.3125	1	5.6	97	3	4.5	4	22.5	0773550-----	100773550-----
0015-6CH	6' Heavy-Duty Closet Pole	CH	72	1.3125	1.3125	1	4.5	73	3	4.5	4	18.1	077355078817	10077355078814
0015-8CH	8' Heavy-Duty Closet Pole	CH	96	1.3125	1.3125	1	5.6	97	3	4.5	4	22.5	077355078824	10077355078821
0015-6OK	6' Heavy-Duty Closet Pole	OK	72.00	1.3125	1.3125	1	2.69	73.00	4.25	3.00	6	16.86	029274345815	10029274345812
0015-8OK	8' Heavy-Duty Closet Pole	OK	96.00	1.3125	1.3125	1	3.58	97.00	4.25	3.00	6	22.47	029274345839	10029274345836
0015-6WT	6' Heavy-Duty Closet Pole	WT	72	1.3125	1.3125	1	4.5	73	3	4.5	4	18.1	077355000092	10077355000099
0015-8WT	8' Heavy-Duty Closet Pole	WT	96	1.3125	1.3125	1	5.6	97	3	4.5	4	22.5	077355000108	10077355000105
Heavy-Duty Adjustable Closet Rods														
RP0020-48/72BN	48"-72" Heavy-Duty Adjustable Rod	BN	39.50	2.50	1.25	1	3.844	3.25	8.75	40.875	6	23.813	029274351083	10029274351080
RP0020-48/72BRZ	48"-72" Heavy-Duty Adjustable Rod	BRZ	39.50	2.50	1.25	1	3.844	3.25	8.75	40.875	6	23.813	029274351175	10029274351172
RP0020-48/72CH	48"-72" Heavy-Duty Adjustable Rod	CH	39.50	2.50	1.25	1	3.844	3.25	8.75	40.875	6	23.813	029274351052	10029274351059
RP0020-48/72WH	48"-72" Heavy-Duty Adjustable Rod	WH	39.50	2.50	1.25	1	3.844	3.25	8.75	40.875	6	23.813	029274351021	10029274351028



Heavy-Duty Shelf & Rod Brackets



0495

- Holds up to 1,000 lbs. per pair
- Slide-Thru™ feature
- Poles snap into place



Over-the-Door Program



261-4PM

261-1PM

261-2PM

- Fits door sizes of 1-3/8" and 1-3/4" thickness
- Easy to install



Item	Description	Finish	Unit Dimensions			Unit Pack Qty.	Unit Wt. (lbs.)	Master Carton Dimensions			Master Pack Qty.	Master Carton Wt. (lbs.)	UPC Code	SCM Code
			L	W	D			L	W	D				
Closet-Max™														
Heavy-Duty Shelf & Rod Bracket														
RP-0495-BN	Heavy-Duty Shelf & Rod Bracket	BN	7.750	1.063	12.688	1	1.4	13.5	8.63	7	10	13.7	077355004762	10077355004769
RP-0495-BRZ	Heavy-Duty Shelf & Rod Bracket	BRZ	7.750	1.063	12.688	1	1.4	13.5	8.63	7	6	8.2	077355000139	10077355000136
RP-0495-CH	Heavy-Duty Shelf & Rod Bracket	CH	7.750	1.063	12.688	1	1.4	13.5	8.63	7	10	13.7	077355080261	10077355080268
RP-0495-PM	Heavy-Duty Shelf & Rod Bracket	PM	7.750	1.063	12.688	1	1.4	13.5	11.25	8.62	10	13.7	077355080254	10077355080251
RP-0495-WT	Heavy-Duty Shelf & Rod Bracket	WT	7.750	1.063	12.688	1	1.4	13.5	11.25	8.63	10	13.7	077355049503	10077355049500
Over-the-Door Program														
261-1PM	Over-the-Door Valet Rod	Nickel	3.50	11.75	2.25	1	0.77	12.20	7.50	7.50	6	5.51	077355001228	10077355001225
261-2PM	Over-the-Door Garment Rail	Nickel	18.125	8.875	1.25	1	1.56	18.50	9	7.88	6	9.92	077355001242	10077355001249
261-4PM	Over-the-Door Closet Rod Kit	Nickel	20.125	6.625	2.125	1	1.35	20.50	7	9.83	4	6.61	077355001235	10077355001232




Heavy-Duty Closet Pole Sockets



0010

- Packed in pairs
- For 1-5/16" diameter poles
- Mounting hardware included




Shelf Bracket Screws



0047

- Finishes available to match Shelf & Rod Brackets



Decorative Closet Pole End Caps



0017

- Packed in pairs
- Covers up pole ends
- Keeps hangers from sliding off
- Set screw holds cap in place



Item	Description	Finish	Unit Dimensions			Unit Pack Qty.	Unit Wt. (lbs.)	Master Carton Dimensions			Master Pack Qty.	Master Carton Wt. (lbs.)	UPC Code	SCM Code
			L	W	D			L	W	D				
Closet-Max™														
Heavy-Duty Closet Pole Socket (Carded size)														
CD-0010-BN	Heavy-Duty Pole Socket	BN	6.313	3.813	1.125	1	0.4	6.5	6.25	4.06	6	2.1	077355001037	10077355001034
CD-0010-BRZ	Heavy-Duty Pole Socket	BRZ	6.313	3.813	1.125	1	0.4	6.5	6.25	4.06	6	2.1	077355001013	10077355001010
CD-0010-CH	Heavy-Duty Pole Socket	CH	6.313	3.813	1.125	1	0.4	6.5	6.25	4.06	6	2.1	077355078831	10077355078838
CD-0010-OK	Heavy-Duty Pole Socket, Pair	OK	48.00	8.00	0.625	1	7.49	49.50	8.60	3.50	5	37.44	029274351090	10029274351097
CD-0010-WT	Heavy-Duty Pole Socket	WT	6.313	3.813	1.125	1	0.4	6.5	6.25	4.06	6	2.1	077355001006	10077355001003
Decorative Closet Pole End Cap (Carded size)														
CD-0017-BN	Decorative End Cap	BN	5.875	3.813	1.000	1	0.3	6.5	5.75	4.06	6	1.6	077355001754	10077355001751
CD-0017-BRZ	Decorative End Cap	BRZ	5.875	3.813	1.000	1	0.3	6.5	5.75	4.06	6	1.6	077355001747	10077355001744
CD-0017-CH	Decorative End Cap	CH	5.875	3.813	1.000	1	0.3	6.5	5.75	4.06	6	1.6	077355001723	10077355001720
CD-0017-WT	Decorative End Cap	WT	5.875	3.813	1.000	1	0.3	6.5	5.75	4.06	6	1.6	077355001716	10077355001713
Shelf Bracket Screws														
CD-0047	Screws w/white caps for brackets	WT	3.938	3.500	0.500	1	0.1	10.75	6.75	4.06	20	1.6	077355004700	10077355004707
CD-0047-BRZ	Painted screws for brackets	BRZ	3.938	3.500	0.500	1	0.1	4.25	4	12	10	0.6	077355004731	10077355004738
CD-0047-CH	Chrome plated screws for brackets	CH	3.938	3.500	0.500	1	0.1	4.25	4	12	10	0.6	077355004717	10077355004714
CD-0047-PM	Painted screws for brackets	PM	3.938	3.500	0.500	1	0.1	4.25	4	12	10	0.6	077355004748	10077355004745

