

T-4002-30x

Single Temperature Thermostat with Cover and Two-Pipe Conversion Kits

Description

The T-4002-30x Thermostat with Cover and Two-Pipe Conversion Kits feature a T-4002-201 (D.A.) or a T-4002-202 (R.A.) Thermostat. The kits also contain a white or beige cover and cover plate, a selection of faceplates, and all other necessary parts and mounting hardware required to convert a wide array of two pipe competitors' thermostats.

Refer to *T-4002-301*, *T-4002-303 (DA)* and *T-4002-302*, *T-4000-304 (RA) Thermostat with Cover and Two-Pipe Conversion Kits Product/Technical Bulletin (LIT-7171090)* for important product information.

Repair Information

If the T-4002-30x Thermostat with Cover and Two-Pipe Conversion Kit fails to operate within its specifications, replace the unit. For a replacement thermostat, contact the nearest Johnson Controls® representative.

Selection Chart

Code Number	Description
T-4002-301	Direct Acting Thermostat and White Cover with Two-Pipe Conversion Kit
T-4002-302	Reverse Acting Thermostat and White Cover with Two-Pipe Conversion Kit
T-4002-303	Direct Acting Thermostat and Beige Cover with Two-Pipe Conversion Kit
T-4002-304	Reverse Acting Thermostat and Beige Cover with Two-Pipe Conversion Kit

Features

- reduces the number of stocked items
- simplifies the ordering process
- includes:
 - T-4002-201 (D.A.) or T-4002-202 (R.A.) Thermostat
 - White or Beige Cover
 - Terminal Connector and Tubing
 - Tube Couplings and Clamps
 - Installation Instructions
 - Faceplates (horizontal w/window, horizontal w/logo, vertical w/logo, and blank)
 - Cover Plate/Subplate
 - Adjustable Pipehead
 - Mounting Hardware



T-4002-30x Thermostat

Non-Johnson Controls Conversions

Converts the Following Non-Johnson Controls Thermostats:
Barber-Colman "TK" Series or "TKR" Series Wallbox and Mortar Joint
Honeywell TO900 or TP900 Series Wallbox
Honeywell TO910 or TP910 Series Wallbox and Mortar Joint
Honeywell TP970 Series Shallow and Deep Wallboxes
Landis & Gyr Powers TH832 "D" Series Wallbox and Ground Plate
Landis & Gyr Powers T-21 Series Ground Plate, Wallbox and Mortar Joint
Landis & Gyr Powers TH180 Series Wallbox and Drywall Mounting
Landis & Gyr Powers TH192 Series Wallbox and Drywall Mounting
Robertshaw T-15 (Metal) Early Wallbox and Mortar Joint
Robertshaw T-15 Later Wallbox and Mortar Joint
Robertshaw 2212 Series ¹
Robertshaw T-18 (Plastic) Drywall Mounting
Draeger (ITT/Essen/Johnson Controls) Wallbox
UPC

1. Converts dead band thermostat to single temperature control.