



Jonard Industries Pliers are High Quality tools that are precision machined, hardened, and carefully tempered for maximum strength performance and durability.



JIC-22148




JIC-63050



JIC-750




JIC-5026



JIC-891



JIC-50210



JIC-7858



JIC-50212



JIC-683



DIAGB6




JIC-21257



JIC-2288



JIC-3385



JIC-842



JIC-453



JIC-3026

JIC-22148 • 7" Combo Crimper Long Nose Pliers
Five tools in one. .030 in. stripping hole. Press UG, UR, and UY Connectors.

JIC-63050 • High Leverage Cable Cutter
Cuts aluminum and soft copper cable up to 100-pair. 9 in. long.

JIC-750 • 3/4" Coax Cable Cutter
Also known as a Banana Cutter, this cutter is designed to cut 3/4" coaxial cable. 8" long.

JIC-5026 • 6" Pump Pliers
Tongue & groove design. Wide range of jaw openings.

JIC-50210 • 10" Pump Pliers
Tongue & groove design. Wide range of jaw openings.

JIC-50212 • 12" Pump Pliers
Tongue & groove design. Wide range of jaw openings.

JIC-891 • 6" Connector-Crimping Pliers with Side Cutters Press UG, UR and UY connectors

JIC-7858 • 6 1/2" Telecom Diagonal Cutter Pliers
Tapered nose diagonal cutting pliers with standard bevel knives with .030" and .045" skinning holes, with crusher used for multi-purpose wire work, with two V-shaped stripping notches. The comfortable handles are red plastic.

DIAGB6 • 6 1/16" Diagonal Pliers - Skinning & Stripping
Tapered nose diagonal cutting pliers with standard bevel knives with one .045" skinning hole, crusher used for multipurpose wire work, and two V shaped stripping notches.

JIC-683 • 9" Lineman's B Side Cut Pliers
Heavy-duty general use pliers.

JIC-2288 • 8" High Leverage Diagonal Cutter
For heavy-duty wire cutting.

JIC-21257 • 6 7/8" Telecom Long Nose Pliers
Long nose have side cutting blades, a crushing slot, one .030" stripping hole, and a thin knurled nose. Also known as KS21257L1.

JIC-842 • 6 7/8" Telecom Long Nose D Pliers
General use looping, bending and cutting.

JIC-3385 • 5 1/2" Curved Needle Nose Pliers
Nose is bent 60° for maximum visibility. Pliers has a spring loaded ergonomic design.

JIC-3026 • 6 3/8" - Curved Long Nose Pliers
Nose is bent 70° for maximum visibility. Design includes knurled jaws for sure wrapping and looping. Comfortable ergonomic handles.

JIC-453 • 4 1/2" Flush Cut Pliers
A close cutting plier used to trim conductors from the 710 connector modules without leaving exposed conductors. Ideal for close trimming of gates and sprue on injection molded plastic parts. Jaw design aids in use in confined areas. Turquoise color handle.