




**JOBSITE EQUIPMENT**

# REPLACEMENT PARTS

**JOBMASTER® CHESTS**  
**MODELS 32, 36, 42, 60, 2472, 4824, & 4830**

**FOR REPLACEMENT PARTS GO TO WWW.KNAACK.COM**

Current Models with  
**WATCHMAN® IV Lock System**




**For Customer Service**  
**call toll free:**  
**1-800-456-7865**


**\*NOTE, WELDING REQUIRED ON SOME REPLACEMENT PARTS.**  
The parts noted require welding by a certified welder and some touchup paint over newly welded areas. Welding Instructions available.  
Knaack LLC assumes no legal responsibility for any welding done outside the factory.  
All warranties will be voided.

ITEM	PART No.	DESCRIPTION	FITS MODEL #
1	7286-1PK	WATCHMAN® IV Lock System	Lock tab with bolt for all current models with deadbolt lock system
2	800-1PK	WATCHMAN® III Lock System (next page)	Lock tab with bolt for models made 1989-2000
3	955	WATCHMAN® II Lock System (next page)	Lock tab with bolt for models made 1980-1989
4	70030-1PK	POWER PASS™ Grommet	WATCHMAN® IV Model Chests starting fall 2007, except Models 32 and 36
5	7127	Pipe Handle	Single 12" handle for Models 32, 36, 42
5	7128	Pipe Handle	Single 17" handle for Models 60, 2472, 4824
5	7129	Pipe Handle	Single 22-1/2" handle for Models 4830
6	15-0001B	Cover Handle (next page)	WATCHMAN® III Series
6	7287	Cover Handle	WATCHMAN® IV Series
7	7343	Cover	WATCHMAN® IV Series cover for Model 32
7	7344	Cover	WATCHMAN® IV Series cover for Model 36
7	7345	Cover	WATCHMAN® IV Series cover for Model 42
7	7348	Cover	WATCHMAN® IV Series cover for Model 60
7	7342	Cover	WATCHMAN® IV Series cover for Model 2472
7	7346	Cover	WATCHMAN® IV Series cover for Model 4824
7	7347	Cover	WATCHMAN® IV Series cover for Model 4830
8	7012	19" Skid	Models 32, 36, 42
8	7013	24" Skid	Models 60, 2472, 4824
8	7014	30" Skid	Models 4830
9	70053	Left Cover Support	Models 32, 36, 42, 60, 2472, 4824, 4830
9	70054	Right Cover Support	Models 60, 2472, 4824, 4830
10	70056	Cover Hinge	WATCHMAN® IV 2-point and 3-point latching Model 32
10	70057	Cover Hinge	WATCHMAN® IV 2-point and 3-point latching Model 36
10	70058	Cover Hinge	WATCHMAN® IV 2-point and 3-point latching Model 42
10	7405	Cover Hinge	WATCHMAN® III & WATCHMAN® IV 2-point latching Model 60
10	70046	Cover Hinge	WATCHMAN® IV 2-point and 3-point latching Model 60
10	70055	Cover Hinge	WATCHMAN® III & WATCHMAN® IV 2-point and 3-point latching Model 2472
10	7404	Cover Hinge	WATCHMAN® III & WATCHMAN® IV 2-point latching Model 4824, 4830
10	70047	Cover Hinge	WATCHMAN® IV 3-point latching Model 4824, 4830
11	956	Corner Tang, Catch (next page)	WATCHMAN® III JOBMASTER® Chests: all
11	70059	Corner Cover Catch	WATCHMAN® IV JOBMASTER® Chests: all
11	70060	Center Cover Catch	WATCHMAN® IV JOBMASTER® Chests: 42, 60, 2472, 4824, 4830
12	495	4" Accessory Casters - set of 4	Load Rating 1600 Lbs., 2" wide wheels
12	505	5" Accessory Casters - set of 4	Load Rating 1240 Lbs., 1-1/4" wide wheels
12	516	6" Accessory Casters - set of 4	Load Rating 2240 Lbs., 2" non-marking wheels
12	600	6" Accessory Casters - set of 4	Load Rating 3280 Lbs., 2" wide wheels
12	695	6" Accessory Casters - set of 4	Load Rating 2600 Lbs., 2" wide wheels
13	41	Accessory Tool Tray	Models 32, 36, 42
13	21	Accessory Tool Tray	Models 60, 2472, 4824
13	31	Accessory Tool Tray	Model 4830
13	10	Accessory Tote Tray	Any Model, no dividers
13	11	Accessory Tote Tray	Any Model, with dividers
14	953-1CN	Aerosol Paint (not shown)	Genuine KNAACK® Tan trademarked color
	N/A	Latch Rod	Not available as a Replacement Part






**Previous generation models with  
WATCHMAN® III Lock System**



**Previous generation models with  
WATCHMAN® II Lock System**



**Installation Instructions for WATCHMAN®  
Lock Systems available at [www.knaack.com](http://www.knaack.com)**