

YES! ✓ WE CAN!

USE WITH STANDARD HI-TECH COMPONENTS

HI-TECH™ HIPOST

HALLOWELL® High Capacity Shelving

H-Post High capacity Shelving is ideal when additional strength is required for any shelving installation. It is also recommended for multi-high-rise applications.

H-Posts are fabricated from 14 gauge cold rolled steel and formed into a unique tubular design to provide more than **twice the load capacity** compared to the standard posts.



ONE PIECE SHELF CLIP

- Each shelf requires four of these sturdy and compact clips
- Clips key firmly into post slots to hold shelves securely in place
- Also fits Beaded Front, Angle Back Posts and T-Posts
- Provides independent shelf positioning on 1-1/2" centers
- Non-Intrusive clip sits flush with inside edge of front posts

H-POSTS

- Designed for high-density applications
- More than twice the capacity of standard posts
- Used at front and back
- Used with standard Hi-Tech components

CLOSED UNITS

COLOR SELECTION ✓

711
PLATINUM (PL)

H-POST
COLOR SELECTION ✓

707
MARINE BLUE
(MB)



8 Shelf Unit



6 Shelf Unit



5 Shelf Unit

OPEN UNITS



8 Shelf Unit



6 Shelf Unit



5 Shelf Unit



ADDER UNITS



Adder units are available in open and closed versions.



All models shown with the standard foot plate that provides a strong and secure anchoring point



Special triple point brace clip provides a strong and ridged anchor point for the cross braces.

AVAILABLE IN 7' AND 10' HIGH

YES!

WE CAN!



STARTER UNIT



ADDER UNIT



5 SHELF UNIT



6 SHELF UNIT



8 SHELF UNIT

OPEN H-POST SHELVING HEAVY AND EXTRA HEAVY-DUTY

W	H	D		Shelf Capacity*	5-Adj Shelf Unit SKU no.	6-Adj Shelf Unit SKU No.	8-Adj Shelf Unit SKU No.
HEAVY-DUTY							
36	87	18	Starter	800	4GZL3	4GZL7	4GZN2
36	87	18	Add-on	800	4GZL5	4GZL9	4GZN4
36	87	24	Starter	800	4GZL4	4GZL8	4GZN3
36	87	24	Add-on	800	4GZL6	4GZN1	4GZN5
48	87	18	Starter	450	4GZN6	4GZP1	4GZP5
48	87	18	Add-on	450	4GZN8	4GZP3	4GZP7
48	87	24	Starter	500	4GZN7	4GZP2	4GZP6
48	87	24	Add-on	500	4GZN9	4GZP4	4GZP8
36	123	18	Starter	800	4GZU6	4GZV1	4GZV5
36	123	18	Add-on	800	4GZU8	4GZV3	4GZV7
36	123	24	Starter	800	4GZU7	4GZV2	4GZV6
36	123	24	Add-on	800	4GZU9	4GZV4	4GZV8
48	123	18	Starter	450	4GZV9	4GZW4	4GZW8
48	123	18	Add-on	450	4GZW2	4GZW6	4GZX1
48	123	24	Starter	500	4GZW1	4GZW5	4GZW9
48	123	24	Add-on	500	4GZW3	4GZW7	4GZX2
EXTRA HEAVY-DUTY							
36	87	18	Starter	1200	4GZZ9	4HAA4	4HAA8
36	87	18	Add-on	1200	4HAA2	4HAA6	4HAC1
36	87	24	Starter	1250	4HAA1	4HAA5	4HAA9
36	87	24	Add-on	1250	4HAA3	4HAA7	4HAC2
48	87	18	Starter	900	4HAC3	4HAC7	4HAD2
48	87	18	Add-on	900	4HAC5	4HAC9	4HAD4
48	87	24	Starter	900	4HAC4	4HAC8	4HAD3
48	87	24	Add-on	900	4HAC6	4HAD1	4HAD5
36	123	18	Starter	1200	4HAH3	4HAH7	4HAJ2
36	123	18	Add-on	1200	4HAH5	4HAH9	4HAJ4
36	123	24	Starter	1250	4HAH4	4HAH8	4HAJ3
36	123	24	Add-on	1250	4HAH6	4HAJ1	4HAJ5
48	123	18	Starter	900	4HAJ6	4HAK1	4HAK5
48	123	18	Add-on	900	4HAJ8	4HAK3	4HAK7
48	123	24	Starter	900	4HAJ7	4HAK2	4HAK6
48	123	24	Add-on	900	4HAJ9	4HAK4	4HAK8
ADDITIONAL SHELVES					Heavy-Duty	Extra Heavy-Duty	
36	18				4CPP1	4CPP5	
36	24				4CPP2	4CPP6	
48	18				4CPP3	4CPP7	
48	24				4CPP4	4CPP8	

NOTES: posts and sides 707 Marine Blue, backs and shelves 711 Platinum.

*Safety factor=1.65

OPEN UNITS: Starter units include four posts, one pair back sway braces, two pair side sway braces and 5-8 shelves. Adder units include two posts, one pair back sway braces, one pair side sway braces and 5-8 shelves, 10 Ft. high units will have 2 sets of shelving braces. Foot plates are included for all H-Post units

USE WITH STANDARD HI-TECH COMPONENTS

**CLOSED H-POST SHELVING
HEAVY AND EXTRA HEAVY-DUTY**

W	H	D		Shelf Capacity*	5-Adj Shelf Unit SKU No.	6-Adj Shelf Unit SKU No.	8-Adj Shelf Unit SKU No.
HEAVY-DUTY							
36	87	18	Starter	800	4GZP9	4GZR4	4GZR8
36	87	18	Add-on	800	4GZR2	4GZR6	4GZT1
36	87	24	Starter	800	4GZR1	4GZR5	4GZR9
36	87	24	Add-on	800	4GZR3	4GZR7	4GZT2
48	87	18	Starter	450	4GZT3	4GZT7	4GZU2
48	87	18	Add-on	450	4GZT5	4GZT9	4GZU4
48	87	24	Starter	500	4GZT4	4GZT8	4GZU3
48	87	24	Add-on	500	4GZT6	4GZU1	4GZU5
36	123	18	Starter	800	4GZX3	4GZX7	4GZY2
36	123	18	Add-on	800	4GZX5	4GZX9	4GZY4
36	123	24	Starter	800	4GZX4	4GZX8	4GZY3
36	123	24	Add-on	800	4GZX6	4GZY1	4GZY5
48	123	18	Starter	450	4GZY6	4GZZ1	4GZZ5
48	123	18	Add-on	450	4GZY8	4GZZ3	4GZZ7
48	123	24	Starter	500	4GZY7	4GZZ2	4GZZ6
48	123	24	Add-on	500	4GZY9	4GZZ4	4GZZ8

EXTRA HEAVY-DUTY							
36	87	18	Starter	1200	4HAD6	4HAE1	4HAE5
36	87	18	Add-on	1200	4HAD8	4HAE3	4HAE7
36	87	24	Starter	1250	4HAD7	4HAE2	4HAE6
36	87	24	Add-on	1250	4HAD9	4HAE4	4HAE8
48	87	18	Starter	900	4HAE9	4HAF4	4HAF8
48	87	18	Add-on	900	4HAF2	4HAF6	4HAH1
48	87	24	Starter	900	4HAF1	4HAF5	4HAF9
48	87	24	Add-on	900	4HAF3	4HAF7	4HAH2
36	123	18	Starter	1200	4HAK9	4HAL4	4HAL8
36	123	18	Add-on	1200	4HAL2	4HAL6	4HAM1
36	123	24	Starter	1250	4HAL1	4HAL5	4HAL9
36	123	24	Add-on	1250	4HAL3	4HAL7	4HAM2
48	123	18	Starter	900	4HAM3	4HAM7	4HAN2
48	123	18	Add-on	900	4HAM5	4HAM9	4HAN4
48	123	24	Starter	900	4HAM4	4HAM8	4HAN3
48	123	24	Add-on	900	4HAM6	4HAN1	4HAN5

ADDITIONAL SHELVES		Heavy-Duty	Extra Heavy-Duty
36	18	4CPP1	4CPP5
36	24	4CPP2	4CPP6
48	18	4CPP3	4CPP7
48	24	4CPP4	4CPP8



STARTER UNIT



ADDER UNIT



5 SHELF UNIT



6 SHELF UNIT



8 SHELF UNIT

NOTES: posts and sides 707 Marine Blue, backs and shelves 711 Platinum.

*Safety factor=1.65

CLOSED UNITS: Starter units include four posts, one back panel assembly, two side panel assemblies and 5-8 shelves.
Adder units include two posts, one back panel assembly, one side panel assembly and 5-8 shelves.
Foot plates are included for all H-Post units