

# STRONG, DURABLE, DEPENDABLE PRODUCTS THAT HAVE BEEN TRUSTED BY THE PROS FOR OVER 65 YEARS

**FIBERGLASS**



FS1106HD



FS1506



FS2006



FM1106HD



FM1506

**STEP**

**FS1100 - 375 lbs TYPE IAA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y470	FS1110HD	10'	45
36Y471	FS1112HD	12'	56

**FS1300 - 375 lbs TYPE IAA**

36Y472	FS1304HD	4'	15
36Y473	FS1305HD	5'	18
36Y474	FS1306HD	6'	22
36Y475	FS1308HD	8'	28
36Y476	FS1310HD	10'	40
33J684	FS1312HD	12'	41

**FS1400HD - 375 lbs TYPE IAA**

33J674	FS1403HD	3'	11.7
1CMR3	FS1404HD	4'	15
36Y477	FS1405HD	5'	17
1CMR4	FS1406HD	6'	21
36Y478	FS1407HD	7'	25
1CMR5	FS1408HD	8'	28
1CMR6	FS1410HD	10'	34
1CMR7	FS1412HD	12'	51

**STEP**

**FS1500 - 300 lbs TYPE IA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
1CMV5	FS1502	2'	8
33J704	FS1503	3'	12
1CMR1	FS1504	4'	14
36Y479	FS1505	5'	17
1CMP7	FS1506	6'	20
33J664	FS1507	7'	22
1CMP8	FS1508	8'	26
1CMP9	FS1510	10'	34
1CMR2	FS1512	12'	37

**L-3016 - 300 lbs TYPE IA**

36Y495	L-3016-04	4'	14
36Y496	L-3016-06	6'	20
36Y497	L-3016-08	8'	26
36Y498	L-3016-10	10'	34
36Y499	L-3016-12	12'	47

**STEP**

**FS2000 - 250 lbs TYPE I**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
1CMV5	FS2004	4'	12
33J704	FS2005	5'	15
1CMR1	FS2006	6'	17
36Y479	FS2007	7'	20
1CMP7	FS2008	8'	22

**FS4000 - 225 lbs TYPE II**

33J664	FS4004	4'	11
1CMP8	FS4006	6'	16
33J682	FS4007	7'	18
1CMP9	FS4008	8'	21

**TWIN**

**FM1100HD - 375 lbs TYPE IAA**

36Y449	FM1104HD	4'	28
36Y450	FM1106HD	6'	32
36Y451	FM1108HD	8'	48
33J743	FM1110HD	10'	64
33J660	FM1112HD	12'	78

**PLATFORM**

**FM1400HD - 375 lbs TYPE IAA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
1CMT6	FM1404HD	4'	21
33J708	FM1405HD	5'	24
1CMT7	FM1406HD	6'	27
33J772	FM1407HD	7'	32
1CMT8	FM1408HD	8'	36
1CMT9	FM1410HD	10'	55
1CMU1	FM1412HD	12'	68
1CMU2	FM1414HD	14'	84
1CMU3	FM1416HD	16'	100

**MRI CONDITIONAL TWIN FRONT**

**L-3431-MR - 375 lbs TYPE IAA**

15G136	L-3431-06MR	6'	27
36Y501	L-3431-08MR	8'	34

**TWIN FRONT**

**FM1500 - 300 lbs TYPE IA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
33J720	FM1503	3'	16
1CMU4	FM1504	4'	19
36Y452	FM1505	5'	22
1CMU5	FM1506	6'	27
33J668	FM1507	7'	30
1CMU6	FM1508	8'	34
5MRG5	FM1510	10'	44
5MRG6	FM1512	12'	62

**FM2000 - 250 lbs TYPE I**

36Y453	FM2004	4'	17
33J669	FM2006	6'	24
36Y454	FM2008	8'	34
36Y455	FM2010	10'	45
36Y456	FM2012	12'	55

**PLATFORM**

**FP1100HD - 375 lbs TYPE IAA**

36Y465	FP1104HD	4'	25
36Y466	FP1106HD	6'	36
36Y467	FP1108HD	8'	49
36Y468	FP1110HD	10'	61
36Y469	FP1112HD	12'	73

# STRONG, DURABLE, DEPENDABLE PRODUCTS THAT HAVE BEEN TRUSTED BY THE PROS FOR OVER 65 YEARS

**FIBERGLASS**



FP1104HD



FMP1504-4C



FT1006



FY8002



FX1108



FH1000



FE8800

## PLATFORM

### FP1400HD - 375 lbs TYPE IAA

ITEM NUMBER	MFR. MODEL	HT. TO PLTFRM.	SHIPPING WT. (LBS)
33J739	FP1403HD	3'	20
1CMU9	FP1404HD	4'	22
33J680	FP1405HD	5'	25
1CMU7	FP1406HD	6'	28
1CMV1	FP1408HD	8'	42
33J713	FP1410HD	10'	58
5MRG7	FP1412HD	12'	69

### FP1500 - 300 lbs TYPE IA

33J687	FP1503	3'	19
2KMC3	FP1504	4'	23
33J705	FP1505	5'	25
2KMC4	FP1506	6'	28
2KMC5	FP1508	8'	41
1CMU8	FP1510	10'	57
33J725	FP1512	12'	68

## TWIN PLATFORM

### FMP1500 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	HT. TO PLTFRM.	SHIPPING WT. (LBS)
36Y457	FMP1504	4'	34.87
36Y458	FMP1504-4C	4'	41.7
36Y459	FMP1506	6'	55.72
36Y460	FMP1506-4C	6'	62.55
36Y461	FMP1508	8'	76.53
36Y462	FMP1508-4C	8'	83.4
36Y463	FMP1510	10'	97.42
36Y464	FMP1510-4C	10'	104.24

"4C" indicates models with four casters

### STEP-TO-STRAIGHT

### FC1200 - 375 lbs TYPE IAA

33J688	FC1206	6'	33
33J768	FC1207	7'	36
33J692	FC1208	8'	41

## TRIPOD

### FT1000 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	HT. TO PLTFRM.	SHIPPING WT. (LBS)
36Y485	FT1004	4'	17
33J677	FT1005	5'	20
33J678	FT1006	6'	24
36Y486	FT1007	7'	27
36Y487	FT1008	8'	31
33J681	FT1010	10'	44
33J767	FT1012	12'	53

### THE ULTIMATE™

### L-3092 - 375 lbs TYPE IAA

4EB24	L-3092-13	13'	46
4EB25	L-3092-15	15'	49

## INDUSTRIAL STEP STAND

### FY8000 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	HT. TO PLTFRM.	SHIPPING WT. (LBS)
1CMV2	FY8001	1'	8
1CMV3	FY8002	2'	15
5MRH1	FY8003	3'	20
5MRH2	FY8004	4'	25
33J722	FY8004-S55-S56	4'	25

### MINI WORKING PLATFORM

### L-3041 - 300 lbs TYPE IA

33J771	L-3041-03	3'	13
--------	-----------	----	----

### EXTENSION TRESTLE

### FX1100 - 300 lbs TYPE IA

36Y488	FX1108	8'	65
33J662	FX1112	12'	115

## SHELF

### FH1000 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
33J706	FH1004	4'	8
33J729	FH1005	5'	10
33J679	FH1006	6'	11
33J665	FH1007	7'	12
33J717	FH1008	8'	14
33J675	FH1010	10'	20
33J676	FH1012	12'	24
33J718	FH1014	14'	28

### MANHOLE


### FE8800 - 300 lbs TYPE IA

36Y445	FE8808	8'	19
33J694	FE8810	10'	23
33J693	FE8812	12'	25
36Y446	FE8814	14'	30
36Y447	FE8816	16'	36
36Y448	FE8818	18'	41
33J685	FE8820	20'	45



**STRONG, DURABLE, DEPENDABLE PRODUCTS THAT HAVE BEEN TRUSTED BY THE PROS FOR OVER 65 YEARS**

**FIBERGLASS**



**EXTENSION**

**FE4200HD - 375 lbs TYPE IAA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
33J730	FE4216HD	16'	41
36Y422	FE4220HD	20'	50
33J697	FE4224HD	24'	58
33J670	FE4228HD	28'	67
36Y423	FE4620HD	20'	48
36Y424	FE4624HD	24'	56
36Y425	FE4628HD	28'	64

**FE3100 - 300 lbs TYPE IA**

36Y415	FE3108	8'	16
36Y416	FE3110	10'	21
36Y417	FE3112	12'	25
36Y418	FE3114	14'	28
36Y419	FE3116	16'	36
36Y420	FE3118	18'	41
36Y421	FE3120	20'	45

**EXTENSION**

**FE3200 - 300 lbs TYPE IA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
1CMW3	FE3216	16'	30
1CMW1	FE3220	20'	42
1CMV8	FE3224	24'	52
1CMV9	FE3228	28'	58
1CMW2	FE3232	32'	70
5MRG8	FE3240	40'	92

**L-3022-PT - 300 lbs TYPE IA WITH PROTOP™**

5MRH3	L-3022-20PT	20'	42
5MRH4	L-3022-24PT	24'	52
5MRH5	L-3022-28PT	28'	58
5MRH6	L-3022-32PT	32'	70

**EXTENSION**

**FE7000 - 300 lbs TYPE IA**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y426	FE7108	8'	16
36Y427	FE7110	10'	22
33J666	FE7112	12'	26
36Y428	FE7114	14'	32
36Y429	FE7116	16'	37
36Y430	FE7118	18'	53
36Y431	FE7120	20'	61
33J683	FE7216	16'	34
33J663	FE7220	20'	45
33J673	FE7224	24'	53
33J728	FE7228	28'	62
33J686	FE7232	32'	72
36Y432	FE7236	36'	110
33J671	FE7240	40'	117

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y433	FE7512	12'	27
36Y434	FE7514	14'	31
36Y435	FE7516	16'	36
36Y436	FE7518	18'	50
36Y437	FE7520	20'	54
36Y438	FE7616	16'	34
36Y439	FE7620	20'	44
36Y440	FE7624	24'	52
36Y441	FE7628	28'	60
36Y442	FE7632	32'	73
36Y443	FE7636	36'	100
36Y444	FE7640	40'	108

**EXTENSION**

**FE1700 - 250 lbs TYPE I**

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y411	FE1716	16'	30
36Y412	FE1720	20'	44
36Y413	FE1724	24'	52
36Y414	FE1728	28'	60

**FE0600 - 225 lbs TYPE II**

36Y407	FE0616	16'	28
36Y408	FE0620	20'	39
36Y409	FE0624	24'	48
36Y410	FE0628	28'	53