

# YES!

WE CAN!

## Antimicrobial Hi-Tech™ Shelving

# MedSafe™

*Medsafe shelving brings together the antimicrobial finish qualities of our Medsafe Locker and the versatility of the Hi-Tech shelving system.*

The Antimicrobial powder-coat finish provides protection against microbes, such as bacteria, mold and mildew for up to 20 years making this versatile shelving ideal for schools, healthcare facilities and any other facility where the spread of microbes is a concern. This aesthetically appealing platinum shelving is available in configurations that can easily accommodate today's shelving needs.

- **Open and closed styles**
- **8-shelf and 11-shelf configurations**
- **Shelves easily adjust on 1-1/2" centers**
- **Boxed formed shelves for added strength**
- **Easy assembly**

*Specially formulated powder coat finish protects against bacteria, mold, yeast & mildew for up to 20 years!*



11 shelves  
open  
starter unit



11 shelves  
closed  
starter unit





### Open Shelving

W	D	H		8-Shelf Unit Catalog No.	11-Shelf Unit Catalog No.	Shelf Capacity*
36	12	87	Starter	14C751	14C775	500
36	12	87	Adder	14C752	14C776	500
36	18	87	Starter	14C753	14C777	500
36	18	87	Adder	14C754	14C778	500
36	24	87	Starter	14C755	14C779	500
36	24	87	Adder	14C756	14C780	500
48	12	87	Starter	14C757	14C781	375
48	12	87	Adder	14C758	14C782	375
48	18	87	Starter	14C759	14C783	375
48	18	87	Adder	14C760	14C784	375
48	24	87	Starter	14C761	14C785	350
48	24	87	Adder	14C762	14C786	350

\*Shelf capacity based on a uniformly distributed load and a safety factor of 1.65

Starter Unit: Consists of two beaded front posts, two back angle posts, one back sway brace assembly and two side sway brace assemblies Adder Unit: Consists of one beaded front post, two back angle posts, one back sway brace assembly and one side sway brace assembly

### Closed Shelving

W	D	H		8-Shelf Unit Catalog No.	11-Shelf Unit Catalog No.	Shelf Capacity*
36	12	87	Starter	14C763	14C787	500
36	12	87	Adder	14C764	14C788	500
36	18	87	Starter	14C765	14P335	500
36	18	87	Adder	14C766	14P336	500
36	24	87	Starter	14C767	14P337	500
36	24	87	Adder	14C768	14P338	500
48	12	87	Starter	14C769	14P339	375
48	12	87	Adder	14C770	14P340	375
48	18	87	Starter	14C771	14P341	375
48	18	87	Adder	14C772	14P342	375
48	24	87	Starter	14C773	14P343	350
48	24	87	Adder	14C774	14P344	350

\*Shelf capacity based on a uniformly distributed load and a safety factor of 1.65

Starter Unit: Consists of two beaded front posts, two back angle posts, one back panel assembly and two side panel assemblies

Adder Unit: Consists of one beaded front post, two back angle posts, one back panel assembly and one side panel assembly