

JOBBOX[®]

STEEL UNDERBED BOXES

**NEW &
IMPROVED
DESIGN**




Unmatched Security, Versatility and Durability

DROP DOWN DOOR

- Exclusive new design allows door to drop down out of the way for easier loading and unloading of large, heavy or awkward equipment

QUICK-RELEASE KEYWAY CONNECTORS

- Connectors allow the door end of the support cable to be easily and quickly disconnected to allow the door to drop down



3-POINT LOCKING SYSTEM

- System locks the door at the top and both sides for strength and security. It draws the high-strength door tight against the bulb-shaped weather stripping to seal out moisture and dust



EXTENDED RAIN GUTTER

- 3/4" wide rain gutter surrounds to door opening to channel moisture around the opening to protect the contents



ROTATING T-HANDLE

- T-handle draws the door tight against the weather stripping and locks at 3-points. Reinforced cam lock for superior security



PREMIUM STORAGE SOLUTIONS



Steel Models Available in Armor-Brite White or Black Powder Paint

Model #	UPC	L	W	H	Shipping Cu. Ft.	Shipping Wt. (Lbs.)
---------	-----	---	---	---	------------------	---------------------

14" Tall Black Steel Underbed Boxes

727980	0-43419-91279-3	24"	12"	14"	2.9	49.0
728980	0-43419-91280-9	36"	12"	14"	4.4	67.0
729980	0-43419-91281-6	24"	16"	14"	3.8	55.0
731980	0-43419-91283-0	36"	16"	14"	5.6	76.0

18" Tall Black Steel Underbed Boxes

732980	0-43419-91284-7	18"	18"	18"	4.0	55.0
733980	0-43419-91285-4	24"	18"	18"	5.3	68.0
734980	0-43419-91286-1	30"	18"	18"	6.6	80.0
735980	0-43419-91287-8	36"	18"	18"	8.9	92.0
738980	0-43419-91290-8	48"	18"	18"	10.5	117.0
739980	0-43419-91291-5	60"	18"	18"	13.1	142.0
740980	0-43419-91292-2	72"	18"	18"	15.7	168.0

24" Tall Black Steel Underbed Boxes

748980	0-43419-91300-4	24"	24"	24"	9.1	94.0
749980	0-43419-91301-1	30"	24"	24"	11.4	110.0
750980	0-43419-91302-8	36"	24"	24"	13.6	126.0
752980	0-43419-91304-2	48"	24"	24"	18.0	158.0
754980	0-43419-91306-5	60"	24"	24"	22.7	190.0



UNDERBED MOUNTING BRACKETS

Heavy-Duty 2" C-Channel Brackets have multiple holes for easy installation. Sold in pairs.

18" x 18"—Model 228000
24" x 24"—Model 229000


INDUSTRIAL-GRADE STEEL HINGES

- Rugged 3" long, 7/8" outside diameter hinges with 1/2" diameter stainless steel pin



ONE-PIECE LOCK HOUSING

- Heavy-duty steel housing covers the locking system and locking rods to prevent damage and jamming. Housing adds extra strength to the door



Model #	UPC	L	W	H	Shipping Cu. Ft.	Shipping Wt. (Lbs.)
---------	-----	---	---	---	------------------	---------------------

18" Tall White Steel Underbed Boxes

741980	0-43419-91293-9	18"	18"	18"	4.0	55.0
742980	0-43419-91294-6	24"	18"	18"	5.3	68.0
743980	0-43419-91295-3	30"	18"	18"	6.6	80.0
744980	0-43419-91296-0	36"	18"	18"	7.9	92.0
745980	0-43419-91297-7	48"	18"	18"	10.5	117.0
746980	0-43419-91298-4	60"	18"	18"	13.1	142.0
747980	0-43419-91299-1	72"	18"	18"	15.1	168.0

www.deltastorage.com

Delta Consolidated Industries, Inc.
 PO BOX 1846 Jonesboro, AR 72403-1846
 800-643-0084 • Fax 877-356-1879

All information on this sheet is subject to change without notice. 09/10_5K
 For ordering, use Part# LIT155 © 2009 Delta Consolidated Industries, Inc.