

DESCRIPTION

TFW™ Multipurpose Thread Sealant with PTFE is a nonhardening soft set, nontoxic thread sealant for sealing and protecting NPT pipe fittings. **TFW™** is specially formulated to seal piping used for pressurized air, natural gas, water, and fire sprinkler systems. **TFW™** works as well in other fluid and air applications.

TFW™ provides sealing performance upon application and is specifically formulated to seal threaded connections against leakage due to internal pressure.

TFW™ contains no lead or harmful metals and is safe for use on potable water lines. **TFW™** is listed under the Uniform Plumbing Code (IAPMO), File Number 1282. **TFW™** conforms to Federal Specification TT-S-1732 and the requirements of British Standard 6920: Parts 1 and 2.

TFW™ is FBC™ System Compatible.*

- Contains PTFE
- Seals upon application
- Nontoxic
- Nonstaining
- Conforms to AB 1953 lead requirements
- For use with potable water and a wide range of other products including liquids and gases

* FBC™ System Compatible indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster®, and Corzan® pipe and fittings.

FBC™, FlowGuard Gold®, BlazeMaster®, and Corzan® are licensed trademarks of the Lubrizol Corporation.

PRODUCT CHARACTERISTICS

Fluid Type	Synthetic
Color / Appearance	White grainy paste
Specific Gravity	1.20
Density (lb/gal)	10.0
Oil Separation	<5.0
WT. % LOSS @ 212°F (100°C)	
Flash Point (ASTM D-92)	>350°F (177°C)
Nonvolatile Content	100%
Copper Strip Corrosion (ASTM D-4048)	1A
Viscosity, Brookfield ASTM D2196	140k - 240k cps
#7 spindle, 5 rpm @ 77°F (25°C)	
VOC	0 g/L
Brushable To	0°F (-18°C)
Service Rating:	
Temperatures to:	500°F (260°C)
Pressures to:	10,000 psi liquids 2,000 psi gases

PACKAGING

Code No.	Container Size	Container
24055	¼ pt.	Brush Top Can
24002	½ pt.	Brush Top Can
24004	1 pt.	Brush Top Can
24007	2 qt.	Plug Top Can
24023	1 gal.	Pail
24015	5 gal.	Pail
24024	15 gal.	Drum
24029	50 gal.	Drum

LIMITED WARRANTY

Jet-Lube, Inc. makes the Limited Express Warranty that at the date of delivery, this product shall be free from defects in Jet-Lube, Inc. materials and workmanship.

This Limited Express Warranty is expressly in lieu of any other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, and of any other obligation on the part of Jet-Lube, Inc.

The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and Jet-Lube, Inc. shall not be liable for incidental or consequential damages.

