

PIG® Grippy® Absorbent Mat Roll

#MAT1625 - 16" x 25'



The only absorbent mat with Grippy backing stays put no matter what! Exclusively from New Pig.

- Specially formulated, full-coverage adhesive backing holds tight but leaves no residue; eliminates the need for tapes and trays
- Peels up easily for quick changeouts; reduces cleanup time for a more productive facility
- Eight layers of fine-fiber polypropylene safely absorb leaks, drips and overspray of oils, coolants, solvents and water to keep liquids from being tracked around
- No curling or bunching; lies flat to reduce trip hazards around workstations, walkways and machinery
- Poly backing creates a liquidproof barrier that keeps floors completely dry
- Tough, spunbond top layer with heavy-duty zigzag stitching stands up to foot and light-wheeled traffic as well as heavy equipment driveovers
- Dark color hides grime so mat stays down longer
- When used as part of your floor safety program, high-traction surfaces such as PIG Grippy Mat have been proven to reduce slip-and-fall claims by as much as 90%
- Tested and certified by the National Floor Safety

Always in stock. Ships within 24 hours.



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT1625 - Pg 1 of 2

MAT1625 Specifications

Color:	Blue
Dimensions:	16" W x 25' L
Mat Weight:	Medium-weight
Fluids Absorbed:	Oils, Coolants, Solvents & Water
Recycled Content:	40% Recycled Content
Absorbency:	Up to 2 gal. per roll
Dispenser:	No
Perforated:	No
Poly-Backing:	Yes
UV Resistant:	No
Sold as:	1 roll
Weight:	4.25 lbs.
New Pig Patent:	Patent Pending
# per Pallet:	130
Composition:	Absorbent - Polypropylene with Polyester Stitching Backing - Proprietary Material
UNSPSC:	47131901

MAT1625 Metric Equivalent

Dimensions:	40.6cm W x 8m L
Absorbency:	Up to 7.6 L per roll
Weight:	1.9 kg

Technical Information

Warnings & Restrictions:

Grippy® Notice

Please note: all adhesives have some potential to lift finish coatings or paint depending on the condition and age of the floor surface. Grippy® Mat is formulated to work with most common industrial floor surfaces, but if you have questions about the suitability of Grippy® Mat for your application, test a 6" x 6" piece in a noncritical area before use.

Certifications, Approvals and Ratings:

NFSI Certified
ANSI B101.1- 2009

Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT1625 - Pg 2 of 2