

PIG® Barrel Top Absorbent Mat

#MAT255 - Heavy-weight • For 55-Gallon Steel/Poly Drum • 25 pads



Shaped to fit on drum tops to keep them clean, these absorbent mats last 2x longer than ordinary mats for fewer change-outs.

- Soak up pump drips without cluttering up your work space with dirty rags!
- Eight layers of 100% polypropylene are thermally bonded to make PIG Mat the strongest mat on the market; won't rip, tear or fray even when saturated
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Absorbs most common industrial liquids - oils, water, solvents, coolants and more
- Absorbed leaks and drips blend right in; dark gray color hides grime so mat stays on the job longer
- Fits dual-bung steel or poly 55-gallon drum; pre-cut with two 3.5" dia. holes to provide a perfect fit
- Heavy-weight construction is highly durable and absorbent to handle pump drips and dispensing spills
- Dispenser box makes it easy to take, carry and store your mat while protecting it from dirt and moisture

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT255 - Pg 1 of 2

MAT255 Specifications

Use With:	55-Gallon Steel/Poly Drum
Color:	Gray
Dimensions:	ext. dia. 22"
Mat Weight:	Heavy-weight
Fluids Absorbed:	Oils, Coolants, Solvents & Water
Recycled Content:	50% Recycled Content
Absorbency:	Up to 5.9 gal. per box
Absorbency per:	Up to 30.2 oz. per pad
Dispenser:	Yes
Pre-cut Holes:	2 (3.5" Dia.)
Sold as:	25 pads per box
Weight:	7.2 lbs.
# per Pallet:	72
Composition:	100% polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



MAT255 Metric Equivalent

Dimensions:	ext. dia. 55.9cm
Absorbency:	Up to 22.3 L per box
Absorbency per:	Up to 893 mL per pad
Weight:	3.3 kg



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT255 - Pg 2 of 2