

STRONG, DURABLE, DEPENDABLE PRODUCTS THAT HAVE BEEN TRUSTED BY THE PROS FOR OVER 65 YEARS

ALUMINUM



AS1106HD



AS3006



AM1106HD



AP1004



AM8006

STEP

AS1100HD - 375 lbs TYPE IAA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y383	AS1106HD	6'	25
36Y384	AS1108HD	8'	30
36Y385	AS1110HD	10'	37
36Y386	AS1112HD	12'	44

AS1000 - 300 lbs TYPE IA

36Y375	AS1003	3'	12
36Y376	AS1004	4'	14
36Y377	AS1006	6'	20
33J650	AS1008	8'	24
36Y378	AS1010	10'	30
36Y379	AS1014	14'	38
36Y380	AS1016	16'	60
36Y381	AS1018	18'	70
36Y382	AS1020	20'	81

STEP

AS3000 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y387	AS3002	2'	6
36Y388	AS3003	3'	10
36Y389	AS3004	4'	13
36Y390	AS3005	5'	15

36Y391 AS3006 6' 17

36Y392	AS3008	8'	23
36Y393	AS3010	10'	28

AS2100 - 250 lbs TYPE I

1CMT1	AS2104	4'	11
1CMR8	AS2106	6'	15
1CMR9	AS2108	8'	22
1CMT5	AS2110	10'	28

AS4000 - 225 lbs TYPE II

36Y394	AS4003	3'	8
36Y395	AS4004	4'	9
36Y396	AS4005	5'	11
36Y397	AS4006	6'	13
36Y398	AS4008	8'	18

TWIN

AM1100 - 375 lbs TYPE IAA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y366	AM1104HD	4'	24
36Y367	AM1106HD	6'	34
36Y368	AM1108HD	8'	42
36Y369	AM1110HD	10'	57
36Y370	AM1112HD	12'	68

L-2431-MR - 375 lbs TYPE IAA - MRI

15G135	L-2431-06MR	6'	24
36Y494	L-2431-08MR	8'	33.6

AM1000 - 300 lbs TYPE IA

33J773	AM1003	3'	16
36Y359	AM1004	4'	18
36Y360	AM1005	5'	22
33J714	AM1006	6'	24
33J715	AM1008	8'	32
36Y361	AM1010	10'	42
36Y362	AM1012	12'	51
36Y363	AM1014	14'	79
36Y364	AM1016	16'	101
36Y365	AM1020	20'	114

PLATFORM

AP1100 - 375 lbs TYPE IAA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
2KMC6	AP1104HD	4'	23
2KMC7	AP1106HD	6'	30
2KMC8	AP1108HD	8'	40

AP1000 - 300 lbs TYPE IA

33J648	AP1004	4'	22
33J649	AP1005	5'	24
33J651	AP1010	10'	42
36Y372	AP1012	12'	64
36Y373	AP1014	14'	75
36Y374	AP1016	16'	85

AP5000 - 300 lbs TYPE IA

33J646	AP5004	4'	42
33J695	AP5006	6'	56
33J696	AP5008	8'	68
33J645	AP5010	10'	82

SAWHORSE

L-2032 - 300 lbs TYPE IA

36Y489	L-2032-02	2'	14
36Y490	L-2032-03	3'	20
36Y491	L-2032-04	4'	24

THE ULTIMATE®

L-2090 - 375 lbs TYPE IAA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
4XZ83	L-2092-13	13'	36
4XZ85	L-2091-17	17'	43

INDUSTRIAL STEP STAND

AY8000 - 300 lbs TYPE IA

1CMV6	AY8001	1'	8
1CMV7	AY8002	2'	14
33J655	AY8002-S55S56	2'	14
5MRG9	AY8003	3'	19
5MRH0	AY8004	4'	24

AIRCRAFT MECHANIC

AM8000 - 300 lbs TYPE IA

33J737	AM8004	4'	22
33J647	AM8006	5'	24
3LW23	AM8008	10'	42
33J738	AM8010	12'	64
33J736	AM8012	14'	75
36Y371	AM8014	16'	85

STRONG, DURABLE, DEPENDABLE PRODUCTS THAT HAVE BEEN TRUSTED BY THE PROS FOR OVER 65 YEARS

ALUMINUM



L-2094-17



AX1008



AE120HD



AE2108



AE2220



AE1660



AE320PG



L-2346-03

SHELF

AH1000 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
33J724	AH1004	4'	6
33J711	AH1005	5'	8
33J643	AH1006	6'	10
33J721	AH1007	7'	11
33J644	AH1008	8'	12
33J726	AH1012	12'	16
33J759	AH1014	14'	20
36Y358	AH1016	16'	23

TRESTLE

AX1000 - 300 lbs TYPE IA

36Y399	AX1008	8'	58
36Y401	AX1010	10'	74
33J712	AX1012	12'	90

MULTI PURPOSE

L-2094 - 300 lbs TYPE IA

36Y492	L-2094-13	10'	35
33J732	L-2094-17	17'	42
33J699	L-2094-22	22'	50

MINI WORKING PLATFORM

L-2241 - 225 lbs TYPE II - ALUMINUM

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y493	L-2241-03	3'	11

EXTENSION

AE1200HD - 375 lbs TYPE IAA

36Y326	AE1216HD	16'	38
36Y327	AE1220HD	20'	42.79
36Y328	AE1224HD	24'	52.03
36Y329	AE1228HD	28'	59.26
36Y330	AE1232HD	32'	73.19
36Y331	AE1236	36'	81.57
33J703	AE1240	40'	90.26
36Y332	AE1248	48'	122

AE2800 - 300 lbs TYPE IA

36Y342	AE2816	16'	32
3LW20	AE2820	20'	39
3LW21	AE2824	24'	46
36Y343	AE2828	28'	59
36Y344	AE2832	32'	66
2KMC1	AE2836	36'	80
2KMC2	AE2840	40'	89

EXTENSION

AE2100 - 300 lbs TYPE IA

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y334	AE2108	8'	15
36Y335	AE2110	10'	18
33J653	AE2112	12'	22
36Y336	AE2114	14'	28
36Y337	AE2116	16'	30
36Y338	AE2118	18'	38
36Y339	AE2120	20'	42

AE2200 - 300 lbs TYPE IA

1CMW4	AE2216	16'	30
1CMW5	AE2220	20'	37
1CMW6	AE2224	24'	44
1CMW7	AE2228	28'	56
1CMW8	AE2232	32'	62
36Y340	AE2236	36'	76
36Y341	AE2240	40'	84

EXTENSION

AE1660 - 250 lbs TYPE I

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y333	AE1660	60'	169

AE3200 - 250 lbs TYPE I

36Y345	AE3216	16'	27
36Y346	AE3220	20'	32
36Y347	AE3224	24'	38
36Y348	AE3228	28'	53
36Y349	AE3232	32'	60
36Y350	AE3236	36'	72
36Y351	AE3240	40'	80

AE3200PG - 250 lbs TYPE I - PROGRIP™

15G128	AE3216PG	16'	27
15G129	AE3220PG	20'	32
15G130	AE3224PG	24'	38
15G131	AE3228PG	28'	53
15G132	AE3232PG	32'	60
15G133	AE3236PG	36'	72
15G134	AE3240PG	40'	80

EXTENSION

AE4100 - 225 lbs TYPE II

ITEM NUMBER	MFR. MODEL	LADDER SIZE	SHIPPING WT. (LBS)
36Y352	AE4110	10'	17
36Y353	AE4112	12'	20
36Y354	AE4114	14'	23
36Y355	AE4116	16'	29
36Y356	AE4118	18'	31
36Y357	AE4120	20'	36

EURO PLATFORM

L-2346 - 250 lbs TYPE I

33J652	L-2346-03	3'	9
--------	-----------	----	---