

# SHELVING UNITS

Lyon has over 100 years of commitment in designing storage systems that help organize, store, and secure products while maximizing workspace.

## T-Post Uprights

Patented design, formed of tough, durable, hot rolled steel affords easy shelf adjustment on 1-1/2" centers using shelf clips.

## Shelf Clips

Quickly lock into place, on either side of uprights. Disengages easily to re-position shelves, no tools needed.

## Open Shelving Section

Ideal for storing packaged stock and other material where high visibility is a concern.

## Closed Shelving Section

Can be used to divide work and storage space into separate areas.

## Shelves

Patented Box "W" design provides added support to the front and rear of the shelf. Lapped and welded shelf corners provide added strength and durability. Available in 22-Gauge Box "W", 20-Gauge Box "W", 18-Gauge Box "W" and 18-Gauge Flanged. Capacity from 300 lbs to 1,300 lbs.



22-Gauge  
Medium-Duty, Box "W"  
shelves provide up to  
600 lb. capacity\*.



20-Gauge  
Heavy-Duty, Box "W"  
shelves provide up to  
900 lb. capacity\*.



18-Gauge  
Extra Heavy-Duty, Box "W"  
shelves provide up to  
1300 lb. capacity\*.



18-Gauge  
Traditional Flanged  
shelves provide up to  
700 lb. capacity\*.

*\*Capacities are based on evenly distributed load. Maximum load capacity: 8000 lbs. per section and a maximum of 18" shelf spacing with no seismic.*

# LYON®



## BULK STORAGE RACK

- Heavy-duty 14-gauge steel beams
- Width and height available in:  
60", 72", 84" and 96"
- Depth sizes are:  
24", 30", 36" and 48"
- Choose between 3 and 4 levels
- Select Decking with capacities up to 1,800 lbs:  
Solid  
Particle Board  
Ribbed  
Waterfall Wire  
Flat Wire Decking



## RIVET RACK

- Beams drop into slots on uprights to create a sturdy, rigid structure
- Choose from heights of:  
39", 60", 72", 84", 96", 120" or 144"
- Beam widths available from:  
12" to 96"
- Select Beams:  
Double-Rivet medium-duty flanged  
"C" Channel, heavy-duty beams
- Select Decking:  
Particle Board or Rivet Rack Wire decking



## CHROME WIRE SHELVING

- Provide up to 600 lbs. loading capacity per shelf. Add 200 lb. capacity casters for mobility and ease of cleaning behind and under shelving unit
- In stock items available for immediate shipment
- Height:  
72" (overall height - 73-1/2")
- Depth:  
24"
- Width:  
24", 36", 48", 60" and 72"

---

# LYON®