

PIG® Universal Light-Weight Absorbent Drum-Top Pad

#25103 - Light-weight • For 55-Gallon Steel Drum • 20 pads



Eliminate messy drum storage areas without touching a mop or rag! Precut to fit on 55-gallon drums, PIG® Drum-Top Pads quickly absorb drips or overfills to help keep your shop clean and safe, so you can focus on repairing vehicles.

- Precut with holes for 3/4" and 2" bungs to provide a perfect fit on steel 55-gallon drum tops
- Soak up overflow and pump drips to keep them off floors without cluttering up your shop with dirty rags
- Eight layers of 100% polypropylene are thermally bonded to make PIG® Mat the strongest mat on the market; won't rip, fray or fall apart, even when saturated
- Highly absorbent material traps liquids, so it won't drip or leave behind fibers when you pick it up; spend less time collecting used absorbent between jobs
- Exclusive dimple pattern speeds wicking of liquid toward dry spots on Mat, so messes disappear fast, cleanup is simple and you use more of each Pad
- Safely absorbs and retains oil, coolants, water, grease, gasoline, solvents, auto fluids, paint overspray, battery acid and most other liquids
- Can be air-dried for reuse when soaked with water or washer fluid
- Dark gray color hides grime, so Mat can stay on the job longer and still look clean
- Light-weight construction has low "cost per toss" for nuisance drips and leaks
- Widemouth Dispenser Box makes Mat easy to access, carry and store while protecting contents from dirt and moisture
- Bulk quantity for supplying multiple drum storage points; hangs for convenience
- Self-extinguishing material helps eliminate fire hazards; melts instead of burning if contacted by direct flame
- Can be wrung out, compacted and/or incinerated after use to better manage waste streams

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: 25103 - Pg 1 of 2

25103 Specifications

Use With:	55-Gallon Steel Drum
Color:	Gray
Dimensions:	ext. dia. 22"
Mat Weight:	Light-weight
Fluids Absorbed:	Oils, Coolants, Solvents & Water
Recycled Content:	50% Recycled Content
Absorbency:	Up to 3 gal. per box
Absorbency per:	Up to 18 oz. per pad
Dispenser:	Yes
Poly-Backing:	No
Pre-cut Holes:	1 (.75" Dia.), 1 (2" Dia.)
Sold as:	20 pads per box
Weight:	3 lbs.
# per Pallet:	64
Composition:	100% polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Technical Documents:

(Available at newpig.com)
Product Data Sheet (PDS)



25103 Metric Equivalent

Dimensions:	ext. dia. 55.9cm
Absorbency:	Up to 11.4 L per box
Absorbency per:	Up to 532.3 mL per pad
Weight:	1.4 kg



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com