



**PB SERIES » MEDIUM ROUND ILLUMINATED**

- 7 Amp rated contacts
- Includes interchangeable green and red lenses
- Red LED on plate
- Stainless Steel single gang plate: 4-1/2" x 2-3/4" [114mm x 70mm]
- UL outdoor rate

**» MODELS**

PART # | Description

<b>PB</b>	PB - Momentary, S.G., DPST, Illuminated w/ Red/Grn Lens
<b>PBA</b>	PB - Alternate, S.G. DPST, Illuminated w/ Red/Grn Lens



**PB2 SERIES » LARGE SQUARE**

- Easy to read 2" size
- 5 Amp rated contacts
- Includes interchangeable green, red and blue ADA lenses
- Stainless steel single gang plate: 4-1/2" x 2-3/4" [114mm x 70mm]

**Product Options**

- Standard or Illuminated
- Single Pole-Double Throw
- Double Pole-Double Throw
- Red LED on plate

**» MODELS**

PART # | Description

<b>PB2</b>	PB - Momentary, Single Gang, Grn/Red/Handicap
<b>PB22</b>	PB - 2", Sq Grn Mom, DP w/Light - SG, Green/Red/Handicap
<b>PB2E</b>	PB - Momentary, Single Gang, Green/Red/Handicap
<b>PB2-LK</b>	Illumination Kit for PB2E, PB5E, EEB2 Series Push Buttons

# PB

## Push Buttons

**Securiton® Quality with a Wide Range of Options for Size, Color and Function**

High-quality Securiton Push Buttons are available in a broad selection of colors, sizes, switch types and outputs. With a wide range of options for interchangeable lenses and field convertible outputs, Securiton push buttons can release any maglock, alone or in conjunction with door closers and other hardware.



**PB3 SERIES » ASSORTED SIZES AND COLORS WITH A UNIFORM LOOK**

- 3 Amp rated contacts
- Includes interchangeable green and red lenses
- Field convertible from DPST to DPDT
- Stainless steel single gang plate: 4-1/2" x 2-3/4" [114mm x 70mm]
- Stainless steel narrow stile plate: 4-1/2" x 1-3/4" [114mm x 44mm]
- Surface mount: 3-7/8" x 2" [98mm x 51mm]
- Red LED on plate

**» MODELS**

PART # | Description

<b>PB3</b>	PB - Momentary, Single Gang, Green/Red Lens
<b>PB3A</b>	PB - Alternate, Single Gang, Grn/Red Lens
<b>PB3AN</b>	PB - Alternate, Narrow, Grn/Red Lens
<b>PB3E</b>	PB - Momentary, Single Gang, Grn/Red Lens
<b>PB3EA</b>	PB - Alternate, Single Gang, Grn/Red Lens
<b>PB3EAN</b>	PB - Alternate Narrow, Grn/Red Lens
<b>PB3EAR</b>	PB - Remote Alternate, Surface Mount Green/Red Lens
<b>PB3EN</b>	PB - Momentary, Narrow Grn/Red Lens
<b>PB3ER</b>	PB - Remote Momentary, Surface Mount Grn/Red Lens
<b>PB3-LK</b>	Illumination Kit, Grn/Red for PB3E/EEB3N Series
<b>PB3N</b>	PB - Momentary Narrow, Green/Red Lens

