

# PIG® Universal Light-Weight Absorbent Drum-Top Pad

#25102 - Light-weight • For 55-Gallon Steel/Poly Drum • 5 pads



Eliminate messy drum storage areas without touching a mop or rag! Precut to fit on 55-gallon drums, PIG® Drum-Top Pads quickly absorb drips or overfills to help keep your shop clean and safe, so you can focus on repairing vehicles.

- Precut with holes for 3/4" and 2" bungs to provide a perfect fit on steel 55-gallon drum tops
- Soak up overflow and pump drips to keep them off floors without cluttering up your shop with dirty rags
- Eight layers of 100% polypropylene are thermally bonded to make PIG® Mat the strongest mat on the market; won't rip, fray or fall apart, even when saturated
- Highly absorbent material traps liquids, so it won't drip or leave behind fibers when you pick it up; spend less time collecting used absorbent between jobs
- Exclusive dimple pattern speeds wicking of liquid toward dry spots on Pad, so messes disappear fast, cleanup is simple and you use each Pad to full capacity
- Safely absorbs and retains oil, coolants, water, grease, gasoline, solvents, auto fluids, paint overspray, battery acid and most other liquids
- Can be air-dried for reuse when soaked with water or washer fluid
- Dark gray color hides grime, so Mat can stay on the job longer and still look clean
- Light-weight construction has low "cost per toss" for nuisance drips and leaks
- be wrung out, compacted and/or incinerated after use to better manage waste streams

Always in stock. Ships within 24 hours.



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: 25102 - Pg 1 of 2

## 25102 Specifications

<b>Use With:</b>	55-Gallon Steel/Poly Drum
<b>Color:</b>	Gray
<b>Dimensions:</b>	ext. dia. 22"
<b>Mat Weight:</b>	Light-weight
<b>Fluids Absorbed:</b>	Oils, Coolants, Solvents & Water
<b>Recycled Content:</b>	50% Recycled Content
<b>Absorbency:</b>	Up to 90 oz. per box
<b>Absorbency per:</b>	Up to 18 oz. per pad
<b>Dispenser:</b>	No
<b>Poly-Backing:</b>	No
<b>Pre-cut Holes:</b>	1 (1.5" Dia.), 1 (2.875" Dia.)
<b>Sold as:</b>	5 pads per box
<b>Weight:</b>	0.61 lbs.
<b># per Pallet:</b>	432
<b>Composition:</b>	100% Polypropylene
<b>UNSPSC:</b>	47131901

## Technical Information

### Warnings & Restrictions:

There are no known warnings and restrictions for this product.

### Technical Documents:

(Available at [newpig.com](http://newpig.com))  
Product Data Sheet (PDS)



## 25102 Metric Equivalent

<b>Dimensions:</b>	ext. dia. 55.9cm
<b>Absorbency:</b>	Up to 2.7 L per box
<b>Absorbency per:</b>	Up to 532.3 mL per pad
<b>Weight:</b>	.3 kg



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304  
© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: 25102 - Pg 2 of 2