


PIG® Oil-Only UV-Resistant Absorbent Mat Pad

#MAT4105 - Heavy-weight • 16" x 20" • 100 pads



Withstands direct sun for up to a year without disintegrating. Absorbs oils and fuels, NOT water.

- Tough spunbond top layer won't rip, tear or fray and is UV resistant up to 12 months; provides long-term outdoor use without degradation
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Absorbs oil and fuels, NOT water
- Bright-white color tells you it's only for oils and fuels and makes absorbed oil easier to see; draws attention to machine leaks and clearly shows saturation level during spill response
- Floats to clean up spills on water
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Easy-tear perforations let you take only what you need, so you use less mat and save money
- Under the UV-resistant top layer is the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Heavy-weight construction is highly durable and absorbent for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT4105 - Pg 1 of 2

MAT4105 Specifications

Color:	White
Dimensions:	16" W x 20" L
Mat Weight:	Heavy-weight
Fluids Absorbed:	Oil-based Liquids But Not Water
Absorbency:	Up to 22 gal. per bag
Absorbency per:	Up to 28.16 oz. per pad
Dispenser:	No
Perforated:	Centered Widthwise
Poly-Backing:	No
UV Resistant:	Yes
Sold as:	100 pads per bag
Weight:	19 lbs.
# per Pallet:	30
Composition:	100% Polypropylene
UNSPSC:	47131901

MAT4105 Metric Equivalent

Dimensions:	40.6cm W x 50.8cm L
Absorbency:	Up to 83.3 L per bag
Absorbency per:	Up to 832.7 mL per pad
Weight:	8.6 kg

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Regulations and Compliance:

40 CFR 122.26 - When applying for a National Pollutant Discharge Elimination System (NPDES) permit, facilities must have a plan in place that describes actions, procedures, control techniques, management practices and equipment available to prevent illegal discharge of pollutants into waterways.

40 CFR 112.7 - SPCC planning requirements state that facilities subject to these regulations must have written plans in place discussing the products, countermeasures and procedures that are in place, or will be taken by the facility to prevent discharge of oil into waters of the United States.

Technical Documents:

(Available at newpig.com)
Product Data Sheet (PDS)
Safety Data Sheet (SDS)



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT4105 - Pg 2 of 2