











	PLATFORM TRUCK		CONVERTIBLE PLATFORM TRUCK		WORK-HEIGHT PLATFORM TRUCK		SIDE PANEL TRUCK		SHEET & PANEL	
										
	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS
SMALL	1,000-2,000 LBS.	36" (L) X 24" (W)	—	—	2,000 LBS.	40.1" (L) X 24.25" (W) X 38.9" (H)	1,000-1,200 LBS.	44" (L) X 24.25" (W) X 39.24" OR 41.5" (H)	2,000 LBS.	38.75" (L) X 24.25" (W) X 38" (H)
MEDIUM	1,200-2,500 LBS.	48" (L) X 24" (W)	750 LBS. AS CART 1,000 LBS. AS PLATFORM	61.5" (L) X 24.25" (W) X 41.1" (H)	2,000 LBS.	52.1" (L) X 24.25" (W) X 40.9" (H)	2,000 LBS.	56" (L) X 24.25" (W) X 41.25" (H)	2,000 LBS.	47.9" (L) X 24.25" (W) X 39.9" (H)
LARGE	1,200-2,500 LBS.	60" (L) X 30" (W)	750 LBS. AS CART 1,000 LBS. AS PLATFORM	61.5" (L) X 24.25" (W) X 44.6" (H)	2,000 LBS.	64.1" (L) X 30.25" (W) X 40.75" (H)	1,200-2,000 LBS.	68.1" (L) X 30.25" (W) X 41.4" (H)	2,000 LBS.	59.9" (L) X 30.25" (W) X 39.9" (H)
EXTRA-LARGE	1,000-2,000 LBS.	70" (L) X 40" (W)	—	—	—	—	—	—	—	—
WHEN TO USE	IDEAL FOR TRANSPORTING A WIDE VARIETY OF BULK GOODS, SUPPLIES, AND MATERIALS EFFICIENTLY THROUGHOUT A FACILITY		VERSATILE SOLUTION THAT CAN BE CUSTOMIZED FROM JOB-TO-JOB TO ELIMINATE THE NEED FOR MULTIPLE TRUCKS TO SAVE MONEY & IMPROVE PRODUCTIVITY		ERGONOMIC HEIGHT PLATFORM TRUCKS IDEAL FOR PULLING STOCK, ASSEMBLY OPERATIONS AND OTHER HEAVY TASKS		IDEAL FOR TRANSPORTING AND RETAINING SMALL PACKAGES AND MATERIALS.		IDEAL FOR MOVING BULKY, HARD-TO-HANDLE ITEMS SUCH AS: SHEET GOODS, DOORS, LUMBER, TABLES, AND MATTRESSES	
MATERIAL	HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)	
CASTER & SIZE OPTIONS	TPR: 6" OR 8" POLYOLEFIN: 6" OR 8" PNEUMATIC: 8"		TPR: 6" ON MEDIUM PNEUMATIC: 8" ON LARGE		TPR: 6" ON SMALL, 8" ON MEDIUM AND LARGE		TPR: 6" OR 8" PNEUMATIC: 8"		POLYOLEFIN: 6" ON SMALL, 8" ON MEDIUM AND LARGE	
COLOR	BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED	
POWDER-COATED METAL	•		•		•		•		•	
HANDLE RETAINER CLIPS	•		•		•		•		•	
TEXTURED DECK SURFACE	•		•		•		•		•	
MOLDED-IN TIE DOWN SLOTS (4)	•		•		•		•		•	

	A-FRAME		CONVERTIBLE A-FRAME		5TH WHEEL WAGON		STANCHION PLATFORM TRUCKS		SEMI-LIVE SKIDS	
										
	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS	WEIGHT CAPACITY	DIMENSIONS
SMALL	2,000 LBS.	35.9" (L) X 24.25" (W) X 43" (H)	—	—	1,200 LBS.	45" (L) X 24.25" (W) X 16.75" (H)	2,500 LBS.	35.9" (L) X 24.25" (W) X 38.9" (H)	2,000 LBS.	35.9" (L) X 24.25" (W) X 12.5" (H)
MEDIUM	2,000 LBS.	47.9" (L) X 24.25" (W) X 44.9" (H)	—	—	2,000 LBS.	56.25" (L) X 24.25" (W) X 17.5" (H)	2,500 LBS.	47.9" (L) X 24.25" (W) X 42.5" (H)	2,000 LBS.	47.9" (L) X 24.25" (W) X 12.5" (H)
LARGE	2,000 LBS.	59.9" (L) X 30.25" (W) X 44.9" (H)	2,000 LBS.	51.13" (L) X 28.13" (W) X 17.25" (H)	2,000 LBS.	70.1" (L) X 30.25" (W) X 17.5" (H)	2,500 LBS.	59.9" (L) X 30.25" (W) X 42.5" (H)	2,000 LBS.	59.9" (L) X 30.25" (W) X 12.5" (H)
EXTRA-LARGE	—	—	—	—	2,000 LBS.	70" (L) X 40" (W) X 21" OR 18.75" (H)	—	—	—	—
WHEN TO USE	IDEAL FOR SAFELY MOVING LARGE, BULKY SHEET AND PANEL GOODS		UNIQUE, CONVERTIBLE DESIGN IDEAL FOR SAFELY MOVING LARGE, BULKY SHEET AND PANEL GOODS AS WELL AS LONG ITEMS LIKE LUMBER AND PIPE		IDEAL FOR MOVING LARGE, HEAVY LOADS IN ALMOST ANY INDOOR AND OUTDOOR ENVIRONMENT		IDEAL FOR MOVING AND STORING LONG, BULKY ITEMS OF ROLL GOODS, PIPE, CARPET, LUMBER AND LINOLEUM		PERFECT FOR TEMPORARY MOVING AND STORING OF MATERIALS, PARTS, AND SUPPLIES	
MATERIAL	HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)	
CASTER & SIZE OPTIONS	POLYOLEFIN: 6" ON SMALL, 8" ON MEDIUM AND LARGE		POLYOLEFIN: 8"		TPR: 10" OR 12" PNEUMATIC: 10", 12" OR 16"		POLYOLEFIN: 6" OR 8"		TPR: 8"	
COLOR	BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED	
POWDER-COATED METAL	•		•		•		•		•	
HANDLE RETAINER CLIPS	•		•		•		•		•	
TEXTURED DECK SURFACE	•		•		•		•		•	
MOLDED-IN TIE DOWN SLOTS (4)	•		•		•		•		•	

PLATFORM TRUCKS

SELECTION GUIDE

To see our complete range of material handling solutions visit our online catalog at rubbermaidcommercial.com

RCP-390
#141734
©2015 Rubbermaid Commercial Products LLC
8900 Northpointe Executive Drive, Huntersville, NC 28078

