

STI Break Glass Stopper®



STI-6100

STI-4130

NOTE: Glass is clear — only appears dark for photo purposes.

PRODUCT OVERVIEW

Accepted by many fire marshals, these versions of the world famous STI Stopper® II are designed for areas where a "break glass" cover is specified, such as unsupervised areas. Each device consists of a red polycarbonate cover, mounting frame, a pane of single-strength clear glass (easily replaced when broken), a glass-breaking bar, screws and anchors for installation. Gaskets are also available to improve weather resistance.

HOW IT WORKS

Three models are available for fire, the smaller STI-6100, the larger STI-4100 and the STI-4130 for surface mount; the STI-4130 is the STI-3100-R conduit spacer and the STI-4100, the spacer will add two inches of depth and accommodate up to ¾" conduit. A fourth "generic" model (STI-6700) is available to cover devices other than manual pull stations. The same size as the STI-6100, it includes a wall mount hanging clip for keys, etc. This model for non-fire applications simply says, "BREAK GLASS."

FEATURES

- Housing is molded of super tough polycarbonate material.
- Aesthetically appealing.
- Fire alarm remains clearly visible and accessible.
- Fast, easy installation.
- Glass replacement is simple.
Suggestion: Order extra panes with each unit, for immediate replacement.
- Accepted by many fire marshals. Obtain local fire marshal approval prior to installation.
- Gaskets available to improve weather resistance.
- Typical working properties of polycarbonate are -40° to 250°F (-40° to 121°C).
- Three year guarantee against breakage of polycarbonate in normal use.

STI Break Glass Stopper®

Dimensions and Technical Information

MODELS AVAILABLE

STI-4100	Break Glass Stopper - large
STI-4130	Kit containing both STI-4100 and STI-3100-R
STI-6100	Break Glass Stopper - small
STI-6700	Break Glass Stopper Keys Under Glass
STI-3100-R	2" Conduit Spacer (red) for STI-4100
SUB-08	Replacement Break Glass Tool
SUB-09	Replacement Glass for STI-6100
SUB-10	Replacement Glass for STI-4100
SUB-67	Replacement Glass for STI-6700 - Reads "Break Glass"
STI-6702	Tamperproof Screw Kit
STI-1280	Backplate for STI-4100
STI-3002	Weather Gasket - large*
STI-3003	Conduit Gasket 1/2"
STI-6501	Weather Gasket - small*

*Gaskets may need to be trimmed prior to installation.


ACCESSORIES

Several accessories are available for the Break Glass Stopper. They include a polycarbonate mounting backplate (recommended for all installations with irregular mounting surfaces), additional spacer for stations with greater depth or exposed conduit and tamperproof screws (STI-4100 only).

NOTE: Local fire marshal approval should be obtained prior to installation.

WARRANTY

Three year guarantee against breakage of polycarbonate in normal use.



Safety Technology International, Inc.

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
Toll-free: 800-888-4784
info@sti-usa.com
www.sti-usa.com

Unit 49G Pipers Road
Park Farm Industrial Estate
Redditch, Worcestershire
B98 0HU England

Tel: 44 (0) 1527 520 999
Fax: 44 (0) 1527 501 999
Free: 0800 085 1678 (UK)
www.sti-europe.com