




## KIMTECH PURE\* W4

### Dry Wipers

**100% Polypropylene.** Recommended for surface wiping in ISO Class 4 or higher cleanroom environments. Suitable for food processing environments.

#### Product Qualities

- 100% Polypropylene base sheet
- Acid-, base-, and solvent-resistant
- Thermally bonded – no glues or binders
- Straight, clean, knife-cut edges minimize lint
- Double-bagged with case liner
- Certificate of Conformance available online at [www.kimtech.com/certificates](http://www.kimtech.com/certificates)




**KIMTECH**  
PURE\* BRAND



## Product Specifications

Characteristic	Specification Target
<b>Particle Generation</b>	
Biaxial Shake, particles $\geq 0.5$ microns	$8.7 \times 10^6/m^2$
Biaxial Shake, fibers $\geq 100$ microns	$1.8 \times 10^9/m^2$
<b>Total Extractables</b>	
Deionized Water	0.15 g/m <sup>2</sup>
Isopropyl Alcohol (IPA, isopropanol)	0.17 g/m <sup>2</sup>
<b>Ions</b>	
Sodium (Na <sup>+</sup> )	57.7 ppm
Potassium (K <sup>+</sup> )	2.7 ppm
Chloride (Cl <sup>-</sup> )	28.1 ppm
<b>Absorbency</b>	
Absorbent Capacity	428 ml/m <sup>2</sup>
Absorbency Rate	1.9 seconds



All tests performed in accordance with IEST RP-CC004.3.

For more information, contact our Customer Technical Helpline at 1-800-851-7538 or e-mail us at [kimtech@kcc.com](mailto:kimtech@kcc.com).

### KIMTECH PURE\* W4 Dry Wipers

Code	Cleanroom Class: ISO / FS209	Delivery System	Color	Material	Size (W x L)	Put-Up	Case Count
33390	4 / 10	Flat / Double Bag	White	Polypropylene	9" x 9"	5/100	500
33330	4 / 10	Flat / Double Bag	White	Polypropylene	12" x 12"	5/100	500



#### Our Guarantee

Your total satisfaction means everything to us. If, for any reason, our products do not meet your expectations, Kimberly-Clark will reimburse you† for your initial purchase, via FREE product, for up to \$1,000.

For more information on KIMBERLY-CLARK PROFESSIONAL\*, visit us online at [www.kcprofessional.com](http://www.kcprofessional.com), contact your Kimberly-Clark Sales Representative, or call us at 1-888-346-GOKC (4652).

† Guarantee extended to consuming end-user accounts only.

Kimberly-Clark warrants that its products comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers. Except to the extent prohibited by applicable law: 1) **THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE**; 2) K-C is not liable for any kind of special, incidental, or consequential damages; and 3) K-C's liability for breach of contract, tort, or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

®/\* Trademarks of Kimberly-Clark Worldwide, Inc. Marques déposées de Kimberly-Clark Worldwide, Inc. The COLOR PURPLE is a Registered Trademark of KCWW. © 2008 KCWW.  
Printed in the USA. K01117 K01980-08-01 06/08