

MODEL 500XL

1/2", 3/4", 1"

LEAD-FREE*



*This product contains a weighted average lead content less than 0.25% for wetted surfaces.

ITEM NO.	DESCRIPTION	1/2"	3/4"	1"
1	MAIN CAP	501-3XL-010F	602-3XL	603-3AXL-010F
2	CAP WASHER	501A-12	503A-13	603A-12A
3	WASHER	—	—	204-14A
4	SPRING	602-33LPVS	602-33LPVS	602-33LPVS
5	PLUNGER	602-34XL	602-34XL	603-34XL
	PLUNGER	602-34XLLP	602-34XLLP	603-34XLLP
	PLUNGER	612-34XL,604C-12, 602B-11	612-34XL,604C-12, 602B-11	613-34XL,604C-12, 602B-11
	PLUNGER	602-34XLCH	602-34XLCH	603-34XLCH
6	SEAT WASHER	502-12	502-12	603-12A
7	WASHER	601-14	502-14	62-14
8	SEAT	601-18	602-18	603-18
9	SEAT GASKET	501A-13	502A-13	603A-13
10	UNION GASKET	601-13	62-13	63-13
11	TAILPIECE NPT (FEMALE)	601-19XL	602-19XL	63-19XL
	TAILPIECE NPT (MALE)	—	602M-19XL	63M-19XL
	TAILPIECE COPPER (FEM)	—	602C-19	63C-19
	TAILPIECE COPPER (MALE)	—	602CM-19XL	63CM-19XL
12	UNION NUT	601-9-010F	62-9-010F	63-9-010F
13	O-RING	011N	WK-111N	113N
	O-RING	011N	113N	113N
14	STEM	501-5XL	602-5XL	603-5XL
	STEM	501-5XL	602-5XLLP	603-5XL
	STEM	501-5XLCH	602-5XLCH	603-5XLCH
15	TEFLON DIAPHRAGM	62-43HT	62-43HT	503-43HT
16	DIAPHRAGM	501-43	501-43	503-43
	DIAPHRAGM	511-43	511-43	513-43
17	DIAPHRAGM DISC	602-80	602-80	603-80
18	BOLT / NUT	501B-9	501B-9	503-11
	BOLT / NUT	501B-9	503-11	503-11
	BOLT / NUT	501B-9SS	501B-9SS	503-11BR
19	SPRING	62-33	62-33	603-33
	SPRING	601-33HR	601-33HR	503-33HR
20	SPRING DISC	602A-80	602A-80	602A-80
21	FRICITION RING	602B-12	602B-12	603B-12
22	WASHER	606C-12	606C-12	606C-12
23	LOCKNUT	501B-9	501B-9	501B-9
	LOCKNUT SS	501B-9SS	501B-9SS	501B-9SS
24	ADJUSTMENT BOLT	602A-11A	602A-11A	602A-11A
	ADJUSTMENT BOLT	602A-11A	602A-11A	603A-11AHR
	ADJUSTMENT BOLT SS	602A-11ASS	602A-11ASS	602A-11ASS

★ REPAIR KIT ITEMS (ALL ★ ITEMS IN KIT)

