

Dayton Grinder Pumps

PUMPS technical data sheet



Submersible Grinder pumps are designed to remove raw sewage wastewater from residential or commercial applications. Grinder pumps macerate solids contained in normal sewage or waste into fine slurry that can be pumped through small diameter piping to a sewage collection / treatment system for final processing. Grinder pumps can lift sewage to high elevations for pressure sewer applications.





11A343
3 HP, Stainless Steel
Submersible Grinder Pump

HP	3
Voltage	230V
Phase	3
Frequency	60 Hz
Run Amps	9A
Start Amps	54A
RPM	3450
Motor Type	3-phase Oil-filled with Class B insulation

Overload Protection	None - Requires Control Panel
Motor Shaft Material	410 Stainless Steel
Motor Housing Material	Cast Iron and 304 Stainless Steel
Motor Duty	Continuous
Motor End Bearing	Single Row Ball
Pump End Bearing	Single Row Ball
Lubrication	Oil Lubricated
Discharge	1-1/4 Inch FNPT, Flanged, Vertical
Volute Material	Cast Iron
Base Material	Cast Iron
Impeller Type	Open Vortex
Impeller Material	Ductile Iron
Hardware Material	Stainless Steel
Cutter and Ring	HRC 58 Chrome Steel
O-rings	Buna-N
Seal Type	Dual Mechanical
Seal Materials	Carbon Ceramic/ Buna-N Silicon Carbide/Silicon Carbide Buna-N
Operation	Manual
Power Cord	14/3 SJTW, 15' (4.6m), Stripped Leads
Max. Solids Handling	1/8" (0.32cm) spherical
Max. Water Temperature	104°F (40°C)
Designed Fluid Environment	Water / Sewage Wastewater


Outline Dimensions



Performance Data

Head	Feet	5	15	25	30	40	50	60	70	91
	Meters	1.5	4.6	7.6	9.1	12.2	15.2	18.3	21.3	27.7
Flow Rate	GPM	55.5	55	54.4	50.2	48.9	47.6	38.3	30	0
	LPM	210	208	206	190	185	180	145	114	0

Performance Chart



WARNING: Use only with nonflammable liquids compatible with pump component materials and in nonflammable/nonexplosive atmospheres.

Call or visit your local branch or go to grainger.com/dayton for complete product line information

Find it at Grainger.

© 2013 W.W. Grainger, Inc.

