

## KNIPEX Cobra® Insulated

High-Tech Water Pump Pliers, Insulated  
DIN ISO 8976 IEC 60900 DIN EN 60900

87  
26

- > adjustment by shifting the jaw directly on to the workpiece: fast, secure and comfortable handling
- > opening at the touch of a button apart from the workpiece
- > fine adjustment for optimum adaptation to different workpiece sizes and comfortable gripping position
- > good access to the workpiece due to slim size in the head and joint area
- > self-locking on pipes and nuts: no slipping off the workpiece and low handforce required
- > gripping surfaces with special hardened teeth, teeth hardness (approx. 61 HRC): low wear and reliable gripping
- > box-joint design: high stability because of double guide
- > pinch guard prevents operators' fingers being pinched
- > chrome vanadium electric steel; forged, multi stage oil-hardened

The adjustment action to adapt to the workpiece is easy and reliable with the KNIPEX Cobra® Insulated: place the upper gripping jaw of the opened pliers on the workpiece, push pliers to close, done!



87 28 250 US


⚠ 1000 V ASTM 



Quick adjustment to the workpiece without using a push-button



Just push the pliers handle to adjust

Product Number	Packaging	↔ Inch mm		Pliers	Head	Handles	⊘ Inch ⊘ mm	⊘ Inch ⊘ mm	Adjustment positions	⚖ lbs
87 28 250 US	X	10 250	⚠ 1000 V ASTM 	grey atramentized	polished	insulated multi-component grips, ASTM-tested	2 50	1 3/4 46	24	0.88

## KNIPEX Raptor™ Pliers

DIN ISO 5743

87  
4

- > for inch and metric nuts and screws with widths across flats from 3/8" - 1 1/4" (10 - 32 mm); self-locking in the range from 11/16" (17 mm): no slipping off the workpiece
- > reliable and tight gripping of rounded, rusty or overly painted nuts and screws
- > ideal for work on vehicle brake systems
- > quick tightening of nuts and bolts using ratchet action
- > adjustment at the touch of a button directly on the workpiece, one-hand operation
- > fine adjustment for optimum adaptation to different size workpieces and a comfortable gripping position
- > box-joint design: high stability because of double guide
- > reliable catching of the hinge bolt: no unintentional shifting
- > favorable lever action: optimum transmission of force
- > pinch guard prevents operators' fingers being pinched
- > replaces a set of wrenches, ideal for tightening locknuts
- > chrome vanadium electric steel; forged, multi stage oil-hardened



87 41 250



The Raptor Pliers combines the convenience of the comfortable push-button adjustment on the workpiece and the function of an all-purpose tightening tool. Jaw gripping with zero backlash prevents slipping on the bolt head or rounding edges.

Even rusty or thick coated bolted connections which have no surfaces capable of being gripped reliably by a conventional wrench can be managed by the exceptionally powerful closing gripping jaws of this wrench.