



**SPECIFICATIONS:**

DOORS SHOWN AS ALUMINUM SHEET STYLE SERVICE DOORS, DOUBLE ACTING, SHALL BE MODEL SD-2000 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING \_\_\_\_\_ WIDE BY \_\_\_\_\_ HIGH.

DOOR SHALL BE CONSTRUCTED OF .063" THICK ALUMINUM.

COMPLETE WITH CHASE GRAVITY-OPERATED E-HINGE SYSTEM WITH HARDENED STEEL CAM AND ROLLER. BOTTOM HINGE CONSISTS OF A HARDENED STEEL CAM SYSTEM. TOP AND BOTTOM HINGES SHALL MOUNT DIRECTLY TO THE BACK EDGE OF A TRIANGULAR FORMED STEEL SHEET.

ACRYLIC VISION PANEL TO BE 1/4" TH. x 9" x 14" SET IN BLACK RUBBER MOLDING (STD).

INCLUDE OPTIONS AS INDICATED BELOW:

- 3-3/4"x8-3/4" HIGH ALUM. JAMB GUARDS
- 3-3/4"x12" HIGH ALUMINUM JAMB GUARDS
- 3-3/4"x18" HIGH ALUMINUM JAMB GUARDS

- IMPACT PLATE (BOTH SIDES):  YES  NO
- STAINLESS STEEL IMPACT PLATES
  - STAINLESS STEEL/GALVANIZED IMPACT PLATES
  - GALVANIZED IMPACT PLATES
  - PLASTIC IMPACT PLATES
- (SPECIFY COLOR:)  FOREST GREEN  JADE  CADET BLUE  WHITE  GRAY  CLOUD GRAY  CHOCOLATE  RED  MEDIUM BROWN  NAVY  ROYAL BLUE  BLACK  BEIGE  BURGUNDY

- IMPACT PLATE HEIGHT:  
 12"  18"  24"  36"  48"

MODEL # SD-2000, BIPARTING SHEET STYLE SERVICE DOOR



©COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 1 800-543-4455 www.chasedoors.com

CUSTOMER INFORMATION:

DATE: 7/14/00 CHASE APPROVAL

FORM # SD4027

REV. C