


Universal Conventional Liners

MIG Welding Accessory

Issued Sept. 2018 • Index No. SPEC L-1.8

**NEW
DESIGN!**

**New! Universal
Conventional Liner**



All Consumables are Not Created Equal.

It's important to choose longer lasting consumables. They can make the difference between repeated consumable replacement and rework, or more arc time and better bottom line.

100% tested prior to shipment to ensure the smoothest wire feed in the industry.

Liners won't gap when bent.

Produced from high carbon music wire which provides longer life.

Compatible with all legacy Q-Gun™, S-Gun™ and T-Gun™ Series MIG Guns as well as the New! Best of the Best (BTB) Platform.

New! Color coded shrink wrap makes it easier to identify liner wire size.

Made with
Pride and without
Compromise in the **USA**

WARNING:
Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Bernard

A Division of Miller Electric Mfg. Co.
449 West Corning Road, Box 667
Beecher, Illinois 60401 USA

Phone: 1-855-MIGWELD (644-9353) (US & Canada)

+1-519-737-3030 (International)

Fax: 708-946-6726

For more information, visit us at BernardWelds.com

BERNARD™

New! Universal Conventional Liners

New! Universal Conventional Liner Part Numbers

Wire Size	Liner Color	10' (3.05m)	15' (4.57m)	25' (7.62m)
.023"-.030"	Yellow	---	L1A-15	L1A-25
.030"-.035"	Green	---	L2A-15	L2A-25
.035"-.045"	White	L3A-10*	L3A-15*	L3A-25*
.045"-1/16"	Red	L4A-10**	L4A-15**	L4A-25**
5/64"	Blue	---	L6A-15	L6A-25
3/32"	Grey	---	L7A-15	L7A-25
7/64" - 1/8"	Black	---	L8A-15	L8A-25

*Standard Liner for .035" & .045" Guns

**Standard Liner for 1/16" Guns

Cross Reference Chart

Wire Size	Old Bernard Part Number			Old Tregaskiss™ Part Number			New! Universal Conventional Liner Part Number		
	10' (3.05m)	15' (4.57m)	25' (7.62m)	10' (3.05m)	15' (4.57m)	25' (7.62m)	10' (3.05m)	15' (4.57m)	25' (7.62m)
.023"-.030"	---	43015	43025	---	415-23-15	---	---	L1A-15	L1A-25
.030"-.035"	---	43015	43025	---	415-30-15	415-30-25	---	L2A-15	L2A-25
.035"-.045"	44110	44115	44125	415-35-10	415-35-15	415-35-25	L3A-10*	L3A-15*	L3A-25*
	43110	43115	43125	---	---	---	L3B-10	L3B-15	L3B-25
.045"-1/16"	44210	44215	44225	415-116-10	415-116-15	415-116-25	L4A-10**	L4A-15**	L4A-25**
	---	43215	43225	---	---	---	---	L4B-15	L4B-25
5/64"	---	44315	44325	---	415-564-15	415-564-25	---	L6A-15	L6A-25
3/32"	---	45415	45425	---	415-332-15	415-332-25	---	L7A-15	L7A-25
7/64"	---	45615	45625	---	615-18-15	---	---	L8A-15	L8A-25
1/8"	---	46715	46725	---	615-18-15	---	---	L8A-15	L8A-25

*Standard Liner for .035" & .045" Guns

**Standard Liner for 1/16" Guns

Replacement Instructions and Service

CAUTION Disconnect gun from equipment, allow to cool and remove electrode from liner before servicing.

Diffuser/Retaining Head Removal

Using the appropriate wrench remove the gas diffuser/retaining head with a counterclockwise rotation.

Universal Conventional Liner Installation

Re-insert liner into power pin with cable laying straight. Continue until liner lock is fully seated into the power pin. A twisting motion may be necessary to seat the o-ring (some power pins may require installation of additional components to secure liner). Making sure the cable is straight, push liner back into gun (back load) and trim liner on front of the gun per diffuser/retaining head part number on the chart to the right. Remove any burr that may obstruct wire feed.

New Liner Trim Lengths		
Centerfire™ Diffuser Part Number	Liner Trim Length	
D-1	9/16"	14.3 mm
D-1T	13/16"	20.6 mm
D-1T-5	13/16"	20.6 mm
DS-1	9/16"	14.3 mm
DS-1T	5/8"	15.9 mm
DW-1	1/4"	6.4 mm
Quik Tip™ Diffuser Part Number	Liner Trim Length	
D114	5/8"	15.9 mm
D114Q	9/16"	14.3 mm
D118	3/4"	19.1 mm
D118Q	3/4"	19.1 mm
D118QLL	1-5/16"	33.3 mm
D1FQ	7/8"	22.2 mm
D218	7/8"	22.2 mm
TOUGH LOCK™ Retaining Head Part Number	Liner Trim Length	
ALL	3/4"	19.1 mm

