

KOBRA®

FAST - FIERCE - FLEXIBLE

**WHY
KOBRA®
HOSES ARE
JUST BETTER
THAN THE REST**

ANATOMY OF THE KOBRA® CHARGING HOSE

NITRILE COVER

KEVLAR BRAID

RUBBER
VENEER TUBE

Provides a 5 - to -1
safety factor - beats the
industry standard: 4 -1



CLE SERIES HOSE

PRESSURE 800 PSI WORKING, 4000 PSI BURST
ABLE TO HANDLE ALL COMMON REFRIGERANTS EXCEPT AMMONIA

LINING KEVLAR®
THE SAME MATERIAL IN BULLET PROOF VESTS MAKES YOUR HOSES STRONG & FLEXIBLE

COVER NITRILE
MORE OIL, UV & OZONE RESISTANT THAN NEOPRENE SO HOSES LAST LONGER

CRIMP FULL CIRCUMFERENCE GRIP
YIELDS MAXIMUM HOLD & UNIFORM SEAL PREVENTING LEAKS & BURSTS

DEPRESSOR BARBED
LOCKS INTO GASKET ELIMINATING BLOW OUTS

DEPRESSOR MACHINED
FOR MAXIMUM FLOW


BARB ANGLED & SELF CENTERING
FOR SMOOTH & EASY ACTION

GASKET KOBRA® HOOD
LOCKS INTO INTERNAL CUP RIDGE TO ELIMINATE BLOW OUTS

FITTING 14 TPI PITCH KNURL
COMFORTABLE GRIP FOR EASY TURNING AND IMPROVED FINGER-TIGHT SEALING

ORIGIN PRECISELY MACHINED
AT OUR FACILITY IN AURORA, IL USA FOR A FULLY REBUILDABLE & RELIABLE HOSE

CLE KOBRA® CUT AWAY



The KOBRA® CLE features a straight edged hood that snaps into the straight edge of the barb. This edge-to-edge force eliminates blow outs.

The depressor locks into the gasket. The depressors outward force pushes the gasket further into place, preventing blow outs.

AMERICAN
MADE

JB INDUSTRIES

www.jbind.com 800.323.0811 sales@jbind.com



TM.