















**Frame Modules and Modular Connector Fittings** Inches (mm)

1. Choose Plate Frame	Description	Color	HBL4750 Series		HBL6750 Series	
	Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only. Use KPIMBZAL/GY plate with modules for HBL4750 and HBL6750 Series device mounting bracket located on page S46. See Section T for additional Hubbell iSTATION modules and datacom products. <i>Note: Each gang accepts 3 module units.</i>	Gray Ivory		<b>IMF1GY</b> <b>IMF1EI</b>		<b>IMF2GY</b> <b>IMF2EI</b>

2. Choose Modules	Color	Catalog No.	Catalog No.	Catalog No.	Catalog No.
	Gray Ivory	 <b>IMB05GY</b> <b>IMB05EI</b> Blank Module .5 Unit	 <b>IMB1GY</b> <b>IMBEI</b> Blank Module 1 Unit	 <b>IMB15GY</b> <b>IMB15EI</b> Blank Module 1.5 Unit	
	Gray Ivory	 <b>IM1K1GY</b> <b>IM1K1EI</b> Modular Flat 1 Unit	 <b>IM2K1GY</b> <b>IM2K1EI</b> Modular Flat 1 Unit	 <b>IM1KA15GY</b> <b>IM1KA15EI</b> Modular Angled 1.5 Unit	 <b>IM2KA15GY</b> <b>IM2KA15EI</b> Modular Angled 1.5 Unit
	Gray Ivory	 <b>IM1SCA15GY</b> <b>IM1SCA15EI</b> SC 1 Duplex Angled, 1.5 Unit	 <b>IM2SCA2GY</b> <b>IM2SCA2EI</b> SC 2 Duplex Angled, 2 Unit	 <b>IM1IA15GY</b> <b>IM1IA15EI</b> Modular Recessed 1.5 Unit	 <b>IM2IA15GY</b> <b>IM2IA15EI</b> Modular Recessed 1.5 Unit
<b>Keystone Opening</b> Hole size for mounting all Hubbell jacks  A: .580" (14.73) B: .760" (19.30)					

Modular connectors to be used with any plate with a standard modular opening. Not recommended for use with KP plates. For KP applications use KPIMBZAL/GY bezel and appropriate Hubbell iSTATION modules located in the Section T. Use appropriate Hubbell iSTATION modules for SC fiber adapters. See Section T for additional modular connectors.

Modular Connector Fittings	Color	Catalog No.	Catalog No.	Catalog No.
	Gray Ivory	 <b>SFFGGY</b> <b>SFFGEI</b> F-Type Coupler Gold	 <b>SFFGX</b> <b>SFFEX</b> F-Type Coupler Nickel	 <b>SFBG10</b> <b>SFBGE10</b> Blank (10 Pack)
	Gray Ivory	 <b>SFRCRFFGY</b> <b>SFRCRFFEI</b> RCA Gold Pass-through F/F Coupler Red Insulator	 <b>SFRCWFFGY</b> <b>SFRCWFFEI</b> RCA Gold Pass-through F/F Coupler White Insulator	 <b>SFRCYFFGY</b> <b>SFRCYFFEI</b> RCA Gold Pass-through F/F Coupler Yellow Insulator
	Black	 <b>SFSV110BK</b> S-Video 110, Black	 <b>SFSVBK</b> S-Video F/F Coupler	 <b>SFSPGBK*</b> <b>SFSPGR**</b> Speaker Post Connector
Black housing only	 <b>SFRC110R</b> RCA 110 Punchdown Red Insulator	 <b>SFRC110W</b> RCA 110 Punchdown White Insulator	 <b>SFRC110Y</b> RCA 110 Punchdown Yellow Insulator	

\*Office White housing with black ring color  
 \*\*Office White housing with red ring color

Modular Jacks	Color	Catalog No.	Catalog No.	Catalog No.
	See below	 <b>HXJ5E</b> Cat 5e, T568A, T568B, RJ45	 <b>HXJ6</b> Cat 6, T568A, T568B, RJ45	 <b>HXJU</b> 6 Position USOC, RJ25

**xx** = Color: **BK** (Black), **B** (Blue), **GY** (Gray), **GN** (Green), **EI** (Ivory), **OW** (Office White), **OR** (Orange), **R** (Red), **W** (White), or **Y** (Yellow)