

## **Dual Moisture Meter, Pin/Pinless** Model R6018



TECHNICAL DATA

Pin Mode: 5 to 50% (wood); 1.5 to 33% (building materials) Pinless Mode: O to 99.9% (wood and building materials)

Pinless mode: up to 1" (25mm) Pin Mode: +/-(3% + 5 dqt.)

Pin mode: 0.3" (8mm)

(Contact Pins/Pinless)

Audible tone (increased

0.1%

Yes

Yes

Yes

CE

**Dual Function** 

LCD Display





### Features

- Pin and Pinless functions detect moisture in wood and building materials (sheet rock, cardboard, plaster, concrete and mortar)
- Pinless measurement depth up to 1" (25mm)
- Classifies moisture status as: low, medium and high
- Audible alert and Data Hold functions
- Built-in measurement verification and battery check
- · Low battery indicator and auto shut-off
- Replaceable pins
- Includes pins, protective cap and battery

### **Specifications**

Measuring Ranges:

Depth Detection:

Accuracy: **Resolution:** Sensor Type:

Display: Data Hold: Audible Alert Indicator:

**Replaceable Pins:** Auto Shut-off: Low Battery Indicator: Power Supply: Product Certifications: Operating Temperature: Storage Temperature: **Operating Humidity:** Dimensions:

Weight:

# intensity as moisture level rises) Yes (after 2 mins) 9V Battery

41 to 113°F (5 to 45°C) 32 to 122°F (O to 50°C) O to 80% 6.7 x 2.6 x 1.2" (170 x 65 x 30mm) 4.2 oz (120g)

### **R6018-KIT**

Water Damage/Restoration Kit Includes: R6018 Dual Moisture Meter, 8706 Digital Psychrometer, and C-820 Carrying Case



Model	Description
R6018	Dual Moisture Meter, Pin/Pinless
R6018-KIT	Water Damage/Restoration Kit
R6018-P	Replacement Electrode Pins
CA-05A	Soft Carrying Case

### **REED Instruments** 1-877-849-2127 | info@reedinstruments.com | www.reedinstruments.com