



Item Number 16N196

10" BENCH DRILL PRESS



FEATURES	ADVANTAGES	BENEFITS
V-Belt Drive System	Step pulley belt drive transmission delivers 5 different speeds Easy to use belt tension release system	Simple belt speed changes Delivers performance at an economical price
Cast Iron Construction	Better vibration absorption Minimal deflection	Improved performance
Spindle supported by high quality ball bearings	Provides maximum rigidity Minimal deflection	Improved accuracy Longer tool life
Cast iron table with rack and pinion table raiser	Easy adjustment of table height Quick, safe set-ups	Greater operator convenience and safety Improved productivity
table tilts 45° to the right and swivels 360° around the column	Table tilts for all angle drilling applications Table swings around the column to allow drilling operations on larger workpieces secured to the drill press base	Greater versatility Improves efficiency Improved productivity
1/2" through table and base slots	Faster & simpler set-ups Easier clamping of workpiece or vise	Improves efficiency & productivity Greater operator convenience & safety
Laser alignment	The laser beam allows operator to view the drill bit path on the workpiece for proper alignment prior to drilling	Faster set-ups Increased efficiency Greater accuracy Greater operator convenience
Spindle depth stop	Easy to set Easy to read	Faster set-ups Increased efficiency Greater accuracy Greater operator convenience
Front mounted safety, paddle on/off switch	Positioned for easy access & use	Greater operator safety and convenience
3 Spoke quill feed handles	Provides for easy, fast manual feeding of cutting tool into the workpiece Proper size to maximize required thrust needed for drilling operations	Improves cutting tool performance Improves efficiency Greater operator convenience & safety