

TECHNICAL DATA

Features

- Detects very low levels of microwave leakage
- Quick response and high accuracy
- Designed for one-handed operation
- Audible (beep) and visual (flashing LED) alarms at 5 mW/cm²
- 4-digit, backlit LCD display
- Max hold function and low battery indicator
- Zero button for quick adjustment
- Includes soft carrying case and battery

Specifications

| | |
|------------------|------------------------------|
| Measuring Range: | 0 to 9.99 mW/cm ² |
| Accuracy: | ±1mW/cm ² |
| Resolution: | 0.01 mW/cm ² |

General Specifications

| | |
|-------------------------|--------------------------------------------|
| Display: | 4-digit LCD |
| Backlit Display: | Yes |
| Alarm: | Audible (buzzer) and Visual (LED Light) |
| Alarm Limit: | 5 mW/cm ² |
| Max Hold: | Yes |
| Zero Button: | Yes |
| Response Time: | 2x per sec. |
| Power Supply: | 9V Battery |
| Low Battery Indicator: | Yes |
| Product Certifications: | CE |
| Operating Temperature: | 32 to 122°F (0 to 50°C) |
| Storage Temperature: | 14 to 140°F (-10 to 60°C) |
| Operating Humidity: | 10-90% |
| Dimensions: | 6.3 x 2.4 x 1.7" (160 x 60 x 42mm) |
| Weight: | 5.3 oz (151g) |



| Model | Description |
|--------|----------------------------|
| R9200 | Microwave Leakage Detector |
| CA-52A | Soft Carrying Case |