

SHOWA

# S-TEX 541

Reinforced with a stainless steel liner, our patented Hagane Coil technology, and a polyurethane palm coating, S-TEX® 541 hides grime while providing top of the line defense against cuts and lacerations.

## FEATURES

- High performance engineered patented yarns
- Engineered Hagane Coil® fibre
- ANSI cut resistance level: A4
- EN388 cut resistance level: 3
- ISO 13397 cut resistance level: D
- Open back design
- Anatomical hand shape design
- Seamless knit

## BENEFITS

- Better advanced cut protection performance
- High Cut Resistance performance
- Lightweight palm coating ensures maximum dexterity, grip and flexibility
- PU coating provides high abrasion resistance and excellent grip
- Open back design with breathable palm keeps the hand comfortable and dry
- An ergonomically designed hand mould replicates the natural curvature of the human hand and thus reduces hand fatigue
- Seamless knitting gives no irritation

## INDUSTRY



**Airports & Ports**



**Automotive**



**Construction**



**Electronics**



**Glass**



**Manufacturing**



**Mechanical**



**Metallurgy**

## IDEAL APPLICATIONS

- Handling heavy equipment
- Mechanical engineering
- Mechanical and engineering
- Screw and nail setting
- Intricate parts handling
- Handling glass and windows
- Canning
- HVAC



## MATERIAL

- Polyester
- Seamless knit
- Stainless steel

## COATING

- Polyurethane

## GRIP

- Rough

## STANDARDS



0120

ANSI / ISEA  
105-2016



CUT

EN 388:2016



4X41D

ANSI / ISEA  
105-2016



PUNCTURE

SHOWA

# S-TEX 541



**PACKAGING**

- 12 Pair per polybag
- 6 Polybags per case
- 72 Pair per case



**SIZES**

- S
- M
- L
- XL
- XXL



**COLOUR**

- Black w/ gray coating



[ YOU MIGHT ALSO BE INTERESTED IN

SHOWA  
**S-TEX 350**



**MATERIAL**  
Polyester  
**COATING**  
Nitrile

SHOWA  
**546**



**MATERIAL**  
Engineered yarn  
**COATING**  
Polyurethane

SHOWA  
**S-TEX 581**



**MATERIAL**  
Kevlar  
**COATING**  
Foam nitrile

SHOWA  
**540**



**MATERIAL**  
HPPE  
**COATING**  
Polyurethane

[ **USER INSTRUCTIONS**

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[ **DISCLAIMER**

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

**Get in touch**

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved