Honeywell Miller Titan[™] II Harnesses & Lanyards Enhanced Adjustability for Improved Comfort



- Easier vertical adjustability that stays in place, slip resistant back D-ring pad and forward positioned side D-rings, keeping your tool bags in the right place
- More comfort and better fit with lighter, strategically-placed padding that provides optimal airflow
- Increased worksite safety with Hi-Viz color webbing and ANSI Z359.11 compliance
- Quick availability with in-stock items



by Honeywell

Miller Titan[™] II Harnesses

Enhanced Adjustability for Improved Comfort

The new economical Miller Titan[™] II line of harnesses offers enhanced adjustability, improved comfort and increased worksite safety. This next generation of Titan harnesses from Honeywell Industrial Safety is an affordable fall protection solution for the general construction, manufacturing and oil & gas (refinery) markets.

- Expanded Product Line
- New ANSI Z359.11 Compliant
- Maximum capacity 400-lbs. (181.4 kg)

NEW Vibrant. **Hi-Viz Webbing:**



Titan[™] II T-Flex **Stretch Webbing**

Patented stretchable elastomer embedded into tough interwoven webbing provides improved comfort and greater mobility.



Non-Stretch Webbing Durable, lightweight webbing.

that provides optimal airflow

while working at heights.

Back D-Ring Pad

Non-slip design allows back D-Ring to stay in position

Self-Contained Label Pack Integrated pack encapsulates labels, minimizing damage and loss

Pull-Free Lanyard Rings Attach lanyard when not in use to minimize tripping hazards



Oversized ID Tags Quick and easy harness size identification

Friction Buckles Easy to adjust, non-slip design



Optional Front D-Ring Used for ladder climbing, confined space, rescue or suspension applications



Optional Side D-Rings Used for positioning or restraint





Double Slot Side D-Rings

Forward position allows for tools to be placed conveniently at your side

Titan[™] II **TITAN[™] II CONTRACTOR Construction-Style Harness** Designed for more comfort and better fit with lighter, strategically-placed padding





Offers optimal airflow allowing for increased comfort while carrying a full load of tools

Tool Belt Stays in position when disconnected, even when tools are attached

TF4500/UAK



TITAN [™] II NON-STRETCH	TITAN [™] II CONTRACTOR				
T2000/UAK	T4000/UAK	T4007/UAK	T4500/UAK	T4507/UAK	T4577/UAK
T2007/UAK	T4000FD/UAK	T4007FD/UAK	T4500FD/UAK	T4507FD/UAK	
Shown above T2000/UAK	TITAN [™] II T-FLEX				
	TF4000/UAK	TF4007/UAK	TF4500/UAK	TF4507/UAK	
	TF4000FD/UAK	TF4007FD/UAK	TF4500FD/UAK	Shown above	
	Shown above T4000/UAK	Shown above T4007/UAK	Shown above T4500/UAK	T4507/UAK	

TITAN™ II NON-STRETCH HARNESS	TITAN™ II T-FLEX HARNESS				Chest	Shoulder	Leg	Shoulder/	
SKU	SKU	Back D-Ring	Front D-Ring	Side D-Rings	Strap Buckles	Strap Buckles	Strap Buckles	Waist Padding	Removable Tool Belt
T2000/UAK	N/A	Yes	No	No	Mating	N/A	Mating	No	No
T2007/UAK	N/A	Yes	No	Yes	Mating	N/A	Mating	No	No
T4000/UAK	TF4000/UAK	Yes	No	No	Mating	Friction	Mating	No	No
T4000FD/UAK	TF4000FD/UAK	Yes	Yes	No	Mating	Friction	Mating	No	No
T4007/UAK	TF4007/UAK	Yes	No	Yes	Mating	Friction	Mating	No	No
T4007FD/UAK	TF4007FD/UAK	Yes	Yes	Yes	Mating	Friction	Mating	No	No
T4500/UAK	TF4500/UAK	Yes	No	No	Mating	Friction	Tongue	No	No
T4500FD/UAK	TF4500FD/UAK	Yes	Yes	No	Mating	Friction	Tongue	No	No
T4507/UAK	TF4507/UAK	Yes	No	Yes	Mating	Friction	Tongue	No	No
T4507FD/UAK	N/A	Yes	Yes	Yes	Mating	Friction	Tongue	No	No
TITAN [™] II CONTI	RACTOR HARNESS								
T4577/UAK	N/A	Yes	No	Yes	Mating	Friction	Tongue	Yes	Yes

SKU numbers listed are for Universal (Lg./XL) size. Harnesses are also available in small/medium, XXL and XXXL, by replacing the "U" in the SKU number with "S/M", "XXL" or "XXXL" (Ex: T4000/XXLAK).

Miller Titan[™] II Lanyards

Economical with Quick Availability

The new Miller Titan[™] II line of lanyards is economical and features Hi-Viz color for increased worksite safety and quick availability with in-stock items. All connectors are rated at 3,600-lb. gate-strength.





T5111SS-Z7/6FTAF









Harness Connection	Anchorage Connection	Standard Length*
ORBING LANYAR	DS	
Locking snap ho		6-ft. (1.8 m)
Locking snap ho	ok Locking snap hook	6-ft. (1.8 m)
Locking snap ho	ok Locking snap hooks	6-ft. (1.8 m)
Locking snap ho	ok Large locking rebar hook	6-ft. (1.8 m)
t. <i>(3 m)</i> . Locking Snap H	ook — 3/4-in. <i>(19 mm)</i> gate opening. Large loc	king rebar hook – 2-1/2-in. <i>(64 mm)</i> gate opening.
JILT-IN SHOCK-A	BSORBING LANYARDS	
Locking snap ho	ok Large locking rebar hooks	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
Locking snap ho	ok Locking snap hook	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
Locking snap ho		Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
Locking snap ho	· · · · · · · · · · · · · · · · · · ·	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
·····	······································	king rebar hook – 2-1/2-in. <i>(64 mm)</i> gate opening.
SORBING LANY	RDS	
Locking snap ho		6-ft. (1.8 m)
Locking snap ho		6-ft. (<i>1.8 m</i>)
Locking snap ho		6-ft. (<i>1.8 m</i>)
Locking snap ho		6-ft. (1.8 m)
		cking rebar hook – 2-1/2-in. <i>(64 mm)</i> gate opening.
SHOCK ABSORBI		
Locking snap ho		Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
Locking snap ho		Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
Locking snap ho		Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)
Locking snap ho	<u> </u>	Contracts 6-ft. (1.8 m) to 4-ft.(1.2 m)
		cking rebar hook – 2-1/2-in. <i>(64 mm)</i> gate opening.
DS		
Locking snap ho	ok Locking snap hook	6-ft. (1.8 m)
Locking snap ho	······	6-ft. (1.8 m)
······		king rebar hook – 2-1/2-in. <i>(64 mm)</i> gate opening.
with Pack-Type S		
Locking snap ho		6-ft. (1.8 m)
LUCKING Shap no	Forged sliding D-rings	0-1t. (<i>1.0 III</i>)
Locking snap ho	ok Auto-lock carabiner; Forged sliding D-ring	6-ft. <i>(1.8 m)</i>
ft. <i>(3 m)</i> . Locking Snap	Hook — 3/4-in. <i>(19 mm)</i> gate opening. Large lo	cking rebar hook – 2-1/2-in. (64 mm) gate opening.
ft. (3 m). L	Locking Snap H	g snap hook Auto-lock carabiner;

An connectors include 3,000-ID, gate-strength. An while brand fail protection products meet applicable OSHA, ANSI and USA requirements. For CSA 2259 models, when ordering add a "C" at the end of the model number, ie.: T5122-Z7/6FTAFC, with the exception of T9111W-Z7/6FTAF, T9112W-Z7/6FTAF in which the SKU does not change to meet CSA.



by Honeywell



LIMITLESS POSSIBILITIES. Ask the Expert.

Technical Service: 800.873.5242 Customer Care (US): 800.836.8006 Customer Care (Canada): 888.212.7233 www.millerfallprotection.com

This equipment should only be used after reading and understanding the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.

LMBT

Lead them to safety. Build an enduring Culture of Safety where employees make safe choices on their own. www.honeywellsafety.com/culture

