

PRO ROLL™

STANDARD FEATURES

- 1/2 to 36" (1.2 to 91 cm) or 2,000 lbs (900 kg) pip capacity
- Clean and simple design avoids welder interference
- Bronze bearing to eliminate acring
- Handle large enough to work with gloved hand
- Roller adjustment from either side
- Galvanized inside tube resists corrosion
- Patented Fall Guard™ feature allows 1" (2.5 cm) safety zone around lock washer
- Formed steel legs
- Brake to lock loads for layout or fit-up
- Wheels trued for true pipe rotation
- Quick change design increases roller stand utility
- Leveling on either side of stand
- Set screw for double margin of safety



PART NO.	DESCRIPTION	WEIGHT
780440	Pro Roll (base only)	36 lbs (17.2 kg)
780441	Pro Roll with Roller Wheels	47 lbs (21.3 kg)
780442	Pro Roll with Ball Transfer Heads	49 lbs (22.2 kg)
780443	Pro Roll with Rubber Wheels	45 lbs (20.4 kg)
780444	Pro Roll with SS Wheels	47 lbs (21.3 kg)
780446	Pro Roll with Bar Stock Head	49 lbs (22.2 kg)