



Nitrile

Robust protection for food processing and heavy-duty jobs

- Reliable chemical splash protection
- Textured fingertips provide secure grip
- Complies with FDA food handling requirements
- Powdered for easier donning and moisture absorption



Industries

- Life Sciences
- Chemical
- Food Processing

Recommended For

- Transferring liquids and solids
- Sample taking and processing
- Handling incoming goods
- Maintenance
- All food processing, applications that have food contact



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	92-575
Material	Nitrile
Color	Blue
Glove Design	Chlorinated, Powdered, Silicone Free, Textured Fingers
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001:2008
Regulatory/Standards Compliance	Category III, EN 374:2003, EN ISO 374-1:2016, EN 420:2003 + A1:2009, EN ISO 374-5:2016, FDA21 CFR 177-2600, ISO 9001
Packaging	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Thailand
User Needs Segment	Robust
Available sizes	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Anti-static	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767, ASTM D6977, EN 420
Freedom from Holes (Inspection level I)	4.0 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.11 / 4.3		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.14 / 5.5		ASTM D3767, EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	586193	586194	586195	586196

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133


Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.